



Meets ANSI/ESD S20.20 and Packaging standard ANSI/ESD S541

Features

- Constructed from extruded honey-comb structure of high impact polypropylene material yielding superior strength and durability
- Provides physical protection with conductive material ensuring reliable path-to-ground
- Identified with ESD protective symbol as required by ANSI/ESD S541
- Chemical and moisture resistant
- Ideal use where corrugated and/or paper products cannot be used
- Product ships knocked down; easy to assemble
- Durable, reusable, ensuring best value
- Made in the United States of America

Specifications

Properties	Typical Values
Resin Type	Polypropylene
Conductive	Inherently
Surface Resistivity	< 1 x 10 ⁴ ohms per ANSI/ESD STM11.11 and ESD TR53
Material Thickness	4.0 mm
Melting Temperature	320° F
Heat Deflection	185° F

Item	L x W x D (IN)	L x W x D (MM)
39420	12 x 4 x 4	305 x 102 x 102
39421	12 x 6 x 4	305 x 152 x 102
39422	12 x 8 x 4	305 x 203 x 102
39423	18 x 6 x 4	457 x 152 x 102
39424	18 x 8 x 4	457 x 203 x 102
39425	18 x 12 x 4	457 x 305 x 102
39426	24 x 6 x 4	610 x 152 x 102

Unless otherwise noted, tolerances are ± 1/16"

Per Packaging standard ANSI/ESD S54.1 section 6.1. Inside an ESD Protected Area "Packaging used within an EPA (that satisfies the minimum requirements of ANSI/ESD S20.20) shall be:

1. Low charge generation.
2. Dissipative or conductive materials for intimate contact."



Made in the United States of America

Specifications and procedures subject to change without notice.

ENDURA-TEK™ OPEN BIN BOXES

PROTEKTIVE PAK

PROTEKTIVE PAK
 13520 MONTE VISTA AVENUE, CHINO, CA 91710
 PHONE (909) 627-2578
ProtektivePak.com

DRAWING NUMBER
 39420

DATE:
 March
 2024