

COAXIAL TERMINATION, 50 Ohm, MMCX, jack (female)

65_MMCX-50-0-31

Properties

- Various bandwidth
- Impedance matched
- Standard or precision types
- Low and medium power



Product configuration		
Interface	Gender	Standard
MMCX	jack (female)	HUBER+SUHNER - MMCX

Electrical data	
Impedance	50Ω
Operating frequency	0 GHz ... 3 GHz
VSWR	1.22
Return loss	20.1 dB

Electrical Data (frequency related)		
Frequency range	VSWR max	Return loss
0 GHz to 3 GHz	1.22	

Electrical Data (power)	
Average power	0.5 W at 30 °C ambient temperature. Linearly derated to W at 85 °C ambient temperature.

Interface and material data		
Interface	MMCX / jack (female)	
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Piece parts	Material	Plating

COAXIAL TERMINATION, 50 Ohm, MMCX, jack (female)

65_MMCX-50-0-31

Mechanical data	
Weight	0.0014 kg

Environmental data	
Operation temperature	-55 °C ... 85 °C

Ordering Information Table	
Item number	Item description
22649357	65_MMCX-50-0-31/111_OE

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P1769 / Date of publication: 09.11.2023 / uncontrolled copy