




## Cable Ties Polyamide 6.6 standard

- T-Series in PA66 coloured

Material Data	
Material	<b>Polyamide 6.6 (PA66)</b>
Operating Temperature	<b>-40 °C to +85 °C Continuous, (+105 °C for 500 h)</b>
Flammability	<b>UL94 V2</b>



Technical Table

Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile Strength (N)	Material	Colour	Application Tool
Polyamide 6.6 Colours								
116-01816	<b>T18R</b>	100	2.5	22.0	80	PA66	Blue (BU)	1-3, 5
111-03008	<b>T30R</b>	150	3.5	35.0	135	PA66	Blue (BU)	1-3, 5
111-04800	<b>T50R</b>	200	4.6	50.0	225	PA66	Blue (BU)	1-10
111-05404	<b>T50L</b>	390	4.6	110	225	PA66	Blue (BU)	1-10
116-08016	<b>T80R</b>	210	4.7	55.0	355	PA66	Blue (BU)	1-10
116-05416	<b>T80L</b>	390	4.7	110	355	PA66	Blue (BU)	1-10
116-01815	<b>T18R</b>	100	2.5	22.0	80	PA66	Green (GN)	1-3, 5
111-03014	<b>T30R</b>	150	3.5	35.0	135	PA66	Green (GN)	1-3, 5
111-05402	<b>T50L</b>	390	4.6	110	225	PA66	Green (GN)	1-10
116-08015	<b>T80R</b>	210	4.7	55.0	355	PA66	Green (GN)	1-10
116-05415	<b>T80L</b>	390	4.7	110	355	PA66	Green (GN)	1-10
111-12001	<b>T120R(E)</b>	387	7.6	100	535	PA66	Green (GN)	6-10
116-01812	<b>T18R</b>	100	2.5	22.0	80	PA66	Red (RD)	1-3, 5
111-03004	<b>T30R</b>	150	3.5	35.0	135	PA66	Red (RD)	1-3, 5
111-04804	<b>T50R</b>	200	4.6	50.0	225	PA66	Red (RD)	1-10
111-05406	<b>T50L</b>	390	4.6	110	225	PA66	Red (RD)	1-10
116-08012	<b>T80R</b>	210	4.7	55.0	355	PA66	Red (RD)	1-10
116-05412	<b>T80L</b>	390	4.7	110	355	PA66	Red (RD)	1-10
111-12002	<b>T120R(E)</b>	387	7.6	100	535	PA66	Red (RD)	6-10
116-01814	<b>T18R</b>	100	2.5	22.0	80	PA66	Yellow (YE)	1-3, 5
111-03006	<b>T30R</b>	150	3.5	35.0	135	PA66	Yellow (YE)	1-3, 5
111-04805	<b>T50R</b>	200	4.6	50.0	225	PA66	Yellow (YE)	1-10
111-05428	<b>T50L</b>	390	4.6	110	225	PA66	Yellow (YE)	1-10
116-08014	<b>T80R</b>	210	4.7	55.0	355	PA66	Yellow (YE)	1-10
116-05414	<b>T80L</b>	390	4.7	110	355	PA66	Yellow (YE)	1-10
116-15014	<b>T150R(H)</b>	365	7.6	100	670	PA66	Yellow (YE)	6-10

All dimensions in mm. Subject to technical changes.



Please note! Not all products listed on this page may have this approval. For product specific approvals please refer to the Appendix.