



www.centralsemi.com

UNITS V mA mA

DESCRIPTION:

The CENTRAL SEMICONDUCTOR CMPD6001 series types are silicon switching diodes manufactured by the epitaxial planar process, designed for switching applications requiring an extremely low leakage diode.

The following configurations are available:

CMPD6001 SINGLE CMPD6001A DUAL, COMMON ANODE CMPD6001C DUAL, COMMON CATHODE CMPD6001S DUAL, IN SERIES	MARKING CODE: MARKING CODE: MARKING CODE: MARKING CODE:	ULA ULC
MAXIMUM RATINGS: (T _A =25°C)	SYMBOL	
Continuous Reverse Voltage	VR	75
Peak Repetitive Reverse Voltage	V _{RRM}	100
Continuous Forward Current	۱ _F	250
Peak Repetitive Forward Current	IFRM	250
Peak Forward Surge Current, tp=1.0µs	IFSM	4.0
Peak Forward Surge Current, tp=1.0s	IESM	1.0

IFSM	4.0	А
IFSM	1.0	А
PD	350	mW
TJ, T _{stg}	-65 to +150	°C
Θ_{JA}	357	°C/W
	IFSM PD TJ, T _{stg}	^I FSM 1.0 P _D 350 T _J , T _{stg} -65 to +150

ELECTRICAL CHARACTERISTICS PER DIODE: (TA=25°C unless otherwise noted)					
SYMBOL	TEST CONDITIONS	MIN	MAX	UNITS	
I _R	V _R =75V		500	pА	
BVR	Ι _R =100μΑ	100		V	
V _F	I _F =1.0mA		0.85	V	
VF	I _F =10mA		0.95	V	
V _F	I _F =100mA		1.1	V	
CT	V _R =0, f=1.0MHz		2.0	pF	
t _{rr}	$I_R=I_F=10$ mA, $I_{rr}=1.0$ mA, $R_L=100\Omega$		3.0	μs	


R5 (9-May 2011)






SURFACE MOUNT ULTRA LOW LEAKAGE SILICON SWITCHING DIODES

SOT-23 CASE - MECHANICAL OUTLINE



DIMENSIONS						
	INCHES		MILLIMETERS			
SYMBOL	MIN	MAX	MIN	MAX		
А	0.003	0.007	0.08	0.18		
В	0.006	-	0.15	-		
С	-	0.005	-	0.13		
D	0.035	0.043	0.89	1.09		
Е	0.110	0.120	2.80	3.05		
F	0.075		1.90			
G	0.037		0.	95		
Н	0.047	0.055	1.19	1.40		
	0.083	0.098	2.10	2.49		
J	0.014	0.020	0.35	0.50		
SOT-23 (REV: R3)						

PIN CONFIGURATIONS



R5 (9-May 2011)

www.centralsemi.com

OUTSTANDING SUPPORT AND SUPERIOR SERVICES



PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- Inventory bonding
- Consolidated shipping options

- Custom bar coding for shipments
- Custom product packing

DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free quick ship samples (2nd day air)
- Online technical data and parametric search
- SPICE models
- Custom electrical curves
- Environmental regulation compliance
- Customer specific screening
- Up-screening capabilities

- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- Application and design sample kits
- Custom product and package development

CONTACT US

Corporate Headquarters & Customer Support Team

Central Semiconductor Corp. 145 Adams Avenue Hauppauge, NY 11788 USA Main Tel: (631) 435-1110 Main Fax: (631) 435-1824 Support Team Fax: (631) 435-3388 www.centralsemi.com

Worldwide Field Representatives: www.centralsemi.com/wwreps

Worldwide Distributors: www.centralsemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: <u>www.centralsemi.com/terms</u>

www.centralsemi.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Central Semiconductor: CMPD6001S TR PBFREE