

LTM8063 40V, 2A Step-Down µModule Regulator

DESCRIPTION

Demonstration circuit 2494A is a 40V, 2A step-down µModule® regulator featuring the **LTM8063**. The demo board is designed for 5V output from a 6.5V to 40V input. The wide input range allows a variety of input sources, such as automotive batteries and industrial supplies. The user adjustable features of the LTM8063 such as output voltage, switching frequency, soft-start, and power good can be changed on DC2494A simply by modifying the appropriate resistors and/or capacitors.

The LTM8063 can be programmed to different operation modes. The SYNC pin on the demo board is grounded by default for low ripple Burst Mode® operation. Moving JP1 to PULSE SKIPPING position changes the operation mode to pulse-skipping operation. To synchronous to an external clock, move JP1 to SYNC and apply the external clock to the SYNC turret. Once JP1 is on SPREAD SPECTRUM position, an external DC source can be applied to the SYNC pin to enable low EMI spread spectrum operation. This DC source can also be generated from Vout with appropriate voltage divider if V_{OUT} is 2.9V or higher. See the [Quick Start Procedure](#) section for more details.

Figure 1 shows the efficiency of the circuit under different input voltages in Burst Mode operation. The rated maximum load current is 2A, while derating is necessary for certain input voltage and thermal conditions. Figure 2 shows the LTM8063 thermal performance on DC2494A demo board.


The demo board has an EMI filter installed. An inductor L1, which is shorted on the board by default, can be added in the EMI filter to further reduce the conducted emission.

The LTM8063 data sheet gives a complete description of the part, operation and application information. The data sheet must be read in conjunction with this demo manual for DC2494A.

Design files for this circuit board are available at <http://www.linear.com/demo/DC2494A>

All registered trademarks and trademarks are the property of their respective owners.

BOARD PHOTO



DEMO MANUAL DC2494A

PERFORMANCE SUMMARY Specifications are at $T_A = 25^\circ\text{C}$

SYMBOL	PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
V_{IN}	Input Voltage Range		6.5		40	V
V_{OUT}	Output Voltage		4.85	5	5.15	V
I_{OUT}	Maximum Output Current		2			A
f_{SW}	Switching Frequency			1.4		MHz
EFF	Efficiency at DC	$V_{IN} = 12\text{V}, I_{OUT} = 1\text{A}$		91.1		%




Figure 1. DC2494A Efficiency vs Load Current




Figure 2. DC2494A Case Temperature Rise vs Input Voltage

PERFORMANCE SUMMARY




Figure 3. DC2494A Output Noise Spectrum, $V_{IN} = 12V$, $V_{OUT} = 5V$, $I_{OUT} = 2A$




Figure 4. DC2494A Output Ripple, $V_{IN} = 12V$, $V_{OUT} = 5V$, $I_{OUT} = 2A$

QUICK START PROCEDURE

Demonstration circuit 2494A is easy to set up to evaluate the performance of the LTM8063. Refer to Figure 4 for proper measurement equipment setup and follow the procedure below:

NOTE: When measuring the input or output voltage ripple, care must be taken to avoid a long ground lead on the oscilloscope probe. See Figure 5 for the proper scope technique.

1. Set an input power supply that is capable of 40V/2A. Then turn off the supply.
2. With power off, connect the supply to the input terminals V_{EMI} and GND.
3. Turn on the power at the input.

NOTE: Make sure that the input voltage never exceeds 40V.

4. Check for the proper output voltage of 5V. Turn off the power at the input.
5. Once the proper output voltage is established, connect a variable load capable of sinking 2A at 5V to the output terminals V_{OUT} and GND. Set the current for 0A.
 - a. If efficiency measurements are desired, an ammeter can be put in series with the output load in order to measure the DC2494A's output current.
 - b. A voltmeter can be placed across the output terminals in order to get an accurate output voltage measurement.

6. Turn on the power at the input.

NOTE: If there is no output, temporarily disconnect the load to make sure that the load is not set too high.

7. Once the proper output voltage is established again, adjust the load and/or input within the operating range and observe the output voltage regulation, ripple voltage, efficiency and other desired parameters.
8. An external clock can be added to the SYNC terminal when SYNC function is used (JP1 on the SYNC position). Please ensure that the chosen RT sets the LTM8063 switching frequency to equal or below the lowest SYNC frequency. An external 2.9V to 4.2V DC voltage can be applied to SYNC turret to enable low noise spread spectrum function (JP1 on the SPREAD SPECTRUM position). This DC voltage can be generated from V_{OUT} with a appropriate voltage divider. See the Synchronization section in the data sheet for more information.

QUICK START PROCEDURE




Figure 5. Proper Measurement Equipment Setup





Figure 6. Measuring Output Ripple

DEMO MANUAL DC2494A

PARTS LIST

ITEM	QTY	REFERENCE	PART DESCRIPTION	MANUFACTURER/PART NUMBER
Required Circuit Components				
1	1	C1	CAP., X7R, 47 μ F, 10V, 10%, 1210	MURATA, GRM32ER71A476KE15L
2	1	C2	CAP., X7R, 4.7 μ F, 50V, 10%, 1206	AVX, 12065C475KAT2A
3	1	C3	CAP., X7R, 0.1 μ F, 16V, 10%, 0603	MURATA, GRM188R71C104KA01D
4	1	R1	RES, CHIP, 100k, 1/10W, 1%, 0603	VISHAY, CRCW0603100KFKEA
5	1	R2	RES, CHIP, 45.3k, 1/10W, 1%, 0603	VISHAY, CRCW060345K3FKEA
6	1	R3	RES, CHIP, 27.4k, 1/10W, 1%, 0603	VISHAY, CRCW060327K4FKEA
7	1	R4	RES., CHIP, 1M, 1/10W, 1%, 0603	VISHAY, CRCW06031M00FKEA
8	1	U1	IC, REGULATOR, 28BGA	LINEAR TECH., LTM8063EY#PBF
Additional Demo Board Circuit Components				
1	0	C4 (OPT)	CAP., OPTION, 0603	
2	1	C5	CAP., X7R, 10 μ F, 10V, 10%, 0805	MURATA, GRM21BR71A106KA73L
3	2	C6, C7	CAP., X7R, 4.7 μ F, 50V, 10%, 1206	AVX, 12065C475KAT2A
4	4	C8, C10, C11, C12	CAP., X7R, 0.1 μ F, 50V, 10%, 0603	MURATA, GRM188R71H104KA93D
5	1	C9	CAP., ALUM, 22 μ F, 63V, 20%	SUN ELEC., 63CE22BS
6	1	FB1	FERRITE BEAD 0805	TDK, MPZ2012S221AT000
7	0	L1 (OPT.)	IND., OPTION	
8	0	R5, R6, R7 (OPT.)	RES., 0603	
Hardware: For Demo Board Only				
1	10	E1-E10	TESTPOINT, TURRET, 0.094"	MILL-MAX, 2501-2-00-80-00-00-07-0
2	1	JP1	DOUBLE ROW HEADER 2 \times 4 0.079"	WURTH ELECTRONICS, 62000821121
3	1	XJP1	SHUNT, 0.079" CENTER	WURTH ELECTRONICS, 60800213421
4	4	MH1-MH4	STAND-OFF, NYLON 0.375"	KEYSTONE, 8832(SNAP ON)

SCHEMATIC DIAGRAM



NOTES: UNLESS OTHERWISE SPECIFIED
 1. ALL RESISTORS ARE 0603.
 ALL CAPACITORS ARE 0603.



ESD Caution

ESD (electrostatic discharge) sensitive device. Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

Legal Terms and Conditions

By using the evaluation board discussed herein (together with any tools, components documentation or support materials, the "Evaluation Board"), you are agreeing to be bound by the terms and conditions set forth below ("Agreement") unless you have purchased the Evaluation Board, in which case the Analog Devices Standard Terms and Conditions of Sale shall govern. Do not use the Evaluation Board until you have read and agreed to the Agreement. Your use of the Evaluation Board shall signify your acceptance of the Agreement. This Agreement is made by and between you ("Customer") and Analog Devices, Inc. ("ADI"), with its principal place of business at One Technology Way, Norwood, MA 02062, USA. Subject to the terms and conditions of the Agreement, ADI hereby grants to Customer a free, limited, personal, temporary, non-exclusive, non-sublicensable, non-transferable license to use the Evaluation Board FOR EVALUATION PURPOSES ONLY. Customer understands and agrees that the Evaluation Board is provided for the sole and exclusive purpose referenced above, and agrees not to use the Evaluation Board for any other purpose. Furthermore, the license granted is expressly made subject to the following additional limitations: Customer shall not (i) rent, lease, display, sell, transfer, assign, sublicense, or distribute the Evaluation Board; and (ii) permit any Third Party to access the Evaluation Board. As used herein, the term "Third Party" includes any entity other than ADI, Customer, their employees, affiliates and in-house consultants. The Evaluation Board is NOT sold to Customer; all rights not expressly granted herein, including ownership of the Evaluation Board, are reserved by ADI. CONFIDENTIALITY. This Agreement and the Evaluation Board shall all be considered the confidential and proprietary information of ADI. Customer may not disclose or transfer any portion of the Evaluation Board to any other party for any reason. Upon discontinuation of use of the Evaluation Board or termination of this Agreement, Customer agrees to promptly return the Evaluation Board to ADI. ADDITIONAL RESTRICTIONS. Customer may not disassemble, decompile or reverse engineer chips on the Evaluation Board. Customer shall inform ADI of any occurred damages or any modifications or alterations it makes to the Evaluation Board, including but not limited to soldering or any other activity that affects the material content of the Evaluation Board. Modifications to the Evaluation Board must comply with applicable law, including but not limited to the RoHS Directive. TERMINATION. ADI may terminate this Agreement at any time upon giving written notice to Customer. Customer agrees to return to ADI the Evaluation Board at that time. LIMITATION OF LIABILITY. THE EVALUATION BOARD PROVIDED HEREUNDER IS PROVIDED "AS IS" AND ADI MAKES NO WARRANTIES OR REPRESENTATIONS OF ANY KIND WITH RESPECT TO IT. ADI SPECIFICALLY DISCLAIMS ANY REPRESENTATIONS, ENDORSEMENTS, GUARANTEES, OR WARRANTIES, EXPRESS OR IMPLIED, RELATED TO THE EVALUATION BOARD INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTY OF MERCHANTABILITY, TITLE, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHTS. IN NO EVENT WILL ADI AND ITS LICENSORS BE LIABLE FOR ANY INCIDENTAL, SPECIAL, INDIRECT, OR CONSEQUENTIAL DAMAGES RESULTING FROM CUSTOMER'S POSSESSION OR USE OF THE EVALUATION BOARD, INCLUDING BUT NOT LIMITED TO LOST PROFITS, DELAY COSTS, LABOR COSTS OR LOSS OF GOODWILL. ADI'S TOTAL LIABILITY FROM ANY AND ALL CAUSES SHALL BE LIMITED TO THE AMOUNT OF ONE HUNDRED US DOLLARS (\$100.00). EXPORT. Customer agrees that it will not directly or indirectly export the Evaluation Board to another country, and that it will comply with all applicable United States federal laws and regulations relating to exports. GOVERNING LAW. This Agreement shall be governed by and construed in accordance with the substantive laws of the Commonwealth of Massachusetts (excluding conflict of law rules). Any legal action regarding this Agreement will be heard in the state or federal courts having jurisdiction in Suffolk County, Massachusetts, and Customer hereby submits to the personal jurisdiction and venue of such courts. The United Nations Convention on Contracts for the International Sale of Goods shall not apply to this Agreement and is expressly disclaimed.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Analog Devices Inc.:](#)

[DC2494A](#)