

# Joysticks

# **SERIES 04J**

Joystick with Center Pushbutton

# **FEATURES**


- Sealed against contamination when properly mounted (IP67)
- Two styles available: behind-panel mount or front-panel mount
- RoHS compliant
- · Short behind panel

### **DESCRIPTION**

Series 04J is a single pole, 4-way toggle switch with a pushbutton in the center position. 4-way contact is made in the opposite direction of travel.

**DIMENSIONS** in inches (and millimeters)





### **ELECTRIC & MECHANICAL RATINGS**

**Rating**: 2 amp resistive; 0.5 amp inductive at 28VDC or 115VAC

Contact Resistance: .05 ohms (max)
Operating Temperature: -55°C to +85°C
Operational Life: 100,000 cycles (min)
Pushbutton Travel: .020 minimum overall
Pushbutton Operating Force: 5 lbs. (max)
Insulation Resistance: 10.000M ohms

Vibration: per MIL-DTL-9419F, Method 3.5.9 Toggle Lever Travel: 15° from center (max) Toggle Operating Force: 16 oz ± 6 oz initial Toggle Pivot & Stop Strength: 25 lbs. (max) Mechanical Shock: per MIL-STD-810, procedure I, method 516.4 Immersion: per MIL-PRF-8805

Moisture Resistance: per MIL-DTL-9419

# **MATERIALS & FINISHES**

Switch Body & Concave Cap: Thermoplastic (black, cone-shaped cap is gray)

Bushing: Aluminum alloy (black chrome)

Contact Terminals: 1/2 hard brass (rold over

Contact Terminals: 1/2 hard brass (gold over silver over nickel plating)

**Spanner Nut**: Stainless steel (black chrome) **O-Ring**: 50 durometer fluorosilicone

