


Central
Semiconductor Corp.

**Central
Semiconductor Corp.**
**Central™
Semiconductor Corp.**

145 Adams Avenue
Hauppauge, New York 11788



2N3641 PN3641
2N3642 PN3642
2N3643 PN3643

JEDEC TO-105 JEDEC TO-92

NPN SILICON SIGNAL TRANSISTORS

DESCRIPTION

The CENTRAL SEMICONDUCTOR 2N3641, PN3641 Series types are Silicon NPN Small Signal Transistors designed for general purpose amplifier applications.

MAXIMUM RATINGS (T_A=25°C)

	<u>SYMBOL</u>	<u>2N3641 2N3643 PN3641 PN3643</u>	<u>2N3642 PN3642</u>	<u>UNIT</u>
Collector-Base Voltage	V _{CB0}	60	60	V
Collector-Emitter Voltage	V _{CE0}	30	45	V
Emitter-Base Voltage	V _{EBO}	5.0	5.0	V
Collector Current	I _C	500	500	mA
		<u>2N3641 2N3642 2N3643</u>	<u>PN3641 PN3642 PN4643</u>	
Power Dissipation Operating and Storage Junction Temperature	P _D T _J , T _{stg}	350 -55 TO +125	625 -55 TO +150	mW °C

ELECTRICAL CHARACTERISTICS (T_A=25°C)

<u>SYMBOL</u>	<u>TEST CONDITIONS</u>	<u>2N3641 PN3641 MIN MAX</u>	<u>2N3642 PN3642 MIN MAX</u>	<u>2N3643 PN3643 MIN MAX</u>	<u>UNIT</u>
I _{CES}	V _{CE} =50V	50	50	50	nA
BV _{CB0}	I _C =10μA	60	60	60	V
BV _{CES}	I _C =10μA	60	60	60	V
BV _{CE0}	I _C =10mA	30	45	30	V
BV _{EBO}	I _E =10μA	5.0	5.0	5.0	V
V _{CE(SAT)}	I _C =150mA, I _B =15mA	0.22	0.22	0.22	V
h _{FE}	V _{CE} =10V, I _C =150mA	40 120	40 120	100 300	
h _{FE}	V _{CE} =10V, I _C =500mA	15	15	25	
f _T	V _{CE} =5.0V, I _C =50mA, f=100MHz	150	150	250	MHz
C _{ob}	V _{CB} =10V, f=140kHz	8.0	8.0	8.0	pF
G _{pe}	V _{CE} =15V, R _G =140Ω, R _L =260Ω, f=30MHz, P _{IN} =40mW	10	10	10	dB
η	V _{CE} =15V, R _G =140Ω, R _L =260Ω, f=30MHz, P _{IN} =40mW	60	60	60	%
t _{on}	I _C =300mA, I _{B1} =30mA	60	60	60	ns
t _{off}	I _C =300mA, I _{B1} =I _{B2} =30mA	150	150	150	ns

145 Adams Avenue, Hauppauge, NY 11788 USA
Tel: (631) 435-1110 • Fax: (631) 435-1824

OUTSTANDING SUPPORT AND SUPERIOR SERVICES



PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- Inventory bonding
- Consolidated shipping options
- Custom bar coding for shipments
- Custom product packing

DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free quick ship samples (2nd day air)
- Online technical data and parametric search
- SPICE models
- Custom electrical curves
- Environmental regulation compliance
- Customer specific screening
- Up-screening capabilities
- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- Application and design sample kits
- Custom product and package development

REQUESTING PRODUCT PLATING

1. If requesting Tin/Lead plated devices, add the suffix "TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
2. If requesting Lead (Pb) Free plated devices, add the suffix "PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

CONTACT US

Corporate Headquarters & Customer Support Team

Central Semiconductor Corp.
145 Adams Avenue
Hauppauge, NY 11788 USA
Main Tel: (631) 435-1110
Main Fax: (631) 435-1824
Support Team Fax: (631) 435-3388
www.centrasemi.com

Worldwide Field Representatives:
www.centrasemi.com/wwreps

Worldwide Distributors:
www.centrasemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: www.centrasemi.com/terms

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Central Semiconductor:](#)

[PN3643 PBFREE](#)