

**Product:** [9239](#) 

Audio Coax, Low Noise, RG-174, 26 AWG Str BCCS, 90% TC Brd, PVC Jkt



## Product Description

Audio Coax, Low Noise, RG-174, 26 AWG (7x34) Bare Copper Covered Steel Conductor, PE Insulation, PVC Conductive Layer, 90% Tinned Copper Braid Shield, PVC Jacket

## Technical Specifications

### Product Overview

Suitable Applications:	Low noise microphone, Analog audio, Instrumentation
------------------------	---

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
26	7x34	BCCS - Bare Copper Covered Steel	0.019 in	1

Conductor Count:	1
------------------	---

#### Insulation

Layer	Material	Nominal Diameter
1	PE - Polyethylene	0.044 in
2	PVC - Polyvinyl Chloride (Conductive)	0.056 in

#### Outer Shield Material

Type	Material	Coverage [%]
Braid	Tinned Copper (TC)	90%

#### Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.101 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
89.6 Ohm/1000ft	97 Ohm/1000ft	14 Ohm/1000ft	11.7 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Shield
44 pF/ft

#### Delay

Nominal Velocity of Propagation (VP) [%]
57%

#### Voltage

Voltage Rating [V]
300 V RMS

Electrical Characteristics Notes:	NBS Low Noise Test (Modified), MIL-DTL-17J Paragraph 4.8.14, 8 mV Peak to Peak Max
-----------------------------------	--

## Temperature Range

Non-UL Temp Rating:	60°C
Operating Temp Range:	-40°C To +60°C

## Mechanical Characteristics

Bulk Cable Weight:	7.6 lbs/1000ft
Max. Pull Tension:	14.4 lbs
Min Bend Radius/Minor Axis:	1 in

## Standards

CPR Euroclass:	Eca
----------------	-----

## Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

## Flammability, LS0H, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
-------------------	---------------

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	Putup Type	Length	UPC
9239 010100	Black	Reel	100 ft	612825358824
9239 010500	Black	Reel	500 ft	612825358855
9239 0101000	Black	Reel	1,000 ft	612825357728

## Product Notes

Notes:	Not recommended for RF use. Low noise audio applications.
--------	---

## History

Update and Revision:	Revision Number: 0.230 Revision Date: 09-30-2020
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product

Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9239 010500](#) [9239 0101000](#) [9239 010100](#)