


3M™ High Flex Life Cable

.050" 28 AWG Stranded, PVC

3319 Series



- Flex life of 100 million cycles at 1 3/4 inch diameter
- 19 strands of high strength copper alloy provide the longest flex life available for dynamic applications
- 28 AWG wire on .050 inch wire spacing permits mass termination to a broad line of IDC connectors
- Zippable for branching or discrete termination
- RoHS* Compliant

Date Modified: November 30, 2006

TS-0059-14
Sheet 1 of 2

Physical

Insulation

Material: Polyvinyl Chloride (PVC)

Color: Black

Marking

Standard: None

Canadian Option: **UL** AWM 2651 105C 300V VW1 3M NU **CSA** AWM IA 105C 300V FT1 EU <50V

Conductors: 28 AWG, 19 x 40 AWG [19 x Ø 0.79] Silver Plated Stranded Copper Alloy (89% Conductivity)

Electrical

Voltage Rating: USA: 300V

Canada: 300V

EU: <50V

Insulation Resistance: $>1 \times 10^{10} \Omega / 10\text{ft}$ [3m]

Unbalanced

Balanced

Characteristic Impedance: 103 Ω

171 Ω

Capacitance: 13.6 pF/ft [44.62 pF/m]

7.9 pF/ft [25.91 pF/m]

Inductance: 0.14 $\mu\text{H}/\text{ft}$ [0.47 $\mu\text{H}/\text{m}$]

0.23 $\mu\text{H}/\text{ft}$ [0.76 $\mu\text{H}/\text{m}$]

Propagation Delay: 1.40 ns/ft [4.59 ns/m]

1.35 ns/ft [4.43 ns/m]

Velocity of Propagation: 73%

75%

Note: Unbalanced is measured between ground-signal-ground conductors. Balanced is measured between signal conductors within a pair.

Environmental

Temperature Rating: -20°C to +105°C

Flammability Rating: USA: VW-1

Canada: FT1

"RoHS compliant" means that the product or part does not contain any of the following substances in excess of the following maximum concentration values in any homogeneous material, unless the substance is in an application that is exempt under RoHS: (a) 0.1% (by weight) for lead, mercury, hexavalent chromium, polybrominated biphenyls or polybrominated diphenyl ethers; or (b) 0.01% (by weight) for cadmium. Unless otherwise stated by 3M in writing, this information represents 3M's knowledge and belief based upon information provided by third party suppliers to 3M.

UL File No.: E42769, Style No.: 2651

3M

Interconnect Solutions

<http://www.3M.com/interconnects/>

3M is a trademark of 3M Company.

For technical, sales or ordering information call


800-225-5373

3M™ High Flex Life Cable

.050" 28 AWG Stranded, PVC

3319 Series

Number of Conductors	3M Part Number	Dimension A	Dimension B
09	3319/09	0.450 ± .010 [11.43]	0.400 ± .007 [10.18]
10	3319/10	0.500 ± .010 [12.70]	0.450 ± .007 [11.43]
14	3319/14	0.700 ± .010 [17.78]	0.650 ± .007 [16.51]
15	3319/15	0.750 ± .010 [19.05]	0.700 ± .007 [17.78]
16	3319/16	0.800 ± .015 [20.32]	0.750 ± .011 [19.05]
20	3319/20	1.000 ± .015 [25.40]	0.950 ± .011 [24.13]
24	3319/24	1.200 ± .015 [30.48]	1.150 ± .011 [29.21]
25	3319/25	1.250 ± .015 [31.75]	1.200 ± .011 [30.48]
26	3319/26	1.300 ± .015 [33.02]	1.250 ± .011 [31.75]
30	3319/30	1.500 ± .020 [38.10]	1.450 ± .015 [36.83]
34	3319/34	1.700 ± .020 [43.18]	1.650 ± .015 [41.91]
36	3319/36	1.800 ± .020 [45.72]	1.750 ± .015 [44.45]
37	3319/37	1.850 ± .020 [46.99]	1.800 ± .015 [45.72]
40	3319/40	2.000 ± .020 [50.80]	1.950 ± .015 [49.53]
50	3319/50	2.500 ± .020 [63.50]	2.450 ± .015 [62.23]
60	3319/60	3.000 ± .020 [76.20]	2.950 ± .015 [74.93]
64	3319/64	3.200 ± .020 [81.28]	3.150 ± .015 [80.01]




Inch
[mm]

Tolerance Unless Noted			
	.0	.00	.000
inch	±.1	±.01	±.005

[] Dimensions for Reference Only

Note: Red marking on one edge of cable designates wire #1.

Ordering Information



Note: Contact 3M for availability of additional conductor counts and/or custom roll lengths.

TS-0059-14
Sheet 2 of 2

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.



3M Electronics

6801 River Place Blvd.
Austin, TX 78726-9000
800/225-5373
www.3M.com/electronics

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of one (1) year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Minimum 10%
Post-Consumer Fiber

Printed in USA.

© 3M 2006