

# Low Capacitance TRANSZORB<sup>®</sup> Transient Voltage Suppressors


**DO-15 (DO-204AC)**

## FEATURES

- Glass passivated chip junction
- 500 W peak pulse power capability with a 10/1000  $\mu$ s waveform, repetitive rate (duty cycle): 0.01 %
- Excellent clamping capability
- Very fast response time
- Low incremental surge resistance
- Solder dip 275 °C max. 10 s, per JESD 22-B106
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)


**RoHS**  
COMPLIANT

## TYPICAL APPLICATIONS

Use in sensitive electronics protection against voltage transients induced by inductive load switching and lighting on ICs, MOSFET, signal lines of sensor units for consumer, computer, industrial, and telecommunication.

## MECHANICAL DATA

**Case:** DO-15 (DO-204AC)

Molded epoxy over passivated body

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant and commercial grade

**Terminals:** matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test

**Polarity:** color band denotes cathode end

| PRIMARY CHARACTERISTICS |                  |
|-------------------------|------------------|
| $V_{WM}$                | 5.0 V to 50 V    |
| $V_{BR}$                | 7.6 V to 55.5 V  |
| $P_{PPM}$               | 500 W            |
| $P_D$                   | 3.0 W            |
| $T_J$ max.              | 175 °C           |
| Polarity                | Uni-directional  |
| Package                 | DO-15 (DO-204AC) |

| MAXIMUM RATINGS ( $T_A = 25$ °C unless otherwise noted)                     |                |                |      |
|---|----------------|----------------|------|
| PARAMETER   | SYMBOL         | VALUE          | UNIT |
| Peak pulse power dissipation with a 10/1000 $\mu$ s waveform <sup>(1)</sup> | $P_{PPM}$      | 500            | W    |
| Peak pulse current with a 10/1000 $\mu$ s waveform (fig. 3) <sup>(1)</sup>  | $I_{PPM}$      | See next table | A    |
| Power dissipation on infinite heatsink at $T_L = 75$ °C (fig. 2)            | $P_D$          | 3.0            | W    |
| Operating junction and storage temperature range                            | $T_J, T_{STG}$ | -55 to +175    | °C   |

### Note

<sup>(1)</sup> Non-repetitive current pulse, per fig. 3 and derated above  $T_A = 25$  °C per fig. 2



| <b>ELECTRICAL CHARACTERISTICS</b> ( $T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted) |   |   |   |   |  |  |  |  |   |
|--|---|---|---|---|--|--|--|--|---|
| PART NUMBER  | BREAKDOWN VOLTAGE AT $I_T = 1.0\text{ mA}$ $V_{BR}$ (V) | STAND-OFF VOLTAGE <sup>(1)</sup> $V_{WM}$ (V) | MAXIMUM REVERSE LEAKAGE AT $V_{WM}$ $I_D$ ( $\mu\text{A}$ ) | MAXIMUM CLAMPING VOLTAGE AT $I_{PP} = 5.0\text{ A}$ $V_C$ (V) | MAXIMUM PEAK PULSE CURRENT PER FIG. 3 $I_{PP}$ (A) | MAXIMUM JUNCTION CAPACITANCE AT 0 V (pF) | WORKING INVERSE BLOCKING VOLTAGE $V_{WIB}$ (V) | INVERSE BLOCKING LEAKAGE CURRENT $V_{WIB}$ $I_{IB}$ (mA) | PEAK INVERSE BLOCKING VOLTAGE $V_{PIB}$ (V) |
|  | MIN.  |   |   |   |  |  |  |  |   |
| SAC5.0   | 7.60  | 5   | 300   | 10.0  | 44   | 50                                       | 75   | 1.0  | 100   |
| SAC6.0   | 7.90  | 6   | 300   | 11.2  | 41   | 50                                       | 75   | 1.0  | 100   |
| SAC7.0   | 8.33  | 7   | 300   | 12.6  | 38   | 50                                       | 75   | 1.0  | 100   |
| SAC8.0   | 8.89  | 8   | 100   | 13.4  | 36   | 50                                       | 75   | 1.0  | 100   |
| SAC8.5   | 9.44  | 8.5   | 50  | 14.0  | 34   | 50                                       | 75   | 1.0  | 100   |
| SAC10  | 11.10   | 10  | 5.0   | 16.3  | 29   | 50                                       | 75   | 1.0  | 100   |
| SAC12  | 13.30   | 12  | 5.0   | 19.0  | 25   | 50                                       | 75   | 1.0  | 100   |
| SAC15  | 16.70   | 15  | 5.0   | 23.6  | 20   | 50                                       | 75   | 1.0  | 100   |
| SAC18  | 20.00   | 18  | 5.0   | 28.8  | 15   | 50                                       | 75   | 1.0  | 100   |
| SAC22  | 24.40   | 22  | 5.0   | 35.4  | 14   | 50                                       | 75   | 1.0  | 100   |
| SAC26  | 28.90   | 26  | 5.0   | 42.3  | 11.1   | 50                                       | 75   | 1.0  | 100   |
| SAC30  | 33.30   | 30  | 5.0   | 48.6  | 10.0   | 50                                       | 75   | 1.0  | 100   |
| SAC36  | 40.00   | 36  | 5.0   | 60.0  | 8.6  | 50                                       | 75   | 1.0  | 100   |
| SAC45  | 50.00   | 45  | 5.0   | 77.0  | 6.8  | 50                                       | 150  | 1.0  | 200   |
| SAC50  | 55.50   | 50  | 5.0   | 88.0  | 5.8  | 50                                       | 150  | 1.0  | 200   |

**Note**

<sup>(1)</sup> Non-repetitive current pulse, per fig. 3 and derated above  $T_A = 25\text{ }^\circ\text{C}$  per fig. 2

| <b>ORDERING INFORMATION</b> (Example) |                 |                        |               |                                  |
|---------------------------------------|-----------------|------------------------|---------------|----------------------------------|
| PREFERRED PIN                         | UNIT WEIGHT (g) | PREFERRED PACKAGE CODE | BASE QUANTITY | DELIVERY MODE                    |
| SAC5.0-E3/54                          | 0.432           | 54                     | 4000          | 13" diameter paper tape and reel |

**RATINGS AND CHARACTERISTICS CURVES** ( $T_A = 25\text{ }^\circ\text{C}$  unless otherwise noted)




Fig. 1 - Peak Pulse Power Rating Curve




Fig. 3 - Pulse Waveform






Fig. 2 - Power Derating Curve



**Application Note:** Device must be used with two units in parallel, opposite in polarity as shown in circuit for AC signal line protection.

Fig. 4 - AC Line Protection Application


**SCHEMATIC**





### PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

#### DO-15 (DO-204AC)



#### Note

- Dimensions of mold length and diameter do not include mold flash and gate burr, mold flash shall not exceed 0.015 inch per side. These dimensions are measured at the outermost extreme of the plastic body



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Vishay:

[SAC10-E3/4](#) [SAC10-E3/54](#) [SAC10-E3/73](#) [SAC12-E3/54](#) [SAC12-E3/73](#) [SAC15-E3/4](#) [SAC15-E3/54](#) [SAC15-E3/73](#)  
[SAC18/4](#) [SAC18/54](#) [SAC18-E3/4](#) [SAC18-E3/51](#) [SAC18-E3/54](#) [SAC18-E3/73](#) [SAC22/4](#) [SAC22-E3/54](#) [SAC22-E3/73](#) [SAC26/4](#) [SAC26-E3/4](#) [SAC26-E3/54](#) [SAC26-E3/73](#) [SAC30-E3/54](#) [SAC30-E3/73](#) [SAC36-E3/54](#) [SAC36-E3/73](#) [SAC45-E3/23](#) [SAC45-E3/4](#) [SAC45-E3/51](#) [SAC45-E3/54](#) [SAC45-E3/73](#) [SAC5.0/4](#) [SAC5.0/54](#) [SAC5.0-E3/23](#)  
[SAC5.0-E3/4](#) [SAC5.0-E3/51](#) [SAC5.0-E3/54](#) [SAC5.0-E3/73](#) [SAC50/4](#) [SAC50/54](#) [SAC50-E3/4](#) [SAC50-E3/51](#)  
[SAC50-E3/54](#) [SAC50-E3/73](#) [SAC6.0/23](#) [SAC6.0/4](#) [SAC6.0/54](#) [SAC6.0-E3/23](#) [SAC6.0-E3/4](#) [SAC6.0-E3/51](#) [SAC6.0-E3/54](#) [SAC6.0-E3/73](#) [SAC7.0/4](#) [SAC7.0-E3/4](#) [SAC7.0-E3/51](#) [SAC7.0-E3/54](#) [SAC7.0-E3/73](#) [SAC8.0-E3/4](#) [SAC8.0-E3/51](#) [SAC8.0-E3/54](#) [SAC8.0-E3/73](#) [SAC8.5/4](#) [SAC8.5-E3/4](#) [SAC8.5-E3/51](#) [SAC8.5-E3/54](#) [SAC8.5-E3/73](#) [SAC10-E3/1](#) [SAC18-E3/1](#) [SAC45/1](#) [SAC45-E3/1](#) [SAC5.0/1](#) [SAC5.0-E3/1](#) [SAC6.0/1](#) [SAC6.0-E3/1](#) [SAC7.0/1](#) [SAC7.0-E3/1](#) [SAC8.0/1](#) [SAC8.5/1](#) [SAC8.5-E3/1](#)