



# proximity sensor SME-8M-DO-24V-K-7,5-OE

Part number: 546799

★ Core product range

FESTO



## Data sheet

Feature	Value
Authorisation	RCM Mark c UL us - Listed (OL)
CE mark (see declaration of conformity)	to EU directive for EMC
Special characteristics	Oil resistant
Materials note	Free of copper and PTFE Conforms to RoHS
Measuring principle	Reed magnetic
Ambient temperature	-40 ... 70 °C
Switch output	with contact, bipolar
Switching element function	Normally closed contact
Max. output current	80 mA
Max. output current in mounting kits	80 mA
Max. contact rating AC	2.4 VA
Max. contact rating DC	2.4 W
Max. switching capacity DC in mounting kits	2.4 W
Max. switching capacity AC in mounting kits	2.4 VA
Voltage drop	4.25 V
Short circuit strength	No
Overload withstand capability	Not available
Operating voltage range AC	5 ... 30 V
Operating voltage range DC	5 ... 30 V
Polarity protected	No
Electrical connection	Cable 3-core
Connector exit direction	axial
Test conditions of cable	Bending strength according to Festo standard Test conditions on request Chain link trunking: 5 million cycles, bending radius 75 mm
Cable length	7.5 m
Cable attribute	Standard + chain link trunking
Material cable sheath	TPE-U(PUR)
Mounting type	Tightened Insertable in slot from above
Product weight	87.1 g
Material housing	PA High alloy steel, non-corrosive
Operating status display	Yellow LED
Ambient temperature with flexible cable installation	-5 ... 70 °C
Protection class	IP65 IP68