



VRef 0...2.5V (0.11 Ohm sense resistor)  
 >=2.50V 100% - 1.77A RMS  
 1.25V 50% - 0.88A RMS  
 0.50V 20% - 0.35A RMS

EN (with pull-up)  
 GND driver enabled  
 VCC driver disabled

PDN/UART (with pull-down)  
 GND automatic standstill current reduction  
 VCC automatic standstill power down disable  
 optional UART interface

CLK (with pull-down)  
 GND internal clock  
 optional supply external clock

MS1	MS2	Steps	Interpolation	ChopperMode
GND	GND	8	Yes to 256	stealthChop2
VCC	GND	2	Yes to 256	stealthChop2
GND	VCC	4	Yes to 256	stealthChop2
VCC	VCC	16	Yes to 256	stealthChop2

To access all other modes (eg spreadCycle) you have to use the UART interface.

Released under the Creative Commons Attribution Share-Alike License. <http://creativecommons.org/licenses/by-sa/4.0/>  
 Designed by Stephan Watterott (Watterott electronic)

[www.watterott.com](http://www.watterott.com)  
 SilentStepStick-TMC2208\_v11  
 06.03.2017 21:25:38  
 Sheet: 1/1

OSHW Watterott

# Component Side View (Bottom)

