




Toroidal Transformer Data Sheet

625VA Open Style, with Leads.
230V Primary, Dual Secondaries

High quality open style toroidal transformers with a single 230V/50-60Hz primary winding. Twin secondary windings may be connected in series or parallel, or used independently



Primary 230V @ 50-60Hz
Secondary: 2 x Vsec @ 312.5VA Each
Suitable for Series/Parallel connection



RS Part No.	Nuvotem Part Number	Full Load Vsec [V]	Rated Current per Sec [A]	No Load Vsec [V]	DC Resistance [Ohms] @ 25°C	DEKRA Certificate
223-8320	RS0625P1-2-040	2 x 40	7.813	2 x 42.31	2 x 0.1418	2161054.02
223-8336	RS0625P1-2-045	2 x 45	6.944	2 x 47.38	2 x 0.1792	2161054.02
223-8342	RS0625P1-2-050	2 x 50	6.250	2 x 52.44	2 x 0.1998	2161054.02
223-8358	RS0625P1-2-055	2 x 55	5.682	2 x 57.96	2 x 0.2509	2161054.02

Primary Winding	Input Voltage Range : 207V–253V (230V +/- 10%) @ 50/60Hz DC Resistance @ 25°C = Approx 1.7 Ohms		
Losses	Iron Losses	2.95 Watts approx	
	Copper Losses	39.0 Watts approx	
Temperature Class	Winding Wire (Primary & Secondary)	Class H (180°C)	
	Insulation between input and output	Class B (130°C)	
	Connection lead insulation	Class A (105°C)	
Standards	Approved to UL506 & UL5085 : File E215495 Approved to EN61558 : DEKRA Certificate 2161054.02 Conforms to EN60065, VDE0550, BS415.		
Physical Data	Approximate Dimensions	Diameter	136mm*
		Height	68mm
		* Measured away from leadout bulge; Allow extra 4mm at leads.	
	Approximate Weight	4.30 Kg	
Terminations	Primary	Solid copper conductors (extension of winding wire), insulated over their entire length with 105°C PVC tubing. Double-insulated over entire length with 105°C PVC tubing. 150mm Long, 10mm tinned ends.	
	Secondary	Solid copper conductors (extension of winding wire), insulated over their entire length with 105°C PVC tubing. 150mm Long, 10mm tinned ends.	
Mounting Hardware	Each transformer is supplied with a mounting kit, comprising:		
	Neoprene Insulating disc	2 pieces	
	Dished Steel Washer	1 piece	
	Bolt M8x80mm Slotted Pan-Head	1 piece	
	Washer M8 Plain	1 piece	
	Nut M8 Hex	1 piece	