

Proximity Sensors Capacitive Thermoplastic Polyester Housing Types CA30CAN/CAF.....

CARLO GAVAZZI



- 4TH Generation TRIPLESIELD™
- Adjustable sensing distance: 2 - 20 mm flush or 4-30 mm non-flush
- Protection: short-circuit, transients and reverse polarity
- Dust and humidity compensation
- Dust or temperature alarm output
- Rated operational voltage: 10-40 VDC
- Output: DC 200 mA, NPN or PNP
- Standard Output: NO and NC
- LED indications for power-supply, output and stability
- IP67, IP68, IP69K, Nema 1, 2, 4, 4X, 5, 6, 6P, 12
- Cable and M12 connector versions available




Product Description

The CA30CA.. capacitive proximity switches feature an improved 4TH generation *TRIPLESIELD™* technology. Furthermore, these sensors feature increased immunity to electromagnetic interference (EMI), especially to frequency drives. Not only does 4TH generation *TRIPLESIELD™* feature an increased EMI, but it also increases the immunity to humidity and dust. The implementation of stability indication eases the setup procedure, as both Stable ON and Stable OFF positions are indicated by

the green and yellow LEDs. The sensing distance is increased by 20 - 25 % allowing room for additional stable detection. The dust alarm function gives an early warning that the sensing surroundings have to be cleaned. The temperature alarm function raises an alarm if the sensing surface goes beyond 60 degree Celsius. The sensor housing is featuring IP69K as well as approval by ECOLAB for cleaning and disinfection agents.

Ordering Key

CA30CAN25NAM1



Type Selection



Housing diameter	Sensor type	Output type	Output function	Connection	Rated operating distance (S _n)	Ordering no. Standard	Ordering no. Dust alarm	Ordering no. Temperature alarm
M 30	Flush	NPN	NO+NC	Cable	0 - 16 mm	CA30CAF16NA		
M 30	Flush	NPN	NO+NC	M12 Plug	0 - 16 mm	CA30CAF16NAM1		
M 30	Flush	PNP	NO+NC	Cable	0 - 16 mm	CA30CAF16PA		
M 30	Flush	PNP	NO+NC	M12 Plug	0 - 16 mm	CA30CAF16PAM1		
M 30	Flush	PNP	NO	Cable	0 - 16 mm		CA30CAF16PODU ¹⁾	CA30CAF16POTA ¹⁾
M 30	Flush	PNP	NC	Cable	0 - 16 mm		CA30CAF16PCDU ¹⁾	CA30CAF16PCTA ¹⁾
M 30	Flush	PNP	NC	M12 Plug	0 - 16 mm		CA30CAF16PCM1DU ²⁾	
M 30	Non-Flush	NPN	NO+NC	Cable	0 - 25 mm	CA30CAN25NA		
M 30	Non-Flush	NPN	NO+NC	M12 Plug	0 - 25 mm	CA30CAN25NAM1		
M 30	Non-Flush	PNP	NO+NC	Cable	0 - 25 mm	CA30CAN25PA		
M 30	Non-Flush	PNP	NO+NC	M12 Plug	0 - 25 mm	CA30CAN25PAM1		
M 30	Non-Flush	PNP	NO	Cable	0 - 25 mm		CA30CAN25PODU ³⁾	CA30CAN25POTA ³⁾
M 30	Non-Flush	PNP	NC	Cable	0 - 25 mm		CA30CAN25PCDU ³⁾	CA30CAN25PCTA ³⁾

¹⁾ Replaced by CA30CAF16BPA2IO
²⁾ Replaced by CA30CAF16BPM1IO
³⁾ Replaced by CA30CAN25BPA2IO


Specifications EN 60947-5-2

Rated operating distance (S _n) Non-flush mounted sensor	0 - 25 mm (factory setting 25 mm), (ref. target 75x75 mm ST37, 1 mm thick, grounded)	Flush mounted sensor	0 - 16 mm (factory setting 16 mm - non-flush mounted) (ref. target 48x48 mm ST37, 1 mm thick, grounded)
--	--	----------------------	--

Specifications (cont.) EN 60947-5-2

Sensitivity control	Adjustable by potentiometer	Connection	
Electrical adjustment	11 turns	Cable	PVC, Ø5.2 x 2 m, 4 x 0.34 mm ²
Mechanical adjustment	16 turns		Oil proof, grey
Adjustable distance		Plug (M1)	M12 x 1 - 4 pin
Flush types	2 to 20 mm	Temperature alarm output	60°C ± 5°C
Non-flush types	4 to 30 mm	Response time examples T _A = 25°C	16 sec @ T _{EXC} = 800°C 390 sec @ T _{EXC} = 80°C
Effective operating dist. (S_r)	0.9 x S _n ≤ S _r ≤ 1.1 x S _n	TRIPLESHIELD™	
Usable operating dist. (S_u)	0.85 x S _r ≤ S _u ≤ 1.15 x S _r	Exceeding the norms for capacitive sensors	
Repeat accuracy (R)	≤ 5%	Electrostatic discharge (EN61000-4-2)	> 40 kV
Hysteresis (H)	3 - 20%	Contact discharge	> 40 kV
Rated operational volt. (U_B)	10 to 40 VDC (ripple incl.)	Air discharge	> 40 kV
Ripple	≤ 10%	Electrical fast transients/burst (EN 61000-4-4)	±4kV
Output function	NPN or PNP	Surge (EN 61000-4-5)	Power-supply > 2kV (with 500 Ω) Sensor output > 2kV (with 500 Ω)
Output switching function	N.O. and N.C.	Wire conducted disturbances (EN 61000-4-6)	> 20 Vrms
Rated operational current (I_a)	≤ 200 mA (continuous)	Power-frequency magnetic fields (EN 61000-4-8)	Continuous > 60 A/m, 75.9 μ tesla Short-time > 600 A/m, 759 μ tesla
Capacitive load	100 nF	Radiated RF electromagnetic fields (EN 61000-4-3)	> 20 V/m
No-load supply current (I_o)	≤ 12 mA	Shock (IEC 60068-2-32)	30 G / 11ms, 3 pos, 3 neg per axis
Voltage drop (U_d)	≤ 2.0 VDC @ 200 mA DC	Rough handling shocks (IEC 60068-2-31)	twice from 1 m 100 times from 0.5 m
Minimum operational current (I_m)	≥ 0.5 mA	Vibration (IEC 60068-2-6)	10 to 150 Hz, 1 mm / 15 G
OFF state current (I_r)	≤ 100 μA	Housing material	
Protection	Short-circuit, reverse polarity, transients	Body	PBT, grey, 30% glass reinforced
Frequency of operating cycles (f)	50 Hz	Cable gland	PA12, black
Response time OFF-ON (t_{on})	≤ 10 ms	Fingernuts	PA12, black
Response time ON-OFF (t_{off})	≤ 10 ms	Trimmershaft	Nylon
Power ON delay (t_v)	≤ 200 ms	Weight	
Indication		Cable version	190 g
Target detected	LED, yellow	Plug version	106 g
Power and detection stability	LED, green	Approvals	cULus (UL508), ECOLAB
Environment		CE-marking	Yes
Installation category	III (IEC 60664, 60664A; 60947-1)	MTTF_d	829 years @ 40°C (+104°F)
Degree of pollution	3 (IEC 60664, 60664A; 60947-1) 		
Degree of protection	IP 67, IP 68/60 min., IP69K* 		
NEMA type	1, 2, 4, 4X, 5, 6, 6P, 12		
Operating temperature	-30 to +85°C (-22 to +185°F)		
Max. temperature on sensing face	120°C (248°F)		
Storage temperature	-40 to +85°C (-40 to +185°F)		
Rated insulation voltage	1 kVAC (rms) IEC protection class III		
Tightening torque	≤ 7.5 Nm		

* The IP69K test according to DIN 40050-9 for high-pressure, high-temperature wash-down applications. The sensor must not only be dust tight (IP6X), but also able to withstand high-pressure and steam cleaning. The sensor is exposed to high-pressure water from a spray nozzle that is fed with 80°C water at 8'000-10'000 KPa (80-100bar) and a flow rate of 14-6L/min. The nozzle is held 100-150 mm from the sensor at angles of 0°, 30°, 60° and 90° for 30s each. The test device sits on a turntable that rotates with a speed of 5 times per minute. The sensor must not suffer any damaging effects from the high pressure water in appearance and function.



Adjustment Guide


The environments in which capacitive sensors are installed can often be unstable as regards temperature, humidity, object distance and industrial (noise) interference. This is why Carlo Gavazzi offers, as a stand-

ard feature in all TRIPLESHIELD™ capacitive sensors, a user-friendly sensitivity adjustment instead of a fixed sensing range. Likewise, these sensors provide an extended sensing range to accommodate mechanically


demanding areas and temperature stability to ensure high immunity to electromagnetic interference (EMI) and a minimum need for adjusting sensitivity if the temperature varies.

Note:
The sensors are factory set (default) to nominal sensing range S_n .


Wiring Diagram




Detection Diagram



Detection Stability Indication



Dimensions



Installation Hints





Capacitive sensors have a unique ability to detect almost any material in liquid or solid form. Capacitive sensors are able to detect metallic as well as non-metallic objects. However, their traditional use is for non-metallic materials such as:

- **Plastics Industry**
Resins, regrinds or mould-
ed products.
- **Chemical Industry**
Cleansers, fertilizers, liq-
uid soaps, corrosives and
petrochemicals.
- **Wood Industry**
Saw dust, paper products,
door and window frames.
- **Ceramics & Glass
Industry**
Raw materials, clay or
finished products, bottles.

- **Packaging Industry**
Package inspection for lev-
el or contents, dry goods,
fruits and vegetables, dairy
products.

Materials are detected due to their dielectric constant. The bigger the size of an object, the higher the density of material, the better or easier it is to detect the object.

The nominal sensing distance for a capacitive sensor is referred to a grounded metal plate (ST37). For additional information regarding dielectric ratings of materials please refer to Technical Information.

<p><i>To avoid interference from inductive voltage/current peaks, separate the prox. switch power cables from any other power cables, e.g. motor, contactor or solenoid cables</i></p> 	<p><i>Relief of cable strain</i></p>  <p>Not correct</p> <p>Correct</p> <p>The cable should not be pulled</p>	<p><i>Protection of the sensing face</i></p>  <p>A proximity switch should not serve as mechanical stop</p>	<p><i>Switch mounted on mobile carrier</i></p>  <p>Any repetitive flexing of the cable should be avoided</p>
---	--	---	---

Delivery Contents

- Capacitive switch: CA30CAN/CAF.....
- User manual
- 2 x M30 fingernuts
- Screwdriver
- **Packaging:** Cardboard box

Accessories

- Connector type CONB14NF-... -series.
- Mounting Brackets AMB30-S.. (straight), AMB30-A.. (angled)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Carlo Gavazzi:](#)

[CA30CAN25NA](#) [CA30CAF16PAM1](#) [CA30CAN25PA](#) [CA30CAF16NAM1](#) [CA30CAF16NA](#) [CA30CAF16PA](#)
[CA30CAN25NAM1](#) [CA30CAN25PAM1](#)