


## FineAdjust Applicator Specification Sheet Order No. 63901-9500






- Quick punch removal with the push of a button for fast and easy tooling change
- Applicator designed to industry standard mounting and shut height 135.80mm (5.346")
- Quick set-up time; plus the crimp height, track and feed adjustments can be set without removing the applicator from the press
- Fine adjustment allows users to achieve target with little effort by adjusting in increments of .015mm (.0006") for conductor crimp height and .063mm (.0025") for insulation height
- Independent adjustment rings allow users to quickly adjust the conductor or insulation crimp height without affecting each other

#### SCOPE

Products: 3.7 LED Connector Plug Crimp Terminal, 26-28 AWG.

Terminal	Terminal	Wire Size			Insulation	Strip Length				
Series No.	Order No.			IPC/WHMA-A620+		Termin	nal <b>++</b>			
Series NO.	Order NO.	AWG	mm²	mm	ln.	mm	ln.	mm	In.	
503485	503485-0000	26-28	.141079	0.93-1.14	.037045	0.93-1.14	.037045	1.30-1.50	.051059	
	<ul> <li>To achieve optimum IPC-A620 insulation crimps, use this insulation OD range.</li> <li>Overall insulation OD specification for terminal.</li> </ul>									

#### **DEFINITION OF TERMS**



The above terminal drawing is a generic terminal representation. It is not an image of a terminal listed in the scope.

Release Date: 05-25-10 Revision Date: 06-07-10 **UNCONTROLLED COPY** 

#### **CRIMP SPECIFICATION**

Terminal Series No.	Bell n	nouth	Cut-off Tab	o Maximum	Conductor Brush		
Terminal Series NO.	Mm	In.	mm	In.	mm	In.	
503485	0.10-0.30	.004012	0.15	.006	0.10-0.40	.004016	

	Bend up Bend down				Punch Width mm (Ref)			(Ref)	Seam	
<b>Terminal Series No.</b>					Conductor		Insulation		Seam shall not be open	
	Deg	ree	Deg	ree	mm	In	mm	In	and no wire allowed out	
503485	3	3	3	6	0.80	.031	1.30	.051	of the crimping area	

After crimping, the conductor profile should measure the following.


Terminal	Wire Size			Pull Force				
Series No.	AWG	mm <sup>2</sup>	Crimp	Height	Crimp Wi	Minimum		
Series NO.	AWG	111111-	mm	In.	mm	In.	N	Lb.
503485	26	0.14	0.56-0.61	.022024	0.85	.033	9.80	2.20
000-00	28	0.08	0.53-0.58	.021023	0.85	.033	9.80	2.20

	Wire	Size	Insulation				
Terminal Ordr No.	AWG	mm²	Crimp	Height	Crimp Width (Ref.)		
			mm	In.	mm	In.	
503485	26	0.14	1.30-1.50	.051059	1.35	.053	
303403	28	0.08	1.30-1.50	.051059	1.35	.053	

Pull Force should be measured with no influence from the insulation crimp. The above specifications are guidelines to an optimum crimp.

### PARTS LIST

FineAdjust Applicator 63901-9500									
ltem	Order No Engineering No. Description								
	•	Perish	nable Tooling						
	63901-9570	63901-9570	Tool Kit (All "Y" Items)	REF					
1	63457-0072	63457-0072	Conductor Punch	1 Y					
2	63455-0099	63455-0099	Conductor Anvil	1 Y					
3	63454-0119	63454-0119	Insulation Punch	1 Y					
4	63456-0082	63456-0082	Insulation Anvil	1 Y					
5	63443-0005	63443-0005	Cut-Off Plunger	1 Y					
6	63443-0012	63443-0012	Front Plunger Retainer	1 Y					
		Other	Components						
7	11-18-4083	60707-8	Feed Guide	1					
8	11-24-1067	4996-4	Cut-Off Plunger Spring	1					
9	63443-0009	63443-0009	Front Scrap Chute	1					
10	63443-0024	63443-0024	Key	1					
11	63443-0090	63443-0090	Wire Stop	1					
12	63443-2201	63443-2201	1.00mm Coarse Spacer	1					
13	63443-2216	63443-2216	16.00mm Coarse Spacer	1					
14	63443-2312	63443-2312	3.60mm Fine Spacer	1					
15	63443-2805	63443-2805	Front Plunger Striker	1					
16	63443-2905	63443-2905	Wire Hold Down Plunger	1					
17	63443-6109	63443-6109	Rear Cover	1					
18	63600-0021	63600-0021	Compression Spring	1					
19	63890-0093	63890-0093	Height Spacer	1					
	•		Frame						
20	63800-4901	63800-4901	Тор	1					
21	63801-3281	63801-3281	Base	1					
22	63801-4650	63801-4650	Track	1					
		Н	ardware						
23	N/A	N/A	M3 by 6 Long SHCS	2**					
24	N/A	N/A	M3 by 6 Long FHCS	1**					
25	N/A	N/A	M4 by 6 Long SHCS	2**					
26	N/A	N/A	M4 by 12 Long BHCS	2**					
27	N/A	N/A	M4 by 50 Long SHCS	2**					
28	N/A	N/A	M5 by 12 Long SHCS	1**					
29	N/A	N/A	#10-32 by 3/8"Long Flat Point SSS	1**					
30	N/A	N/A	#10-32 Hex Jam Nut	1**					
**	** Available from an industrial supply company such as MSC (1-800-645-7270).								



#### NOTES

- 1. Molex recommends an extra perishable tooling kit be maintained at your facility.
- 2. Verify tooling alignment by manually cycling the press and Applicator before crimping under power. Check that all screws are tight.
- 3. Slugs, Terminals, Dirt and Oil should be kept clear of work area.
- 4. Wear safety glasses at all times.
- 5. For recommended maintenance refer to the FineAdjust Manual.

**CAUTION**: This applicator should only be used in a press with a shut height of 135.8mm (5.346"). Tooling damage could result at a lower setting.

**CAUTION**: To prevent injury never operate this Applicator without the guards supplied with the press or wire-processing machine in place. Reference the press or wire processing manufacturer's instruction manual.

**CAUTION**: Molex crimp specifications are valid only when used with Molex terminals, applicators and tooling.

http://www.molex.com

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex: 63901-9570