

# **Product Specifications**

3M<sup>™</sup> Low-Profile Headers Series 25XX

78-5102-0002-1 Rev D

Released: 02-24-21

#### **Table of Contents**

Secti	on	Page
1.	Scope	3
2.	3M Customer Documents	3
3.	Performance and Test Descriptions	3
4.	Requirements Overview	3
5.	Test Results Summary	4
6.	Test Sequences	4
7.	Figures	5
8.	Agency Listings	6

Important Notice	7

Steven A. Neu: Approved: 07-24-12 Sandra J. Stuckert: Approved 07-24-12 Jim W. Wessman: Approved 07-24-12

#### 1. Scope

This document summarizes test methods, test conditions and product performance requirements for the 3M<sup>™</sup> Low Profile Headers. Listings of materials, finishes, test conditions, and test standards are included in this specification. In the event of conflict between this specification and any documents listed below, the listed documentation supersedes this specification.

#### 2. 3M Customer Documents

78-5100-0770-7 TS-0770, Technical Data Sheet for 25XX Series Four-Wall Header 78-9100-7795-3 Instruction Sheet for 3M<sup>™</sup> Polarizing Key 3518

#### 3. Performance and Test Description

Unless otherwise specified, all tests shall be mated to 3M Wiremount Sockets 3425, .100 pitch with 3M Cable 3365 at ambient environmental conditions per EIA-364. Unless otherwise specified, all values and limits are typical of those obtained by qualification testing of the subject product. All specifications are subject to revision and change without notice from 3M.

#### 4. Requirements Overview

#### 4.1 Ratings

Dielectric withstanding voltage: 1000 V<sub>RMS</sub> @ Sea Level

Temperature: -65°C to +105°C

Insulation resistance: >1  $x10^{9}\Omega$  at 500 V<sub>DC</sub>

Current: (EIA-364-070 method 2, 30°C maximum temperature rise.)

- 1.75 Amperes, All contacts powered
- 3.00 Amperes, 6 contacts powered

5.00 Amperes, 1 contact powered

#### 4.2 Materials Header

Insulation: Glass Filled PCT

Latch Insulation: Nylon

Cover Clip: Stainless Steel with Gray Polyurethane Coating Pin Contact: Copper Alloy

-----

#### 4.3 Finishes

Plating:

TS-0770 25XX Series Four-Wall Header

Nickel: 50-150 µ inches, ASTM B689-97, SAE AMS-QQ-N-290

- Gold: 30  $\mu$  inches, MIL-G-45204 Type II, Grade C, ASTM B488-01
- Sn: 200-300 µ" Matte Tin
- D25XX Series Four-Wall Header
- Nickel: 50 150  $\mu$  inches, ASTM B689-97, SAE AMS-QQ-N-290
- Gold: 10 µ inches, MIL-G-45204 Type II, Grade C, ASTM B488-01
- Sn: 40-120 µ" Matte Tin

#### 4.5 Regulatory Compliance

See the Regulatory Information Appendix (RIA) in the "RoHS compliance" section of **www.3Mconnector.com** for compliance information. See customer drawings for regulatory specifics on each connector.

### 5.0 Test Results Summary

#### 5.1 General

#### 5.2 Environmental

Items		Specification	Test Method	
Environmental		<ul> <li>50 Insertions/Withdrawals</li> </ul>	EIA-364-09	
	Durability (30µ" Au)	•Max. ΔR: <10 mΩ		
		<ul> <li>10 Insertions/Withdrawals</li> </ul>	EIA-364-09	
	Durability (10µ" Au)	•Max. ΔR: <10 mΩ		
		<ul> <li>No physical abnormalitities after test</li> </ul>	EIA-364-26	
	Salt Spray	•Max. ΔR: <10 mΩ		
	Thermal Shock	<ul> <li>No physical abnormalitities after test</li> </ul>	EIA-364-32, Table 2, Condition II, -65	
		•Max. ΔR: <10 mΩ	to +105 °C, 5 Cycles	
	Temperature Life	<ul> <li>No physical abnormalitities after test</li> </ul>	EIA-364-17, Method A, Condition 3D,	
	(Thermal Aging)	•Max. ΔR: <10 mΩ	105 °C, 1000 hours	
	Humidity	Max. ΔR: <10 mΩ	EIA-364-31, Method IV, 25-65 °C, -10 °C subcycle, 80-100%RH, 10 cycles	

#### 5.3 Mechanical

Items		Specification	Test Method	
		No physical abnormalitities after test	EIA-364-28, Method V, Condition A,	
		• Max. ΔR: <10 mΩ	Table II	
		<ul> <li>No electrical discontinuity &gt; 10 n sec</li> </ul>		
	Mechanical Shock	<ul> <li>No physical abnormalitities after test</li> </ul>	EIA-364-27, Test Condition A,	
		•Max. ΔR: <10 mΩ	Table 1	
		<ul> <li>No electrical discontinuity &gt; 10 n sec</li> </ul>		
	Contact Retention	3.5 lb. min	EIA-364-29	

#### 5.4 Electrical

Items		Specification	Test Method
Electrical	Low Level Contact Resistance	Max. ΔR: <10 mΩ	EIA-364-23
	Dielectric Withstanding Voltage	1000 Vrms @ Sea Level, 1 min	EIA-364-20
	Insulation Resistance	1 x 10 <sup>9</sup> @ 500 V <sub>dc</sub>	EIA-364-21
	Current Rating	1.75 Amp, All Lines Powered 3.00 Amp, 6 Lines Powered 5.00 Amp, 1 Line Powered	EIA-364-70A, Method 2, 30°C Temperature Rise Limit.

#### 5.4 Physical

Items		Specification	Test Method	
Physical	Visual	No defects such as deformation, blister, damage, crack, etc.	EIA-364-18	
	Nickel Underplating Thickness Gold Thickness Matte Tin Thickness	50-150 µ" 30 µ" 10 µ" 200-300µ"	EIA-364-48, C Average of random measurements from any 3 lots	
	Solderability	>95% Coverage of solderable area	EIA-364-52	

#### 6.0 Test Sequence


6.1 Sequenced Tests	TEST FLOW			
Test	Sequence Numbers for Test Group			
	Α	В	С	D
Visual			1	1
Low Level Connection Resistance (LLCR)	1,3,5,7	1,3	2,4,6	2,4,6
Vibration			3	
Physical Shock			5	
Durability (with Environmental)	2			3
Temperature Life (Thermal Aging)		2		
Humidity	6			
Thermal Shock	4			
Salt Spray				5


#### 6.2 Independent Tests


- 1. Plating Thicknesses
- 2. Header Solderability
- 3. Header Pin Retention
- 4. Dielectric Withstanding Voltage
- Current Rating
   Insulation Resistance
- o. msulation K

#### 7.0 Figures

7.1 Temperature vs. Current







8. Agency Listings 8.1 Underwriters Laboratories (UL)

Agency	File No.
UL	E68080
CUL	E68080

#### 3M is a trademark of 3M Company.

#### **Important Notice**

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

#### Warranty; Limited Remedy; Limited Liability

Regulatory: For regulatory information about this product, contact your 3M representative.

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

**Product Use**: Many factors beyond 3M's control and uniquely within user's control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OR TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

© 3M 2021. All rights reserved.

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## **3M**:

 N3518
 N2526-5003-RB
 N2536-5002-RB
 N2514-6V0C-RB-WD
 N2520-6V0C-RB-WE
 N2524-6V0C-RB-WE
 N2530-6V0C-RB-WE
 N2530-6002-AR
 N2530-6002-AR
 D2530-6002-AR
 D2540-5002-AR
 D2508-6002-AR
 D2508-6002-AR
 D2508-6002-AR
 D2508-6002-AR
 D2508-6002-AR
 D2508-6002-AR