

LINEA light

5925UAP075L51-10 RAL7001

EAN 4031582357684

Swivel castor with wheel brake, housing made of Polyamide, with blind hole for furniture fittings.

Wheel centre made of Polyamide, Tread: Polyurethane, precision ball bearing

Technical Data	
Wheel diameter	75 mm
Width of Tread	15 mm
Castor width	55 mm
Centre hole	10 mm
Dome-Ø	30 mm
Offset	23 mm
Swivel Interference	162 mm
Overall height	75.5 mm
Temperature	- 10 / + 40 °C
Standard	EN 12528
Weight	0.196 kg
Swivel Radius	81 mm
Load capacity	100 kg
Load capacity (static)	200 kg



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

Product Information



LINEA light

5925UAP075L51-10 RAL7001

EAN 4031582357684

