

HALF SIZE DIP LOW VOLTAGE 3.3VHCMOS/TTL COMPATIBLE CRYSTAL CLOCK OSCILLATOR



13.2 x 13.2 x 5.5mm

ACHL Series

Moisture Sensitivity Level (MSL) – This product is Hermetically Sealed and not Moisture Sensitive - MSL = N/A: Not Applicable



RoHS
Compliant

FEATURES:

- Tri-state Enable/Disable option
- Low supply voltage 3.3V
- HCMOS and TTL compatible
- Tight symmetry option 50% +/-5%

APPLICATIONS:

- Clock signal sources for digital chips and microprocessors
- Low power applications

STANDARD SPECIFICATIONS:


Parameters		Minimum	Typical	Maximum	Units	Notes
Frequency Range		0.400	-----	160.000	MHz	
Operating Temperature		0	-----	+70	°C	See options
Storage Temperature		-55	-----	+125	°C	
Overall Frequency Stability		-100	-----	+100	ppm	See options
Supply Voltage (Vdd)		2.97	3.3	3.63	V	
Input Current	0.400MHz ~ 24.999MHz	-----	-----	20	mA	
	25.000MHz ~ 99.999MHz	-----	-----	40		
	100.000MHz ~ 16000MHz	-----	-----	80		
Symmetry (@ 1/2Vdd)		40	50	60	%	See options
Rise and Fall Time (Tr/Tf)	0.400MHz ~ 24.999MHz	-----	-----	10	ns	
	25.000MHz ~ 99.999MHz	-----	-----	5		
	100.000MHz ~ 16000MHz	-----	-----	4		
Output Load		-----	-----	15	pF	See options
		-----	-----	5	TTL	
Output Voltage	VOH	0.9*Vdd	-----	-----	V	
	VOL	-----	-----	0.1*Vdd	V	
Tri-state Function	VIH	2.2	-----	-----	V	"1" or Open: Oscillation "0": Output disable (Hi Z)
	VIL	-----	-----	0.8	V	
Output Enable time		-----	-----	4	ms	For option A only
Output Disable time		-----	-----	100	ns	For option A only
Start-up Time		-----	1	10	ms	
Phase Jitter RMS (12~20MHz)		-----	-----	1	ps	Reference only. Please contact Abracon for specific frequencies
Aging		-5.0	-----	+5.0	ppm	@+25°C First year

* Overall frequency stability includes initial tolerance, temperature stability, and aging.

OPTIONS & PART IDENTIFICATION:

(Left blank if standard)

ACHL - [] MHz - [] - [] - [] - []



(*) Temp option I, D, E and 0°C ~ +70°C only.



2 Faraday, Suite# B | Irvine | CA 92618 **Revised: 01.20.16**
Ph. 949.546.8000 | Fax. 949.546.8001
Visit www.abracon.com for Terms and Conditions of Sale

HALF SIZE DIP LOW VOLTAGE 3.3VHCMOS/TTL COMPATIBLE CRYSTAL CLOCK OSCILLATOR

ACHL Series





RoHS
Compliant



13.2 x 13.2 x 5.5mm

OUTLINE DIMENSIONS:



Pin	Function
1	Tri-State/NC
4	GND
5	Output
8	Vdd

Note: Recommend using an approximately 0.01uF bypass capacitor between PIN 2 and 4.

Dimensions: inches (mm)

Packaging

40pcs /tube

ATTENTION Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS
ISO9001:2008
CERTIFIED



2 Faraday, Suite# B | Irvine | CA 92618 **Revised: 01.20.16**

Ph. 949.546.8000 | Fax. 949.546.8001

Visit www.abracon.com for Terms and Conditions of Sale

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[ACHL-14.31818MHZ-EK](#) [ACHL-24.576MHZ-EK](#) [ACHL-12.000MHZ-EK](#) [ACHL-48.000MHZ-EK](#) [ACHL-48.000MHZ-ER](#)
[ACHL-25.000MHZ-EK](#) [ACHL-16.000MHZ-EK](#) [ACHL-11.0592MHZ-EK](#) [ACHL-50.000MHZ-EK](#) [ACHL-8.000MHZ-EK](#)
[ACHL-44.736MHZ-ER](#) [ACHL-4.000MHZ-EK](#) [ACHL-27.000MHZ-EK](#) [ACHL-10.000MHZ-EK](#) [ACHL-18.432MHZ-EK](#)
[ACHL-34.368MHZ-ER](#) [ACHL-32.000MHZ-EK](#) [ACHL-40.000MHZ-EK](#) [ACHL-20.000MHZ-EK](#) [ACHL-32.768MHZ-EK](#)
[ACHL-3.6864MHZ-EK](#) [ACHL-83.000MHZ-C-S](#) [ACHL-66.000MHZ-C-S](#) [ACHL-128.0000MHZ-E-C-S-A](#) [ACHL-](#)
[48.000MHZ-EK-G](#) [ACHL-66.000MHZ-EK](#)