




Features:

- High efficiency, Low VF
- High current capability
- High reliability
- High surge current capability
- Low power loss



1 Amperes Silicon Rectifiers

DO - 41



Mechanical Data

Case	: Moulded plastic
Epoxy	: UL 94V-0 rate flame retardant
Polarity	: Colour band denotes cathode
High temperature soldering guaranteed	: 260°C / 10 s / 0.375 Inches, (9.5 mm) lead lengths at 5 lbs, (2.3 kg) tension
Weight	: 0.35 g

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified

Single phase, half wave, 60 Hz, resistive or inductive load

For capacitive load, derate current by 20%

Type Number	Symbol	1N 4001	1N 4002	1N 4003	1N 4004	1N 4005	1N 4006	1N 4007	Unit
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	50	100	200	400	600	800	1,000	V
Maximum RMS Voltage	V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V_{DC}	50	100	200	400	600	800	1,000	V
Maximum Average Forward Rectified Current 0.375 Inches (9.5 mm) Lead Length at $T_A = 75^\circ\text{C}$	$I_F (AV)$	1							A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load	I_{FSM}	30							A
Rating for Fusing ($t < 8.3$ ms)	I^2T	3.7							A ² S
Maximum Instantaneous Forward Voltage (Note 1) at 1 A	V_F	1							V
Maximum Reverse Current at Rated VR $T_A = 25^\circ\text{C}$ $T_A = 125^\circ\text{C}$	I_R	5 50							μA
Maximum Full load Reverse Current, Full cycle Average 0.375 Inches (9.5 mm) Lead Length at $T_A = 75^\circ\text{C}$	$I_R (AV)$	30							μA
Typical Junction Capacitance (Note 2)	C_j	10							pF
Typical Thermal Resistance	$R_{\theta JA}$ $R_{\theta JC}$ $R_{\theta JL}$	65 6 15							$^\circ\text{C/W}$
Operating Temperature Range	T_J	-65 to +150							$^\circ\text{C}$
Storage Temperature Range	T_{STG}	-65 to +150							$^\circ\text{C}$

Notes : 1. Pulse Test with PW = 300 usec, 1% Duty Cycle

2. Measured at 1 MHz and Applied Reverse Voltage of 4 V D.C.

Rating and Characteristic Curves

Figure 1. Maximum Forward Current Derating Curve






Figure 2. Maximum Non-Repetitive Forward Surge Current




Rating and Characteristic Curves


Typical Forward Characteristics



Typical Reverse Characteristics



Typical Junction Capacitance



Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.