

guided drive DFM-25-80-P-A-GF



Part number: 170852

★ Core product range

FESTO

With integrated guide.

The proximity switch, type SMTSO-8E, can be used with this product with stroke lengths equal to or greater than 50 mm. The corresponding mounting kit, type SMB-8E, is mounted inwardly or outwardly.



Data sheet

| Feature | Value |
|---|---|
| Centre of gravity distance from working load to yoke plate | 50 mm |
| Stroke | 80 mm |
| Piston diameter | 25 mm |
| Operating mode of drive unit | Yoke |
| Cushioning | P: Flexible cushioning rings/plates at both ends |
| Assembly position | Any |
| Guide | Plain-bearing guide |
| Design structure | Guide |
| Position detection | For proximity sensor |
| Operating pressure | 1.5 ... 10 bar |
| Max. speed | 0.8 m/s |
| Mode of operation | double-acting |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| Ambient temperature | -20 ... 80 °C |
| Impact energy in end positions | 0.3 Nm |
| Max. permissible torque load M _x as a function of the stroke | 3.2 Nm |
| Max. useful load as a function of the stroke at defined distance x _s | 96 N |
| Theoretical force at 6 bar, return stroke | 247 N |
| Theoretical force at 6 bar, advance stroke | 295 N |
| Moving mass | 904 g |
| Product weight | 1,993 g |
| alternative connections | See product drawing |
| Pneumatic connection | G1/8 |
| Materials note | Conforms to RoHS |
| Material cover | Wrought Aluminium alloy |
| Material seals | NBR |
| Material housing | Wrought Aluminium alloy |
| Material piston rod | High alloy steel, non-corrosive |