



PE13SD03M4Q

Ultra Low Capacitance ESD PROTECTION

Voltage

3.3 V




Features

- IEC61000-4-2(ESD) : $\pm 15\text{kV}$ Air, $\pm 14\text{kV}$ Contact
- IEC61000-4-4(EFT) : 40A(5/50ns)
- IEC61000-4-5(Lightning) : 6A(8/20uS)
- Low leakage current, maximum of 1uA at rated voltage
- Ultra low clamping voltage
- Lead free in compliance with EU RoHS 2.0
- Green molding compound as per IEC 61249 standard

Mechanical Data

- Case : DFN2510A-10L Package
- Terminals : Solderable per MIL-STD-750, Method 2026
- Approx. Weight : 0.003 grams

DFN2510A-10L



Maximum Ratings and Thermal Characteristics (T_A = 25°C unless otherwise noted)

PARAMETER	SYMBOL	LIMIT	UNITS
ESD IEC61000-4-2(Air)	V _{ESD}	± 15	kV
ESD IEC61000-4-2(Contact)		± 14	
Operating Junction Temperature Range	T _J	-55~85	°C
Storage Temperature Range	T _{STG}	-55~150	°C



PE13SD03M4Q

Electrical Characteristics (T_A = 25°C unless otherwise noted)

PARAMETER	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNITS
Reverse Stand-Off Voltage ^(Note 1)	V _{RWM}	-	-	-	3.3	V
Reverse Breakdown Voltage	V _{BR}	I _{BR} = 1 mA	5.5	-	16	V
Forward Voltage	V _F	I _F = 15mA, I/O Pin to GND	-	1	-	V
Reverse Leakage Current	I _R	V _R = 3.3 V, I/O Pin to GND	-	-	1	μA
Clamping Voltage	V _{CL}	I _{PP} = 5 A, t _P = 8/20 μs, I/O Pin to GND	-	3.3	-	V
Clamping Voltage TLP ^(Note 2)	V _{CL}	I _{PP} = 8 A, t _P = 100 ns, I/O Pin to GND	-	3.9	-	V
		I _{PP} = 16 A, t _P = 100 ns, I/O Pin to GND	-	5.5	-	
Dynamic Resistance	R _{DYN}	t _P = 100 ns	-	0.2	-	Ω
Off State Junction Capacitance ^(Note 3)	C _J	1.65Vdc Bias, f = 1 MHz, I/O Pins to GND	-	0.27	0.32	pF
		1.65Vdc Bias, f = 1 MHz, Between I/O Pins	-	0.05	0.1	

NOTES :

1. A transient suppressor is selected according to the working peak reverse voltage(V_{RWM}), which should be equal to or greater than the DC or continuous peak operation voltage level.
2. Testing using Transmission Line Pulse (TLP) conditions: Z₀ = 50 Ω, t_P = 100 ns.
3. This parameter is guaranteed by design.
4. This snap-back behavior strongly reduces the clamping voltage to the system behind the ESD protection during an ESD event. Do not connect unlimited DC current sources to the data lines to avoid the ESD protection device maintain in snap-back state after exceeding breakdown voltage



PE13SD03M4Q

TYPICAL CHARACTERISTIC CURVES




Fig.1 Typical Peak Clamping Voltage




Fig.2 Pulse Waveform




Fig.3 Typical Junction Capacitance




Fig.4 TLP Measurement




Fig.5 Insertion Loss



Fig.6 10Gb/s USB3.2 Gen2x1 Eye Diagram





PE13SD03M4Q

Part No. Packing Code Version

Part No.	Package Type	Packing Type	Marking	Version
PE13SD03M4Q	DFN2510A-10L	3K pcs / 7" reel	3D3	Halogen free RoHS compliant

Packaging Information & Mounting Pad Layout





PE13SD03M4Q

Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panjit:

[PE13SD03M4Q_R1_00201](#)