



**Product:** [9913](#)

50 Ohm Wireless Transmission Coax, RG-8, 10 AWG Solid BC, Foil + 90% TC Braid, PVC Jkt

**Product Description**

50 Ohm Wireless Transmission Coax, RG-8, 10 AWG Solid Bare Copper Conductor , PE Insulation, Foil + 90% Tinned Copper Braid Shield, PVC Jacket

**Technical Specifications**

**Product Overview**

Suitable Applications:	Point-to-point and point-to-multipoint wireless antenna communication; Wireless microphones, Two-Way Radios, Amateur (Ham) Radio, Low Power FM, GPS, RFID (Radio Frequency Identification)
------------------------	--

**Construction Details**

RG Type:	8
----------	---

**Conductor**

Size	Stranding	Nom. Diameter	Material
10 AWG	Solid	0.108 in	BC - Bare Copper

**Insulation**

Material	Nom. Insulation Diameter	Notes
PE - Polyethylene (Semi-Solid)	0.285 in (7.24 mm)	Solid PE monofilament spiral around conductor. Solid PE tube over monofilament

**Outer Shield**

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duobond® II	100%
2	Braid	Tinned Copper (TC)		90%

**Outer Jacket**

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.405 in (10.3 mm)

Overall Cable Diameter (Nominal):	0.405 in (10.3 mm)
-----------------------------------	--------------------

**Electrical Characteristics**

**Attenuation**

Frequency	Nom. Attenuation
5 MHz	0.4 dB/100ft
10 MHz	0.5 dB/100ft
50 MHz	1.0 dB/100ft
100 MHz	1.4 dB/100ft
200 MHz	1.8 dB/100ft
400 MHz	2.6 dB/100ft
700 MHz	3.6 dB/100ft
900 MHz	4.1 dB/100ft
1000 MHz	4.4 dB/100ft

**Power Rating**

Frequency	Max. Power Rating
-----------	-------------------

5 MHz	4,021 W
10 MHz	3,217 W
50 MHz	1,609 W
100 MHz	1,149 W
200 MHz	894 W
400 MHz	619 W
700 MHz	447 W
900 MHz	393 W
1,000 MHz	366 W

#### Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
0.9 Ohm/1000ft (3.0 Ohm/km)	1.8 Ohm/1000ft (5.9 Ohm/km)	24.6 pF/ft (80.7 pF/m)	50 Ohm	84%

#### Voltage

Voltage Rating
300 V

## Mechanical Characteristics

#### Temperature

Operating
-30°C to +75°C

#### Bend Radius

Installation Min.
4.0 in

Max. Pull Tension:	184 lbs (83.5 kg)
Bulk Cable Weight:	89 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Sustainability:	CA Prop 65
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	89913

## Product Notes

Notes:	Recommend use of 7810R, 7810A, 9913F7, or 9914 for applications above 1 GHz.
--------	--

## History

Update and Revision:	Revision Number: 0.367 Revision Date: 04-08-2022
----------------------	--

## Part Numbers

#### Variants

Item #	Color	Putup Type	Length	UPC
9913 010100	Black	Reel	100 ft	612825261636
9913 010250	Black	Reel	250 ft	612825261650
9913 010500	Black	Reel	500 ft	612825261667
9913 0101000	Black	Reel	1,000 ft	612825261643
9913 0105000	Black	Reel	5,000 ft	612825261711

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

