

Operation Instructions of Controller

I. Specifications:

Working temperature: -20-60°C

Product size: L62xW35xH23mm

Net weight: 50g

Output: Three CMOS drain-open output

Max load current: 2 A each color

Supply voltage: DC12V

Package size: L105xW65xH55mm

Gross weight: 70g


Connecting Mode: Common anode

II. Control Method:

Adopt IR remoter to control the led controller, which has 24 buttons, the function of each button as the table below:

Brightness+ (Speed up)	Brightness- (Speed down)	Off	On
Static red	Static green	Static blue	Static white
Static orange	Static pea green	Static dark blue	3color jumpy change
Static dark yellow	Static cyan	Static brown	All fade out & fade in
Static yellow	Static light blue	Static pink	7 color fade change
Static straw yellow	Static sky blue	Static purple	3 base color jumpy

III. Panel specification and connecting drawing as follows:



IV. Warning:

1. Supply voltage of this product is DC12V never connect to DC24V or AC220V.
2. Never connect two wires directly in case of short circuit.
3. Lead wire should be connected correctly according to colors that connecting diagram offers.
4. Warranty of this product is one year, in this period We guarantee replacement or repairing with no charge, but exclude the artificial situation of damaged or overload working.