

# RS PRO Pressure Transmitter

RS Stock No.: 2547413

## FEATURES

Pressure range: 0~160bar

Pressure type: Gauge

Electrical connection: Angular DIN175301-803A

Accuracy:  $\pm 0.5\%$ FS

Process connection: G1/2B EN 837

Medium: Air, water, mixed oil or other fluids that can be compatible with wetted parts



### Electrical Specifications

<b>Power supply</b>	<b>8V~30V DC</b>
<b>Output signal</b>	4mA~20mA
<b>Load resistor (<math>\Omega</math>)</b>	$\leq$ (power supply-8V) /0.02A
<b>Total current consumption</b>	$\leq$ 23mA
<b>Reverse polarity protection</b>	$\leq$ 20M $\Omega$ (500V DC)

### Mechanical Specifications

<b>Structure</b>	<b>Full welded,molecular sieve</b>
<b>Housing material</b>	Stainless steel 316L, Nylon
<b>Wetted parts</b>	Stainless steel 316L
<b>Weight</b>	$\leq$ 135g

### Accuracy

<b>Accuracy</b>	<b><math>\pm 0.5\%FS</math></b>
<b>Total error band</b>	0~50 $^{\circ}C$ $\pm 0.75\%FS(max.)$
	-10 $^{\circ}C$ ~80 $^{\circ}C$ $\pm 1.15\%FS(max.)$

### Environmental Conditions

<b>Medium temperature</b>	<b>-30<math>^{\circ}C</math>~85<math>^{\circ}C</math></b>
<b>Environment temperature</b>	-30 $^{\circ}C$ ~85 $^{\circ}C$
<b>Storage temperature</b>	-40 $^{\circ}C$ ~100 $^{\circ}C$

### Operation Conditions

<b>Atmospheric pressure</b>	<b>86kPa~106kPa</b>
<b>Vibration environment</b>	10g (@10Hz~2000Hz)
<b>Shock resistance</b>	100g/11ms
<b>Service life</b>	> 10 million times load cycle(within measuring range)
<b>Position effect</b>	$\leq \pm 0.1\%FS$
<b>Installation direction</b>	Pressure port should be vertically downward

### Protection Category




**IP Rating** IP65

### Approvals

# Pressure Transmitter

Compliance/Certifications CE,RoHS,REACH,UL

## Dimension and Wiring



Current Output Mode(Load Resistor Range)

Pin	Definition
1	V+
2	V-
3	Null
⊥	Grounding