Click here to ask about the production status of specific part numbers.

#### DG1206/DG1207

#### **General Description**

The DG1206 and DG1207 are low-leakage, low-chargeinjection single 16-channel or dual 8-channel multiplexing switch devices. The DG1206 uses four selection inputs A3, A2, A1, and A0 to determine the switching logic; the DG1207 uses three selection inputs A2, A1, and A0. On both devices, an enable (EN) input is used to enable or disable the device.

The ultra-low capacitance and low-charge injection of the DG1206/DG1207 make them ideal for automatic test equipment systems, data acquisition systems, and sample-and-hold systems where low glitch and fast settling time are required.

The DG1206/DG1207 are available in 5mm x 5mm 32-lead TQFN or 28-lead TSSOP packages. The devices are specified for operation over the  $-40^{\circ}$ C to  $+85^{\circ}$ C temperature range.

#### **Applications**

- Automatic Test Equipment Systems
- Data Acquisition Systems
- Sample-and-Hold Systems
- Communication Systems
- Audio and Video Routing

### Low-Leakage, Single 16-Channel and Dual 8-Channel, Analog Multiplexer

#### **Benefits and Features**


- Distortion-Free Measurement
  - $100\Omega$  (typ) On Resistance
  - ≤ 2nA (max) On/Off-Leakage Current for DG1206
  - ≤ 1nA (max) On/Off-Leakage Current for DG1207
  - ≤ 0.5pC (typ) Charge Injection
- Wide Supply Range with Low Supply Current
  - 40µA (typ) Quiescent Current at Room Temperature
  - Fully Specified with ±15V Bipolar Supplies or +12V Single Supply
  - · Rail-to-Rail Operation
- Flexible Design Option
  - GPIO-Compatible Control Inputs
  - EN Input to Enable/Disable Device
  - Available in both 32-TQFN and 28-TSSOP Packages
  - -40°C to +85°C Temperature Range


Ordering Information appears at end of data sheet.



# Low-Leakage, Single 16-Channel and Dual 8-Channel, Analog Multiplexer

### Simplified Block Diagram





### Low-Leakage, Single 16-Channel and Dual 8-Channel, Analog Multiplexer

#### **Absolute Maximum Ratings**

V <sub>POS</sub> to GND0.3V to +20.5V	
V <sub>NEG</sub> to GND20.5V to +0.3V	
V <sub>POS</sub> to V <sub>NEG</sub> 0.3V to +41V	
A_, EN to GND0.3V to (V <sub>POS</sub> + 0.3V)	
NO_, COM_ to GND (V <sub>NEG</sub> - 0.3V) to (V <sub>POS</sub> + 0.3V)	
Continuous Current Into Any Pin ±30mA	
Continuous Power Dissipation (32 TQFN)	
Single-Layer Board (T <sub>A</sub> = +70°C, derate 21.30mW/°C above	
+70°C)	

Continuous Power Dissipation (28 TSSOP)						
Single-Layer Board (T <sub>A</sub> = +70°C, derate 12.8mW/°C above						
+70°C)1025.60mW						
Multilayer Board (T <sub>A</sub> = +70°C, derate 14mW/°C above						
+70°C)1117.30mW						
Operating Temperature Range40°C to +85°C						
Junction Temperature+150°C						
Storage Temperature Range40°C to +150°C						
Soldering Temperature (reflow)+260°C						

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

#### **Package Information**

#### 32 TQFN

Package Code	T3255+4			
Outline Number	<u>21-0140</u>			
Land Pattern Number	<u>90-0012</u>			
Thermal Resistance, Single-Layer Board:				
Junction to Ambient ( $\theta_{JA}$ )	47°C/W			
Junction to Case ( $\theta_{JC}$ )	1.70°C/W			
Thermal Resistance, Four-Layer Board:				
Junction to Ambient ( $\theta_{JA}$ )	29°C/W			
Junction to Case $(\theta_{JC})$	1.70°C/W			

#### **28 TSSOP**

Package Code	U28+2			
Outline Number	<u>21-0066</u>			
Land Pattern Number	<u>90-0171</u>			
Thermal Resistance, Single-Layer Board:				
Junction to Ambient ( $\theta_{JA}$ )	78°C/W			
Junction to Case $(\theta_{JC})$	13°C/W			
Thermal Resistance, Four-Layer Board:				
Junction to Ambient (θ <sub>JA</sub> )	71.6°C/W			
Junction to Case $(\theta_{JC})$	13°C/W			

For the latest package outline information and land patterns (footprints), go to <u>www.maximintegrated.com/packages</u>. Note that a "+", "#", or "-" in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.

Package thermal resistances were obtained using the method described in JEDEC specification JESD51-7, using a four-layer board. For detailed information on package thermal considerations, refer to <u>www.maximintegrated.com/thermal-tutorial</u>.

# Low-Leakage, Single 16-Channel and Dual 8-Channel, Analog Multiplexer

### **Electrical Characteristics - ±15V Bipolar Supplies**

 $(V_{POS} = +15V, V_{NEG} = -15V, GND = 0V, T_A = -40^{\circ}C \text{ to } +85^{\circ}C, \text{ unless otherwise noted.})$  (Note 1)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
POWER SUPPLY						
Positive Power-Supply Voltage	V <sub>POS</sub>		+5		+20	V
Negative Power-Supply Voltage	V <sub>NEG</sub>		-20		-5	v
Positive Power-Supply	er-Supply .	EN = A_ = 0V		40	70	
Current	IPOS	EN = A_ = 2.4V		40	80	μA
Negative Power-Supply Current	1	EN = A_ = 0V	-1		+1	
	INEG	EN = A_ = 2.4V	-1		+1	μA
ANALOG SWITCH		·				
Analog-Signal Voltage Range	V <sub>NO_</sub> , V <sub>COM_</sub>		V <sub>NEG</sub>		V <sub>POS</sub>	V
On-Resistance	R <sub>ON</sub>	V <sub>COM</sub> = 0V, ±5V, ±10V, I <sub>COM</sub> = 1mA ( <u>Note 2</u> )		100	160	Ω
On-Resistance Match Between Channels	ΔR <sub>ON</sub>	V <sub>COM</sub> _ = 0V, ±5V, ±10V, I <sub>COM</sub> _ = 1mA ( <u>Note 2</u> )		10	30	Ω
On-Resistance Flatness	R <sub>FLAT</sub>	V <sub>COM_</sub> = -5V, 0V, +5V, I <sub>COM_</sub> = 1mA ( <u>Note 3</u> )		17	25	Ω
NO_ Off Capacitance	C <sub>NO_OFF</sub>	V <sub>NO</sub> = 0.5V <sub>P-P</sub> , f = 1MHz		4		pF
COM_ Off Capacitance	C <sub>COM_OFF</sub>	V <sub>COM</sub> = 0.5V <sub>P-P</sub> , f = 1MHz		15		pF
COM_ On Capacitance	C <sub>COM_ON</sub>	V <sub>COM</sub> = 0.5V <sub>P-P</sub> , f = 1MHz		10		pF
NO_ Off Leakage Current	I <sub>NO_OFF</sub>	V <sub>NO</sub> _ = ±10V, V <sub>COM</sub> _ = ∓10V ( <u><i>Note 4</i></u> )	-1		+1	nA
COM_ Off Leakage		DG1206, V <sub>NO</sub> = +1/+10V, V <sub>COM</sub> = +10/+1V ( <u>Note 5</u> )	-2		+2	-
Current	ICOM_OFF	DG1207, V <sub>NO</sub> = +1/+10V, V <sub>COM</sub> = +10/+1V ( <u>Note 5</u> )	-1		+1	nA
COM_ On Leakage		DG1206, V <sub>NO</sub> = V <sub>COM</sub> = ±10V	-2		+2	nA
Current	ICOM_ON	DG1207, V <sub>NO</sub> = V <sub>COM</sub> = ±10V	-1		+1	
DYNAMIC CHARACTER	ISTICS					
Turn-On Time	t <sub>ON</sub>	<u>Figure 1</u> (V <sub>S</sub> = 10V)		200	400	ns
Turn-Off Time	tOFF	<u>Figure 1</u> (V <sub>S</sub> = 10V)		300	400	ns
Break-Before-Make Time	t <sub>BBM</sub>	<u>Figure 2</u> (V <sub>S</sub> = 10V)	50			ns
Total Transition Time	t <sub>TT</sub>	<u>Figure 3</u> (V <sub>S</sub> = 10V)			400	ns
-3dB Bandwidth	four	DG1206, <i><u>Figure 4</u></i> (R <sub>S</sub> = R <sub>L</sub> = 50Ω)	= 50Ω) 1	150		MHz
	f <sub>BW</sub>	DG1207, <i>Figure 4</i> (R <sub>S</sub> = R <sub>L</sub> = 50Ω)		200		
Total Harmonic Distortion Plus Noise	THD+N			0.1		%
Off Isolation		<u><i>Figure 6</i></u> (R <sub>S</sub> = R <sub>L</sub> = 50Ω, V <sub>NO</sub> _= 0.5V <sub>P-</sub> P, f = 1MHz)		-80		dB

### Low-Leakage, Single 16-Channel and Dual 8-Channel, Analog Multiplexer

### **Electrical Characteristics - ±15V Bipolar Supplies (continued)**

(V<sub>POS</sub> = +15V, V<sub>NEG</sub> = -15V, GND = 0V,  $T_A$  = -40°C to +85°C, unless otherwise noted.) (Note 1)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS	
Crosstalk		$\frac{Figure 7}{P, f = 1MHz} (R_S = R_L = 50\Omega, V_{NO} = 0.5V_{P}$		-80		dB	
DIGITAL INPUTS (A_, EN	DIGITAL INPUTS (A_, EN)						
Input-Logic-High Voltage	VIH		2.4			V	
Input-Logic-Low Voltage	V <sub>IL</sub>				0.8	V	
Input-Leakage Current	I <sub>IN</sub>		-5		+40	μA	

#### **Electrical Characteristics - +12V Single Supply**

(V<sub>POS</sub> = 12V, V<sub>NEG</sub> = GND = 0V,  $T_A$  = -40°C to +85°C, unless otherwise noted.) (Note 1)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
POWER SUPPLY	•	· · · · ·				
Positive Power-Supply Range	V <sub>POS</sub>	V <sub>NEG</sub> = GND = 0V	10	12	20	V
Positive Power-Supply		EN = A_ = 0V			70	
Current	IPOS	EN = A_ = 2.4V			90	μA
ANALOG SWITCH						•
Analog-Signal Voltage Range	V <sub>NO_</sub> , V <sub>COM_</sub>		0		V <sub>POS</sub>	V
On-Resistance	R <sub>ON</sub>	V <sub>COM</sub> = 3V, 6V, 9V, I <sub>COM</sub> = 1mA ( <u>Note</u> <u>6</u> )		165	250	Ω
On-Resistance Match Between Channels	ΔR <sub>ON</sub>	V <sub>COM</sub> = 3V, 6V, 9V, I <sub>COM</sub> = 1mA ( <u>Note</u> <u>6</u> )		18	50	Ω
On-Resistance Flatness	R <sub>FLAT</sub>	V <sub>COM</sub> = 3V, 6V, 9V, I <sub>COM</sub> = 1mA ( <u>Note</u> <u>6</u> )		15	50	Ω
NO_ Off Capacitance	C <sub>NO_OFF</sub>	V <sub>NO</sub> = 0.5V <sub>P-P</sub> , f = 1MHz		4		pF
COM_ Off Capacitance	C <sub>COM_OFF</sub>	V <sub>COM</sub> = 0.5V <sub>P-P</sub> , f = 1MHz		15		pF
COM_ On Capacitance	C <sub>COM_ON</sub>	V <sub>COM</sub> = 0.5V <sub>P-P</sub> , f = 1MHz		10		pF
NO_ Off Leakage Current	I <sub>NO_OFF</sub>	V <sub>NO_</sub> = +1V/+10V, V <sub>COM_</sub> = +10V/+1V ( <u>Note 7</u> )	-1		+1	nA
COM Off Leakage		DG1206, V <sub>NO</sub> _= +1/+10V, V <sub>COM</sub> _= +10/+1V ( <u>Note 7</u> )	-2		+2	- 0
Current	ICOM_OFF	DG1207, V <sub>NO</sub> = +1/+10V, V <sub>COM</sub> = +10/+1V ( <u>Note 7</u> )	-1		+1	nA
COM_ On Leakage		DG1206, V <sub>NO</sub> = V <sub>COM</sub> = +1V or +10V	-2		+2	
Current	ICOM_ON	DG1207, V <sub>NO</sub> = V <sub>COM</sub> = +1V or +10V	-1		+1	nA
DYNAMIC CHARACTER	ISTICS					
Turn-On Time	ton	<u>Figure 1</u> (V <sub>S</sub> = 10V)		400	600	ns
Turn-Off Time	tOFF	<u>Figure 1</u> (V <sub>S</sub> = 10V)		250	500	ns
Break-Before-Make Time	t <sub>BBM</sub>	<u>Figure 2</u> (V <sub>S</sub> = 10V)	50			ns

# Low-Leakage, Single 16-Channel and Dual 8-Channel, Analog Multiplexer

#### **Electrical Characteristics - +12V Single Supply (continued)**

 $(V_{POS} = 12V, V_{NEG} = GND = 0V, T_A = -40^{\circ}C \text{ to } +85^{\circ}C, \text{ unless otherwise noted.})$  (Note 1)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Total Transition Time	t <sub>TT</sub>	<u>Figure 3</u> (V <sub>S</sub> = 10V)			700	ns
-3dB Bandwidth	f	DG1206, <i><u>Figure 4</u></i> (R <sub>S</sub> = R <sub>L</sub> = 50Ω)		150		N 41 I
	f <sub>BW</sub>	DG1207, <i><u>Figure 4</u></i> (R <sub>S</sub> = R <sub>L</sub> = 50Ω)		200		MHz
Total Harmonic Distortion Plus Noise	THD+N	$\frac{Figure 5}{5}$ (f = 20Hz to 20kHz, V <sub>S</sub> = $5V_{RMS}$ , R <sub>S</sub> = 50 $\Omega$ , R <sub>L</sub> = 10k $\Omega$ )		0.1		%
Off-Isolation		$\frac{Figure \ 6}{P, \ f = 1MHz} (R_S = R_L = 50\Omega, \ V_{NO} = 0.5V_{P}$		-80		dB
Crosstalk		$\frac{Figure 7}{P, f = 1MHz} (R_S = R_L = 50\Omega, V_{NO} = 0.5V_{P}$		-80		dB
DIGITAL INPUTS (A_, EN	1)					
Input-Logic-High Voltage	V <sub>IH</sub>		2.4			V
Input-Logic-Low Voltage	VIL				0.8	V
Input-Leakage Current	l <sub>IN</sub>		-5		+30	μA

Note 1: Limits are 100% tested at T<sub>A</sub> = +85°C. Limits over the operating temperature range and relevant supply voltage range are guaranteed by design and characterization.

Note 2: On Resistance ( $R_{ON}$ ) and On-Resistance Match Between Channels ( $\Delta R_{ON}$ ) are measured when the output channel is turned on. The output (COM\_) is sourced with 1mA current while biased at one of these levels: 0V, ±5V, or ±10V.

Note 3: On-Resistance Flatness (R<sub>FLAT</sub>) is measured when the output channel is turned on. The output (COM\_) is sourced with 1mA current while biased at one of these levels: -5V, 0V, or +5V.

Note 4: NO\_Off-Leakage Current (I<sub>NO\_OFF</sub>) is measured when the output channel is switched off while the input (NO\_) is biased at +10V and output (COM\_) at -10V, or while the input is biased at -10V and output at +10V.

Note 5: COM\_ Off-Leakage Current (I<sub>COM\_OFF</sub>) is measured when the output channel is switched off while the input (NO\_) is biased at +1√ and output (COM\_) at +10√, or while the input is biased at +10∨ and output at +1∨.

Note 6: On Resistance ( $R_{ON}$ ), On-Resistance Match Between Channels ( $\Delta R_{ON}$ ), and On-Resistance Flatness ( $R_{FLAT}$ ) are measured when the output channel is turned on. The output (COM\_) is sourced with 1mA current while biased at one of these levels: 3V, 6V, or 9V.

Note 7: NO\_Off-Leakage Current (I<sub>NO\_OFF</sub>) and COM\_Off-Leakage Current (I<sub>COM\_OFF</sub>) are measured when the output channel is switched off while the input (NO\_) is biased at +1V and output (COM\_) at +10V, or while the input is biased at +10V and output at +1V.




Figure 1. Turn-On Time and Turn-Off Time (Similar Connection for DG1207)




Figure 2. Break-Before-Make Time (Similar Connection for DG1207)




Figure 3. Total Transition Time (Similar Connection for DG1207)




Figure 4. -3dB Bandwidth (Similar Connection for DG1207)




Figure 5. Total Harmonic Distortion Plus Noise (Similar Connection for DG1207)




Figure 6. Off-Isolation (Similar Connection for DG1207)






Figure 7. Crosstalk (Similar Connection for DG1207)


### Low-Leakage, Single 16-Channel and Dual 8-Channel, Analog Multiplexer

**Typical Operating Characteristics** 

(T<sub>A</sub> = 25°C, unless otherwise noted.)









15


12

15

20








# Low-Leakage, Single 16-Channel and Dual 8-Channel, Analog Multiplexer

### **Typical Operating Characteristics (continued)**


 $(T_A = 25^{\circ}C, unless otherwise noted.)$ 




# Low-Leakage, Single 16-Channel and Dual 8-Channel, Analog Multiplexer


### **Typical Operating Characteristics (continued)**


 $(T_A = 25^{\circ}C, unless otherwise noted.)$ 





DG1206 OFF ISOLATION vs. FREQUENCY








2 0

0

3








6


COM\_ VOLTAGE (V)

9

12











# Low-Leakage, Single 16-Channel and Dual 8-Channel, Analog Multiplexer

### **Typical Operating Characteristics (continued)**











# Low-Leakage, Single 16-Channel and Dual 8-Channel, Analog Multiplexer

### **Pin Configurations**

#### DG1206ETJ+



#### DG1206EUI+



# Low-Leakage, Single 16-Channel and Dual 8-Channel, Analog Multiplexer

### **Pin Description**

PIN			FUNCTION		
DG1206ETJ+	DG1206EUI+	NAME	FUNCTION		
POWER SUPP	LY		·		
31	1	V <sub>POS</sub>	Positive Power Supply. Bypass $V_{POS}$ to GND with a minimum 0.1µF ceramic capacitor as close to the pin as possible.		
25	27	V <sub>NEG</sub>	Negative Power Suppy. Bypass $V_{NEG}$ to GND with a minimum 0.1µF ceramic capacitor as close to the pin as possible. In single-supply applications, connect $V_{NEG}$ to GND.		
9	12	GND	Logic Ground Reference		
12, 13, 26, 27, 28, 30, 32	2, 3, 13	NC	Not Connected		
DIGITAL INPU	тѕ		·		
10	14	A3	Logic-Address Input. See the <u>Control Logic</u> section for more information.		
11	15	A2	Logic-Address Input. See the Control Logic section for more information.		
14	16	A1	Logic-Address Input. See the Control Logic section for more information.		
15	17	A0	Logic-Address Input. See the <u>Control Logic</u> section for more information.		
16	18	EN	Enable Input. Drive EN high to enable the multiplexer. Drive EN low to disable all switches. Do not leave EN unconnected.		
ANALOG SWI	тсн				
29	28	COM	Common Bidirectional Analog-Signal Terminal. It can be either an input or output.		
1	4	NO16	Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.		
2	5	NO15	Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.		
3	6	NO14	Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.		
4	7	NO13	Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.		
5	8	NO12	Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.		
6	9	NO11	Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.		
7	10	NO10	Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.		
8	11	NO9	Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.		
24	26	NO8	Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.		
23	25	NO7	Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.		
22	24	NO6	Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.		
21	23	NO5	Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.		


# Low-Leakage, Single 16-Channel and Dual 8-Channel, Analog Multiplexer

### **Pin Description (continued)**

P	IN	NAME	FUNCTION
DG1206ETJ+	DG1206EUI+	NAME	FUNCTION
20	22	NO4	Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.
19	21	NO3	Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.
18	20	NO2	Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.
17	19	NO1	Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.


### **Pin Configurations**

#### DG1207ETJ+



# Low-Leakage, Single 16-Channel and Dual 8-Channel, Analog Multiplexer

#### DG1207EUI+



### **Pin Description**

Р	IN		FUNCTION				
DG1207ETJ+	DG1207EUI+	NAME	FUNCTION				
POWER SUPPLY							
29	1	V <sub>POS</sub>	Positive Power Supply. Bypass $V_{POS}$ to GND with a minimum 0.1 $\mu F$ ceramic capacitor as close to the pin as possible.				
25	27	V <sub>NEG</sub>	Negative Power Suppy. Bypass $V_{NEG}$ to GND with a minimum 0.1 $\mu F$ ceramic capacitor as close to the pin as possible. In single-supply applications, connect $V_{NEG}$ to GND.				
9	12	GND	Logic Ground Reference				
11, 12, 13, 26, 28, 30, 32	3, 13, 14	NC	Not Connected				
DIGITAL INPU	TS						
10	15	A2	Logic-Address Input. See the Control Logic section for more information.				
14	16	A1	Logic-Address Input. See the <u>Control Logic</u> section for more information.				
15	17	A0	Logic-Address Input. See the Control Logic section for more information.				
16	18	EN	Enable Input. Drive EN high to enable the multiplexer. Drive EN low to disable all switches. Do not leave EN unconnected.				
ANALOG SWI	тсн						
31	2	COMB	B-Side Common Bidirectional Analog-Signal Terminal. It can be either an input or output.				
27	28	COMA	A-Side Common Bidirectional Analog-Signal Terminal. It can be either an input or output.				

# Low-Leakage, Single 16-Channel and Dual 8-Channel, Analog Multiplexer

### **Pin Description (continued)**

PIN			FUNCTION
DG1207ETJ+	DG1207EUI+	NAME	FUNCTION
1	4	NO8B	B-Side Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.
2	5	NO7B	B-Side Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.
3	6	NO6B	B-Side Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.
4	7	NO5B	B-Side Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.
5	8	NO4B	B-Side Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.
6	9	NO3B	B-Side Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.
7	10	NO2B	B-Side Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.
8	11	NO1B	B-Side Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.
24	26	NO8A	A-Side Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.
23	25	NO7A	A-Side Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.
22	24	NO6A	A-Side Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.
21	23	NO5A	A-Side Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.
20	22	NO4A	A-Side Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.
19	21	NO3A	A-Side Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.
18	20	NO2A	A-Side Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.
17	19	NO1A	A-Side Normally-Open Bidirectional Analog-Signal Terminal. It can be either an input or output.

### Low-Leakage, Single 16-Channel and Dual 8-Channel, Analog Multiplexer

#### **Detailed Description**

The DG1206/DG1207 are single 16-channel or dual 8-channel multiplexing switch devices with low-leakage and lowcharge injection. The ultra-low capacitance and low-charge injection of the DG1206/DG1207 make them ideal for automatic test equipment systems, data acquisition systems, sample-and-hold systems, and communication systems where low glitch and fast settling time are required.

The DG1206 is a single 16-channel multiplexer. It switches one of the 16 NO\_ inputs to a common output COM, as determined by the four selection inputs A3, A2, A1, and A0. The DG1207 is a dual 8-channel multiplexer. It switches a pair of differential NO\_ inputs to differential outputs COMA and COMB, as determined by the three selection inputs A2, A1, and A0. See the <u>Control Logic</u> section for more information.

The DG1206/DG1207 operate rail-to-rail and are fully specified for  $\pm$ 15V bipolar supplies or  $\pm$ 12V single supply. The EN input on DG1206/DG1207 is used to enable or disable the device. When EN is low, all channels are switched off. When EN is high, each channel conducts bidirectionally according to the selection inputs.

#### Control Logic

The DG1206 uses four selection inputs A3, A2, A1, and A0 to determine the switching logic.

#### Table 1. DG1206 Control Logic

A3	A2	A1	A0	EN	SWITCH ON
Х	X	Х	Х	0	Switch Off
0	0	0	0	1	1
0	0	0	1	1	2
0	0	1	0	1	3
0	0	1	1	1	4
0	1	0	0	1	5
0	1	0	1	1	6
0	1	1	0	1	7
0	1	1	1	1	8
1	0	0	0	1	9
1	0	0	1	1	10
1	0	1	0	1	11
1	0	1	1	1	12
1	1	0	0	1	13
1	1	0	1	1	14
1	1	1	0	1	15
1	1	1	1	1	16

The DG1207 uses three selection inputs A2, A1, and A0 to determine the switching logic.

#### Table 2. DG1207 Control Logic

A2	A1	A0	EN	SWITCH ON
X	Х	Х	0	Switch Off
0	0	0	1	1A, 1B
0	0	1	1	2A, 2B
0	1	0	1	3A, 3B
0	1	1	1	4A, 4B

# Low-Leakage, Single 16-Channel and Dual 8-Channel, Analog Multiplexer


# Table 2. DG1207 Control Logic (continued)

A2	A1	A0	EN	SWITCH ON
1	0	0	1	5A, 5B
1	0	1	1	6A, 6B
1	1	0	1	7A, 7B
1	1	1	1	8A, 8B

# Low-Leakage, Single 16-Channel and Dual 8-Channel, Analog Multiplexer

### **Typical Application Circuits**


#### Data Acquisition System with DG1206 Using Bipolar Supplies



# Low-Leakage, Single 16-Channel and Dual 8-Channel, Analog Multiplexer

### **Typical Application Circuits (continued)**

#### Data Acquisition System with DG1207 Using Single Supply



#### **Ordering Information**

PART NUMBER	PIN-PACKAGE	TEMPERATURE
DG1206ETJ+*	32 TQFN	-40°C to +85°C
DG1206EUI+	28 TSSOP	-40°C to +85°C
DG1207ETJ+*	32 TQFN	-40°C to +85°C
DG1207EUI+	28 TSSOP	-40°C to +85°C

+ Denotes a lead(Pb)-free/RoHS-compliant package.

\*Future products—contact factory for availability.

### Low-Leakage, Single 16-Channel and Dual 8-Channel, Analog Multiplexer

### **Revision History**

REVISION	REVISION	DESCRIPTION	PAGES
NUMBER	DATE		CHANGED
0	6/20	Initial Release	—

For pricing, delivery, and ordering information, please visit Maxim Integrated's online storefront at https://www.maximintegrated.com/en/storefront/storefront.html.

Maxim Integrated cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim Integrated product. No circuit patent licenses are implied. Maxim Integrated reserves the right to change the circuitry and specifications without notice at any time. The parametric values (min and max limits) shown in the Electrical Characteristics table are guaranteed. Other parametric values quoted in this data sheet are provided for guidance.

Maxim Integrated and the Maxim Integrated logo are trademarks of Maxim Integrated Products, Inc.

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Maxim Integrated: DG1206EUI+ DG1207EUI+