


DO NOT SCALE
DIMENSIONS IN mm

METRIC

THIRD ANGLE PROJECTION

NOTES:

- 1 CONNECTOR IS DESIGNED FOR FLAT RIBBON CABLE ON 1.27 CENTERS. FOR CABLE REQUIREMENTS SEE AMP APPLICATION SPECIFICATION 114-19022.
- 2 THESE RECEPTACLE CONNECTORS MATE WITH 0.64^{+0.05}mm SQUARE OR ROUND POSTS ON 2.54mm GRID.
- 3 MARK INDICATING FIRST CABLE POSITION REFERRING TO CONTACT POSITION.
- 4 THERE IS NO POLARIZATION-SLOT AT THIS END IN 4, 6, 8, 10 AND 14 POS CONNECTORS.
- 5 THESE CONNECTORS CAN BE USED IN CONJUNCTION WITH STRAIN-RELIEF COVERS OF PARTNR: 100103.
- 6 THERE IS NO POLARIZATION-SLOT AT THIS END IN 4, 6, AND 8 POS CONNECTORS. PRODUCT SPECIFICATION 108-19033.



QTY PER REEL	DIM. "C"	"B" CABLE POS.	"A" POL. POS.	PART NUMBER	PART REV.
1000	85.9	64	32	6-215919-4	D
1000	80.8	60	30	6-215919-0	D
1000	68.1	50	25	5-215919-0	D
1500	60.5	44	22	4-215919-4	D
1500	55.4	40	20	4-215919-0	D
1500	47.8	34	17	3-215919-4	D
1500	37.6	28	13	2-215919-6	D
1500	30.0	20	10	2-215919-0	D
1500	24.9	16	8	1-215919-6	D
1500	22.4	14	7	1-215919-4	D
1500	17.3	10	5	1-215919-0	D
1500	14.8	8	4	0-215919-8	C
1500	12.2	6	3	0-215919-6	D
1500	9.7	4	2	0-215919-4	C
1500	7.3	3	1	0-215919-3	C

COMPONENT NAME	MATERIAL	PLATING / COLOUR
3 RECEPTACLE CONTACT	PHOSPHORBRONZE Cu Sn6	AT CONTACT-PLACE: 0.2µm GOLD AT WIRING END: 2.5µm/TIN ENTIRE UNDERCOATING: 1.27µm/NICKEL
2 COVER	THERMOPLASTIC POLYESTER GF UL 94 -V0	GREY RAL 7032 ONLY FOR REF.
1 HOUSING		

REV.	DESCRIPTION	DATE	BY	CHK.
D6	ECR-10-026086	21-12-10	LSM	
D5	ECR06-29576	15-12-06	R.M.	
D4	ET00-0243-04	21-03-05	R.M.	
D3	ET00-0159-04	13-07-04	R.M.	
D2	ET00-0180-03	19-01-04	R.M.	
D1	ET00-0093-03	23-05-03	SS	
LTR	REVISION RECORD		DR.	CHK.
DR.	RAHOEVEN	02-02-88	CHK.: RYERSTUNEN	APP.: LVS05ST
DATE:			DATE:	

CUSTOMER DRAWING

AMP ITALIA SpA
Corso F.lli Cervi, 15
COLLENO (TORINO)

AMP-LATCH MIL-TYPE RECEPT.
CONN. ASS'Y 14,9 PRE-ASSEMBLED
0.2 µm GOLD TAPE MOUNTED ON REEL

DWG. No. C-215919

SIZE A3

SHEET 1 OF 1

REV. LTR D6

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-215919-0](#)