

The CAL 9500P

Programmable Profiling Temperature & **Process Controller**











CAL Controls

Ordering information codes

		Code								
Model	48 x 48 mm	95	Ordering example 1 Model 9500P ssd/relay/relay outputs Model	Ordering example 2 Model 9500 with 4-20mA/ssd/relay						
Outputs	SSd / relay	00		tputs, s					•	
	relay / relay	11			_					
	SSd / SSd	22	95 00 1 P B 4 00 95	B2	1	P		0	00	
	4-20mA / relay	B1								
	4-20mA / ssd	B2								
	0-5V / relay	C1								
	0-5V / ssd	C2								
	0-10V / relay	D1								
	0-10V / ssd	D2	Codes for additional software and hardwa	*0						
Output 3	Always relay	1								
Programmer		Р	CALCOMMS charting & logging software	10	01	XX	3	0	0	
Inputs	Sensor	A	CALCOMMS CD Rom demo-disk	0	0	0	1	2	4	
	4-20mA	В	Communications board RS232	3C	00	00	2	0	0	
	0-5V 0-10V	C D	Communications board RS485	3C	00	00	4	0	0	
Communications	None fitted	0	RS232 to RS485 converter	3C	24	00	0	0	0	
	RS232 fitted RS485 fitted	2 4	CALopc OPC server	10	01	GB	S	0	0	
				Available on the web						

Ask for these brochures for our other product ranges



Temperature Controllers

This low-cost range is dedicated for temperature control and also has the added options for RS232 & RS485 communications boards. All controllers have P.I.D. control, autotune, heat-cool strategy and a single ramp-soak profile.

SL000418 33063/01/0900



Temperature Sensors This comprehensive catalog is full of useful thermocouples and RTDs for all to thermowells.


information as well as a wide range of applications. Also included is a range of accessories from cables, connectors, glands




CAL Controls Inc 1580 S. Milwaukee Avenue, Libertyville, IL 60048. USA Tel: (847) 680-7080 Fax: (847) 816-6852 email: sales@cal-controls.com http://www.cal-controls.com

CAL Controls Ltd Bury Mead Road, Hitchin, Herts, SG5 1RT. UK Tel: + 44 (0)1462-436161 Fax: + 44 (0)1462-451801 email: sales@cal-controls.co.uk http://www.cal-controls.com









Solid State Relays

This range of solid-state relays completes the solution from sensors to control output. This catalog shows a range of hockey-puck style SSRs and the Solitron range with built-in heat sinks that are easy to specify and install.

a VIDA GROUP company

The CAL 9500P Programmable Temperature / Process Controller with Communications & Software Support

CAL innovators in control

Established in 1963, CAL is a dynamic and strong company leading the industry in single-loop controllers. CAL's pioneering spirit established many of today's world standards for controllers such as the first 48mm x 48mm (¹/16[™]DIN) analog controller, followed by the first digital controller of the same size and then the first 24mm x 48mm (¹/32ND DIN) controller.

CAL's range of easy-to-use controllers are complemented by a suite of software products for communications, data-logging and supervisory control.

CAL has developed a reputation based on product support, innovation and attractively-styled controllers that enhance our customers' equipment, panels and machines.

Note:



The CAL 9500P programmable process controller

The CAL 9500P is a versatile programmable controller for temperature and process control applications. It is designed to offer the highest functionality in a 48mm x 48mm (1/16[™] DIN) package.

The 9500P can be factory configured in a range of process control or temperature control options making the controller dedicated to the application, ideal for both OEM and manufacturing process applications.

This combination of programmable ramp/soak profiles, process control inputs and 3 outputs, together with RS232 or RS485 comms makes the CAL 9500P a unique and affordable package.

Controller functionality

• Full P.I.D. operation

- Autotune at 75% of set-point or at set-point
- Heat-cool operation
- RS232 or RS485 communications options
- CE, UL & CSA compliant



Inputs

- Thermocouples & RTD (PT100, 2 or 3 wire)
- Analog 0-20mA, 4-20mA, 0-50mV, 0-5V, 0-10V

Easy to scale input signals

CAL has made the task of scaling inputs very simple: **example:** 4-20mA = 60-260 units, where 4mA = 60 units**note:** 4-20mA corresponds to an input range of 10-50mV Step 1, enter scale max' = 260, **Step 2**, enter scale min' = 60,

- Step 3, enter input max' = 50 (i.e. 50mV = 20mA)
- Step 4, enter input min' = 10 (i.e. 10mV = 4mA).

Outputs (total of three outputs)

- Solid state relay drive (SSD) and Relays (2 amp)
- Analogue 4-20mA, 0-5V, 0-10V




Programmer functionality

- Up to 31 programs (profiles)
- Up to 126 segments
- Unlimited use of event outputs via the 2nd and 3rd outputs
- Copy/Paste/Edit/Delete functions to simplify program building
- Call another program as a sub-program segment
- Up to 999 program loop cycles, or continuous loop cycling
- Hold back function, to ensure the next segment is not started until the last segment reaches the set-point
- 3 power fail recovery options, (Hold, Continue or Reset)
- Front panel interrogation of the program position
- Memory usage indication during programming.

(note: program capacity is a memory function and different types of segment use more/less memory).

Profile of a single program

Set-point



Time

Edi E

CoPy

int

1440

Subset of the functions list:

- hoLd Suspends program until run
- on Run program
- Edit Insert, delete or copy programs

Power failure modes

- rSEt Reset to program start
- Cont Continue from interruption
- hoLd Hold at interruption

Segment types

- SPr Ramp to next set-point
- SoAK Hold set-point for set time
- StEP Step to new set-point
- LooP Repeat the program
- CALL Call up another program
- E.oP Generate an event output at end of segment
- Edit Delete or insert a segment

Hold back function

• hb.u Hold back, this function 'holds back' the ramping set-point until the measured value catches up with the ramping set-point. This function ensures that the time taken to ramp does not reduce the next segment.

Visit our website for - pdf technical manuals, application notes, CALCOMMS demo program and much, much more

www.cal-controls.com



Memory Allocation Table

Function	Memory Usage
Ramp	4 Bytes
Ramp with Holdback	5 Bytes
Soak	2 Bytes
Step	3 Bytes
Loops (1-3)	1 Byte
Loop (4+)	2 Bytes
Call	1 Byte
Event Output	1 Byte
Program Header	1 Byte

Examples:

Maximum capacity; 351 Bytes, 126 segments per program, 31 programs

Example 1 (349 Bytes) One program of 116 segments (58 ramps, 58 soaks)

Example 2 (340 Bytes) 4 programs of 28 segments (14 ramps, 14 soaks)


Example 3 (341 Bytes) 31 programs of (ramp-soak-ramp)

The above ramps are without hold-back option

Set-point







The CAL 9500P is potentially the most versatile and flexible controller in its size and price range. The above program shows what is possible from this unique controller.

www.cal-controls.com

Software and Connectivity

Using CAL controllers there's a wide range of software support products designed to suit different applications.

Product	CALCOMMS	CALopc	CALpoll
Description	Easy to use and install software application requiring no design work.	Software driver for OPC client/server applications such as SCADA.	Example demo program plus source code to help you build a custom application.
ldeal for:	Chart-recorders, Data-logger, Alarms	Large SCADA applications requiring many inputs other than CAL	Custom software applications dedicated to one application.
For use by:	Plant/Process engineers, Supervisors, Quality control, System/Machine designers	Process engineers, Plant managers, SCADA system builders.	Software engineers with Visual C experience
Typical applications	Quality control, Process optimisation, Lab equipment	Process control, Manufacturing	OEM machines, development projects
License cost	\$	\$\$\$	Gratis/web
Development cost	\$	\$\$\$	\$\$\$\$\$
Flexibility/versatility	✓ Only connect to CAL	✓✓✓ Connect to other h/w	As flexible as the s/w
Other comments	Designed for simplicity with many features	User must also purchase the SCADA software	For use with Visual C ++ Compiler

Terminology:

- **SCADA** Supervisory Control And Data Acquisition
- OPC Object Linking and Embedding for Process Control
- OEM Original Equipment Manufacturer

CALopc – OPC server

The CALopc server is a MODBUS RTU software product

designed for integration into OPC client/server

applications such as SCADA.

CALopc includes pre-configured templates for all CAL controllers, together with controller bitmaps and the 7-segment LED true type font.

Using this OPC server allows 'tags' to be added to all controller functions and built into the SCADA application enabling the display and changing of any parameters in a custom configured application for complete process monitoring and control.



CALpoll – tools for custom software engineers

CALpoll is a free of charge software product available from www.cal-controls.com It includes an example program and source code in Visual C++. It is ideal for use by software engineers who wish to create custom applications that need to communicate with CAL controllers via the MODBUS RTU protocol.

The source code includes routines for communicating via MODBUS saving the software engineer significant development time. The example program also doubles as an ideal diagnostic tool for proving that the communications hardware is set up correctly.

For further details please contact CAL.


CALCOMMS[™] Chart-recorder, Data-logging & Configuration software for Windows

CALCOMMS[™] charting and logging software is incredibly easy to use. It is designed to connect up to 128 controllers by RS485 into a standard or industrial PC. This allows the user to program all functions of the controller and to data-log the recorded process signals.

Functions

- Data-logger for archiving process data
- Chart-recorder for on-screen viewing of trends
- Virtual instrument display
- On-screen alarm displays
- Configuration/programming tool for controllers
- 'Cloning' of instrument settings
- Saving of applications of multiple controller set-ups
- Remote set-point adjustment






Ideal for:

Recording process data for manufacturing reporting, quality control, health & safety purposes, or OEM system development.

Visit our website for - pdf technical manuals, application notes, CALCOMMS demo program and much, much more

www.cal-controls.com





Applications:

Food industry, Dairy industry, Rubber & Plastics manufacturing, Ovens, Furnaces, Kilns, Plastics machines, Laboratory and Scientific equipment, Bottling and beverage production and many other process industries.

www.cal-controls.com

CAL 9500P Specifications


Thermocouple 9 types: Standards: CJC rejection: External resistance:	B, E, J, K, L, N, R, S, T IEC 584–1–1 : EN60584–1 20:1 (0.05°/°C) typical 100Ω maximum
Resistance thermometer RTD/Pt100 Standards: Bulb current:	2 or 3 wire IEC751: EN60751 (100Ω 0°C/138.5Ω 100°C Pt) 0.2mA maximum
Analog process inputs	0 to 50mV, +/- 0.1%. 0-20mA, 4-20mA, +/- 0.1%. 0-5V, +/- 0.1%. 0-10V, +/- 0.1%
Applicable to all Thermocouple Calibration accuracy: Sampling frequency: Common mode rejection: Series mode rejection: Temperature coefficient: Reference conditions:	e and RTD inputs (SM =sensor maximum) +/- 0.25% SM +/- 1°C input 10Hz, CJC 2 sec. Negligible effect up to 140dB, 240V, 50-60Hz 60dB, 50-60Hz 50ppm/°C SM typical 22°C +/- 2°C, rated voltage after 15 minutes settling time.
Output devices (check configur SSd1 and SSd2: Relay 1,2,3 Analog output:	ration) Solid state relay driver: To switch a remote SSR 6Vdc (nominal) 20mA non-isolated Miniature power relay: Form A/SPST contacts (AgCdO): $2A/250Vac$ resistive load $4-20mA 500\Omega max +/- 0.1\%$ full scale typical $0-5Vdc 10mA (500\Omega min) +/- 0.1\%$ full scale typical $0-10Vdc 10mA (1K\Omega min) +/- 0.1\%$ full scale typical
General Displays: Keypad:	Upper, 4 Digits, high brightness green LED. 10mm (0.4") high. Lower, 4 Digits, high brightness orange LED 9mm (0.35") high. Digital range -199 to 9999. Hi-res mode -199.9 to 999.9. LED output indicators - SP1 square, green; SP2/SP3 round, red 3 elastomeric buttons
Programmer functions: Segments: Programs: Program memory:	Total of 126 per program Maximum of 31 programs 351 Bytes (see memory allocation table)
Environmental Humidity: Altitude: Installation: Pollution: Protection: EMC emission: EMC immunity: Ambient: Mouldings: Weight: Safety:	Max 95% non-condensing up to 2000M Categories II and III Degree II NEMA 4X, IP66 (Front panel only) EN50081-1 FCC Rules 15 subpart J Class A EN50082-2 0-50°C (32-130°F) flame retardant polycarbonate 180g (6.4 oz) EN61010–/CSA22.2 No 1010.1 92 (see users manual)
Dimensions Front facia: Sleeve length: Instrument body: Overall length:	51.0 x 51.0mm (2.0" x 2.0") (includes gasket) 106.7mm (4.2") (with gasket fitted) 44.8 x 44.8mm (1.76" x 1.76") 116.2mm (4.57")
Supply Voltage:	100–240Vac, 50–60Hz +/- 10% maximum permitted fluctuation
Power Requirements:	6.0VA (nominal)

Typical Application

In this example the load temperature is monitored by a temperature transducer/transmitter which provides a 4-20mA input signal to the controller. The 4-20mA output has been allocated to SP1 to drive an SCR power controller providing a phase angle controlled output to the heater.

F1 Fuse:	1A time lag type to IEC127. CSA/UL rating 250Vac
F2 Fuse:	High Rupture Capacity (HRC) Suitable for maximum rated load current


S1 Switch: IEC/CSA/UL Approved disconnecting device.



Visit our website for - pdf technical manuals, application notes, CALCOMMS demo program and much, much more

www.cal-controls.com

Technical Specifications



www.cal-controls.com