

## PCB receptacle female back A-cod 5-pole



Part number	21 03 321 2530
Specification	PCB receptacle female back A-cod 5-pole
HARTING eCatalogue	<a href="https://b2b.harting.com/21033212530">https://b2b.harting.com/21033212530</a>

### Identification

Category	Connector
Series	Circular connectors M12
Element	PCB adapter
Specification	Straight incl. housing for rear mounting

### Version

Termination method	Reflow soldering termination (THR/SMC)
Gender	Female
Locking type	Screw locking
Shielding	Shielded
Number of contacts	5
Coding	A-coding

### Technical characteristics

Rated current	4 A
Rated voltage	50 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Insulation resistance	$> 10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Ambient temperature	-40 ... +85 °C
Mating cycles	$\geq 100$



Pushing Performance

## Technical characteristics

Degree of protection acc. to IEC 60529	IP67
Overvoltage category	III
Isolation group	I ( $600 \leq CTI$ )

## Material properties

Material (insert)	LCP
Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
Material (hood/housing)	Zinc die-cast
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Specifications and approvals

Specifications	IEC 61076-2-101
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079

## Commercial data

Packaging size	60
Net weight	26.33 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440402 PCB connector