



**OptoSupply**

*Light It Up*


**4.7x5.7mm Oval Premium Orange LED**

**OSO5PA4571D**


## ■Features

- High Luminous LEDs
- 4.7x5.7mm Standard Directivity
- UV Resistant Epoxy
- Water Clear Type

## ■Outline Dimension



1. Anode  
2. Cathode  
Unit: mm  
Tolerance:  $\pm 0.2\text{mm}$   
unless otherwise noted



## ■Applications


- Electronic Signs And Signals
- Small Area Illuminations
- Back Lighting
- Other Lighting

## ■Absolute Maximum Rating (Ta=25°C)

Item	Symbol	Value	Unit
DC Forward Current	I <sub>F</sub>	50	mA
Pulse Forward Current#	I <sub>FP</sub>	120	mA
Reverse Voltage	V <sub>R</sub>	5	V
Power Dissipation	P <sub>D</sub>	120	mW
Operating Temperature	T <sub>opr</sub>	-30~ +85	°C
Storage Temperature	T <sub>stg</sub>	-40 ~ +100	°C
Lead Soldering Temperature	T <sub>sol</sub>	260°C /5sec	-

#Pulse width Max.10ms , Duty ratio max 1/10

## ■Directivity



## ■Electrical -Optical Characteristics (Ta=25°C)

Item	Symbol	Condition	Min.	Typ.	Max.	Unit
DC Forward Voltage* <sub>1</sub>	V <sub>F</sub>	I <sub>F</sub> =20mA	-	2.1	2.4	V
DC Reverse Current	I <sub>R</sub>	V <sub>R</sub> =5V	-	-	10	μA
Domi. Wavelength* <sub>2</sub>	λ <sub>D</sub>	I <sub>F</sub> =20mA	600	605	610	nm
Luminous Intensity* <sub>3</sub>	I <sub>v</sub>	I <sub>F</sub> =20mA	4200	5800	-	mcd
50% Power Angle	2θ <sub>1/2</sub>	I <sub>F</sub> =20mA	-	40/70	-	deg

\*<sub>1</sub> Tolerance of measurements of forward voltage is  $\pm 0.1\text{V}$

\*<sub>2</sub> Tolerance of measurements of dominant wavelength is  $\pm 1\text{nm}$

\*<sub>3</sub> Tolerance of measurements of luminous intensity is  $\pm 15\%$

## LED & Application Technologies

