Multi-stage AC/DC EMI Filter with Excellent Attenuation Performance




- Rated currents from 1 to 30 A
- Two-stage filter
- Very high differential and common-mode attenuation
- Optional medical versions (B type)
- Optional safety versions (A type)
- Optional enhanced performance versions
- Optional overvoltage protection (Z type)





Attenuation performance



Technical Specifications

Rated voltage*	250 VAC, 50/60 Hz 250 VDC
Operating frequency	DC to 400 Hz
Rated currents	1 to 30 A @ 40℃ max.
High potential test voltage	P -> N 1100 VDC for 2 sec P -> PE 2000 VAC for 2 sec (equiv. cap <88 nF) P -> PE 2550 VDC for 2 sec (equiv. cap >88 nF) P -> PE 2500 VAC for 2 sec (B types)
Temperature range (operation and storage)	-25°C to +100°C (25/100/21)**
Certified to	UL 1283, CSA 22.2 No. 8 1986, IEC/EN 60939 (applies to AC and DC applications)
Flammability corresponding to	Laces for -07 version: UL 94 VW-1 Terminal plastic for -06/-08 version: UL 94 V-0 Grommet for -07 version: UL 94 V-0
Surge pulse protection (Z type)	Helps compliance to IEC61000-4-5 (Differential Mode only)
Overvoltage category	II acc. IEC 60664-1
Pollution degree	2 acc. IEC 60664-1
Altitude	2000m (above derating applies)**

 maximum RMS operating voltage at rated frequency or the maximum DC operating voltage
 for dedicated requests exceeding this specification (e.g. -40 °C or higher altitude) please contact your local
 Schaffner Sales office

Approvals & Compliances




Features and Benefits

- FN 2090 two-stage filters are designed for easy and fast chassis mounting.
- FN 2090 B versions without capacitors to earth comply to 1MOP for ME (medical equipment) acc. IEC 60601-1
- FN 2090 A versions with low capacitance to earth for safety critical applications with a requirement for low leakage currents.
- FN 2090 filters offers an optimized filter range for enhanced performance AC and DC applications, in same compact size (KK, LL, NN types)
- All filters provide an exceptional conducted attenuation performance, based on chokes with high permeable core material.
- FN 2090 two-stage filters are designed for noisy applications requiring excellent filter performance.
- The higher inductivity offers increased attenuation performance with the same form factor as FN 2060 and FN 2080 series.
- All FN 2090 filters can be delivered with optional surge pulse protection (Z type).
- FN 2090 filters are also available as singlestage filters (FN 2030 series).
- Various terminal options allow you to select the desired connection style.

Typical Applications

- Electrical and electronic equipment
- Consumer goods
- Household equipment
- Building automation
- Industrial applications
- Machinery
- Medical equipment
- Electronic data processing equipment
- Office automation and datacom equipment
- Various noisy applications requiring high filter
- performance

Typical electrical schematic



Filter Selection Table

Filter*	Buy	Rated current	Leakage current**	Power Loss	Inductance***	Cap	oacitan	ce***	Resistance***	Inp	ut/Ou	tput	Weight
	-	@ 40°C (25°C)	@ 250V AC/50 Hz	@ 25°C/DC	L	Cx Cy1 Cy2		R	connections				
			(@ 120V AC/60 Hz)										
		[A]	[mA]	[W]	[mH]	[µF]	[nF]	[nF]	[kΩ]				[g]
FN2090-1		1 (1.1)	0.45 (0.26)	1.8	20	0.22	2.2	1.0	680	-06	-07		73
FN2090-3		3 (3.4)	0.45 (0.26)	3.7	14	0.33	2.2	1.0	470	-06	-07		158
FN2090-4		4 (4.5)	0.45 (0.26)	6.4	14	0.33	2.2	1.0	470	-06	-07		176
FN2090-6		6 (6.7)	0.61 (0.35)	7.1	8	0.47	3.3	1.0	330	-06	-07	-08	191
FN2090-8		8 (8.9)	0.61 (0.35)	7.7	8	0.47	3.3	1.0	330	-06	-07		330
FN2090-10		10 (11.2)	0.61 (0.35)	8.4	8	0.47	3.3	1.0	330	-06	-07	-08	369
FN2090-12		12 (13.4)	0.93 (0.54)	12.1	4	1	10	1.0	220	-06	-07	-08	391
FN2090-16		16 (17.9)	0.93 (0.54)	10.7	4	1	10	1.0	220	-06	-07		425
FN2090-20		20 (22.4)	0.93 (0.54)	8.2	2.7	1	10	1.0	220	-06		-08	530
FN2090-30-08		30 (33.5)	0.93 (0.54)	10.1	1.5	1	10	1.0	220			-08	548
						0.05	0.17	0.17		0.5	07		
FN2090A-1		1 (1.1)	0.13 (0.07)	1.8	20	0.22	0.47	0.47	680	-06	-07		73
FN2090A-3		3 (3.4)	0.13 (0.07)	3.7	14	0.33	0.47	0.47	470	-06	-07		158
FN2090A-4		4 (4.5)	0.13 (0.07)	6.4	14	0.33	0.47	0.47	470	-06	-07		176
FN2090A-6		6 (6.7)	0.13 (0.07)	7.1	8	0.47	0.47	0.47	330	-06	-07	-08	191
FN2090A-8		8 (8.9)	0.13 (0.07)	7.7	8	0.47	0.47	0.47	330	-06	-07		330
FN2090A-10		10 (11.2)	0.13 (0.07)	8.4	8	0.47	0.47	0.47	330	-06	-07	-08	369
FN2090A-12		12 (13.4)	0.13 (0.07)	12.1	4	1	0.47	0.47	220	-06	-07	-08	391
FN2090A-16		16 (17.9)	0.13 (0.07)	10.7	4	1	0.47	0.47	220	-06	-07		425
FN2090A-20		20 (22.4)	0.13 (0.07)	8.2	2.7	1	0.47	0.47	220	-06		-08	530
FN2090A-30-08		30 (33.5)	0.13 (0.07)	10.1	1.5	1	10	10	220			-08	548
FN2090B-1		1 (1.1)	0.00	1.8	20	0.22			680	-06	-07		73
FN2090B-1 FN2090B-3		3 (3.4)	0.00	3.7	14	0.22			470	-06	-07		158
FN2090B-3 FN2090B-4		4 (4.5)	0.00	6.4	14	0.33			470	-06	-07		176
FN2090B-4		6 (6.7)	0.00	7.1	8	0.33			330	-06	-07	-08	170
FN2090B-8		8 (8.9)	0.00	7.7	8	0.47			330	-06	-07	00	330
FN2090B-10		10 (11.2)	0.00	8.4	8	0.47			330	-06	-07	-08	369
FN2090B-12		12 (13.4)	0.00	12.1	4	1			220	-06	-07	-08	391
FN2090B-16		16 (17.9)	0.00	10.7	4	1			220	-06	-07		425
FN2090B-20		20 (22.4)	0.00	8.2	2.7	1			220	-06		-08	530
FN2090B-30-08		30 (33.5)	0.00	10.1	1.5	1			220			-08	548
Enhanced performance													
FN2090KK-1-06		1 (1.15)	3.46 (1.99)	1.8	20	0.22	22	22	680	-06	-07		95
FN2090NN-3-06		3 (3.4)	15.71 (9.05)	3.7	14	0.33	100	100	470	-06			200
FN2090NN-4-06		4 (4.5)	15.71 (9.05)	6.4	14	0.33	100	100	470	-06			210
FN2090NN-6-06		6 (6.7)	15.71 (9.05)	7.1	8	0.47	100	100	330	-06			220
FN2090NN-8-06		8 (8.9)	15.71 (9.05)	7.7	8	0.47	100	100	330	-06			340
FN2090LL-10		10 (11.2)	5.18 (2.98)	8.4	8	0.47	33	33	330	-06		-08	470
FN2090LL-12		12 (13.4)	5.18 (2.98)	12.1	4	1	33	33	220	-06		-08	500
FN2090LL-16-06		16 (17.9)	5.18 (2.98)	10.7	4	1	33	33	220	-06			530
FN2090LL-20		20 (23)	5.18 (2.98)	8.2	2.7	1	33	33	220	-06		-08	580
FN2090LL-30-08		30 (33.5)	5.18 (2.98)	10.1	1.5	1	33	33	220			-08	600
	1	l I		I I	I	l.	I	I	I I			1	1

** To compile a complete part number, please replace the -.. with the required I/O connection style.


** For surge pulse protection, please add Z (e.g. FN2090Z-10-06, FN2090BZ-20-08). The different letters code the used Cy values in the filter type (A = 0.47nF; K = 22nF; L = 33nF; N = 100nF; as the FN2090 is a dual stage filter each letter stands for one stage of Cy)


** Maximum leakage under usual AC operating conditions (acc. IEC 60939-3). Note: if the neutral line is interrupted, worst case leakage could reach twice this level. Leakage current for DC application is 0mA


*** Tolerances apply: Inductance: -30/+50%, Capacitance: ±20%, Resistance: ±10%

Typical Filter Attenuation


Per CISPR 17: symmetrical 50 Ω /50 Ω -> Differential Mode (DM); asymmetrical 50 Ω /50 Ω -> Common Mode (CM)









4 A: Standard type




6 A: Standard type







A type



A type




A type





A type

dB




A type







B type




B type




B type




B type




Enhanced performance




Enhanced performance




Enhanced performance



Enhanced performance





Enhanced performance




10M

30 A: Standard type







A type




A type




A type




A type




B type




B type




B type









B type




Enhanced performance




Enhanced performance



Enhanced performance




Enhanced performance





Enhanced performance


Product Selector		
FN 2090 xy-xx-yy		
	06	Faston 6.3 $ imes$ 0.8 mm (spade/soldering)
	07	Wire leads
	08	Studs (M4 screws)
	– 1 to 30	Rated current
	Blank	Standard version
	Z	With surge protection
	Blank	Standard version
	А	Safety version
·	В	Medical version
	KK/LL/NN	High performance version

Mechanical Data









Dimensions

	1 A	3 A	4 A	6 A	8 A	10 A	12 A	16 A	20 A	30 A	Tolerances
А	71	85	85	85	113.5 ±1	113.5 ±1	113.5 ±1	113.5 ±1	113.5 ±1	113.5 ±1	±0.5
В	46.6	54	54	54	57.5 ±1	57.5 ±1	57.5 ±1	57.5 ±1	57.5 ±1	57.5 ±1	±0.5
с	22.3	30.3	30.3	30.3	45.4 ±1	45.4 ±1	45.4 ±1	45.4 ±1	45.4 ±1	45.4 ±1	±0.5
D	50.5	64.8	64.8	64.8	94 ±1	94 ±1	94 ±1	94 ±1	94 ±1	94 ±1	±0.5
E	44.5	49.8	49.8	49.8	56	56	56	56	56	56	±0.5
F	61	75	75	75	103	103	103	103	103	103	±0.3
G	21	27	27	27	25	25	25	25	25	25	±0.2
н	10.8	12.3	12.3	12.3	12.4	12.4	12.4	12.4	12.4	12.4	±0.5
1	16.8	20.8	20.8	20.8	32.4	32.4	32.4	32.4	32.4	32.4	±0.5
J	25.25	19.9	19.9	19.9	15.5	15.5	15.5	15.5	15.5	15.5	±0.5
κ	5.3	5.3	5.3	5.3	4.4	4.4	4.4	4.4	4.4	4.4	
L	6.3	6.3	6.3	6.3	6	6	6	6	6	6	
м	0.7	0.7	0.7	0.7	1	1	1	1	1	1	±0.3
Connection style -06											
Ν	6.3 x 0.8										
Connection style -07											
0	8.3	8.3	8.3	8.3	8.4	8.4	8.4	8.4			±0.5
P	14	14.9	14.9	14.9	18	18	18	18			±0.5
AWG type wire	AWG 20	AWG 20	AWG 20	AWG 18	AWG 18	AWG 18	AWG 16	AWG 16			
Wire length	140	140	140	140	140	140	140	140			+5
Connection style -08											
Ν						M4	M4	M4	M4	M4	
Recommended torque (Nm)						1.2 - 1.3	1.2 - 1.3	1.2 - 1.3	1.2 - 1.3	1.2 - 1.3	
Earth terminal						1.5 - 1.7	1.5 - 1.7	1.5 - 1.7	1.5 - 1.7	1.5 - 1.7	

All dimensions in mm; 1 inch = 25.4 mm Tolerances according: ISO 2768-m/EN 22768-m

 $\label{eq:please-visit} \begin{tabular}{lll} \textsf{Please-visit} & \underline{www.schaffner.com} \ to \ find \ more \ details \ on \ filter \ connectors. \end{tabular}$

Headquarters, Global Innovation and Development

Switzerland

Schaffner Group Industrie Nord Nordstrasse 11e 4542 Luterbach +41 32 681 66 26 info@schaffner.com

To find your local partner within Schaffner's global network <u>schaffner.com</u>

© 2023 Schaffner Group

The content of this document has been carefully checked and understood. However, neither Schaffner nor its subsidiaries assume any liability whatsoever for any errors or inaccuracies of this document and the consequences thereof. Published specifica-tionsw are subject to change without notice. Product suitability for any area of application must ultimately be determined by the customer. In all cases, products must never be operated outside their published specifications. Schaffner does not guarantee the availability of all published products. This disclaimer shall be governed by substantive Swiss law and resulting disputes shall be settled by the courts at the place of business of Schaffner Holding AG. Latest publications and a complete disclaimer can be downloa-ded from the Schaffner website. All trademarks recognized.

Sales and Application Centers

Finland

Schaffner Oy Sauvonrinne 19 H 8500 Lohja +358 50 468 7284 finlandsales@schaffner.com

France

Schaffner EMC S.A.S. 16-20 Rue Louis Rameau 95875 Bezons +33 1 34 34 30 60 francesales@schaffner.com

Germany

Schaffner Deutschland CmbH Schoemperlenstrasse 12B 76185 Karlsruhe +49 721 56910 germanysales@schaffner.com

India

Schaffner India Pvt. Ltd Regus World Trade Centre WTC 22nd Floor Unit No 2238 Brigade Gateway Campus 26/1 Dr. Rajkumar Road Malleshwaram (W) 560055 Bangalore +91 8067935355 indiasales@schaffner.com

United Kingdom

Schaffner Ltd. Suite 1 Oakmede Place Terrace Road RG42 4JF Binfield +44 118 9770070 uksales@schaffner.com

United States

Schaffner EMC Inc. 52 Mayfield Avenue Edison, New Jersey +1 732 225 9533 usasales@schaffner.com

Sweden

Schaffner EMC AB Östermalmstrorg 1 114 42 Stockholm +46 8 5050 2425 swedensales@schaffner.com

Switzerland

Schaffner EMV AC Industrie Nord Nordstrasse 11e 4542 Luterbach +41 32 681 66 26 switzerlandsales@schaffner.com

Taiwan

Schaffner EMV Ltd.

U-Town 20 Floor-2 No 97 Section 1 XinTai 5th Road XiZhi District 22175 New Taipei City +886 226975500 taiwansales@schaffner.com

Italy

Schaffner EMC S.r.l. Via Ticino, 30 20900 Monza (MB) +39 039 21 41 070 italysales@schaffner.com

Japan

Schaffner EMC K.K.

ISM Sangenjaya 7F 1-32-12 Kamiuma Setagaya-ku 154-0011 Tokyo +81 3 5712 3650 japansales@schaffner.com

Singapore

Schaffner EMC Pte Ltd. Blk 3015A Ubi Road 1 #05-09 Kampong Ubi Industrial Estate 408705 Singapore +65 63773283 singaporesales@schaffner.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schaffner:

 FN2090-1-06
 FN2090-1-07
 FN2090-3-06
 FN2090-3-07
 FN2090-4-06
 FN2090-4-07
 FN2090-6-06
 FN2090-6-07

 FN2090-8-06
 FN2090-8-07
 FN2090-10-06
 FN2090-10-07
 FN2090-12-06
 FN2090-12-07
 FN2090-16-06
 FN2090-16-06
 FN2090-16-06
 FN2090-16-06
 FN2090-16-06
 FN2090-16-06
 FN2090-16-06
 FN2090-12-07
 FN2090-16-06
 FN2090-8-06
 FN2090-8-06