

LITHIUM CELL/BATTERY TEST SUMMARY

IN ACCORDANCE WITH SUB-SECTION 38.3
OF MANUAL OF TESTS AND CRITERIA



N/A = Not Applicable

1. Name of cell / battery
1600-0247 Model 16340 3.7V, 700mAh, 2.59Wh

2. Manufacturer of cell / battery / product	
Name	Ansmann AG
Address	Industriestr. 10, 97959 Assamstadt
Phone	+49 6294 4204-0
Email	info@ansmann.de
Website	www.ansmann.de

3. Test laboratory of cell / battery / product	
Name	ATS Electronic Technology Co., Ltd
Address	3/F, Building A, No.1 Hedong Three Road, Jinxia Community, Changan, Dongguan, Guangdong, C
Phone	+86 769-38975958
Email	ats@dgats.com
Website	http://www.dgats.com

4. ID-number and date			
Unique test report identification number	ATSU181201111	Date of test report	10.01.2019

DESCRIPTION OF CELL / BATTERY

5. Mark the type of cell/battery with an "•"			
<input checked="" type="radio"/>	Lithium ion cell	Lithium metal cell	<input type="radio"/>
<input type="radio"/>	Lithium ion battery	Lithium metal battery	<input type="radio"/>

6. Parameters	Cell	Battery
Mass in gram (g):	17,86	
Lithium ion: Indicate watt-hour rating (Wh):	2,59	
Lithium metal: Indicate lithium metal content in gram (g):	0,245	

7. Physical description of cell / battery
Lithium-Ion

LITHIUM CELL/BATTERY TEST SUMMARY

IN ACCORDANCE WITH SUB-SECTION 38.3
OF MANUAL OF TESTS AND CRITERIA



Name of cell/battery (taken from field 1)
1600-0247 Model 16340 3.7V, 700mAh, 2.59Wh

8. Model numbers
1600-0247

TESTS AND RESULTS

9. List of tests conducted and results - Mark N/A, pass or fail with an "•"	N/A	pass	fail
T1 - Altitude simulation	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T2 - Thermal Test	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T3 - Vibration	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T4 - Shock	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T5 - External Short Circuit	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T6 - Impact / Crush	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T7 - Overcharge	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T8 - Forced Discharge	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>
	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>

10. Reference to assembled battery testing requirements		
	N/A	<input type="text"/>

11. Reference to the revised edition of the Manual of Tests and Criteria used and to amendments thereto
ST-SG-AC10-11-Rev6-38.3-Amend.1

12. The manufacture of the cell / battery is in accordance with the documented quality management system as required by the regulations.

13. Place, Date	14. Title, Surname, First name	15. Company stamp and signature
Assamstadt	Adrian Selke	Selke, Adrian <small>Digital unterschrieben von Selke, Adrian Datum: 2019.12.19 18:35:09 +01'00'</small>