

338TTA035M

AXIAL LEAD

Parts are RoHS compliant

Date code when parts became RoHS: 14



APPLICATIONS: General purpose, filtering, bypass, coupling

ELECTRICAL SPECIFICATIONS

Capacitance: 3300 uF

Dissipation Factor: 0.18 Max at 120 Hz and 20°C

Temperature Range: -40°C to +85°C

Impedance: N/A

Tolerance: -20 %, +20 %

WVDC: 35 Volts DC

SVDC: 44 Volts DC

Ripple Current: 1810 mA at 120 Hz and 85°C

Impedance Ratios:-25°C/20°C 2 and -40°C/20°C - 4

Leakage Current: .03CV or 4uA, whichever is greater

3465 uA after 1 Minute

.01CV or 3uA, whichever is greater

1155uA after 2 Minutes

Load Life: 2000 hours at 85°C with 100 % of rated voltage and with 0 % of rated ripple current

Capacitance Change: ≤20% of initial measured value

Dissipation Factor: ≤200% of maximum specified value

Leakage Current: ≤100% of maximum specified value

Frequency Multipliers:

50 HZ	120 HZ	400 HZ	1 KHZ	10 KHZ	100 KHZ
0.8	1	1.23	1.34	1.5	1.5

Temperature Multipliers:

45°C	60°C	70°C	65°C	75°C	85°C	105°C	125°C
1.8	1.7	1.4	1.6	1	1	0	0

PHYSICAL DIMENSIONS

Diameter (D): 16 mm + 0.5 mm


Length (L): 41 mm + 2 mm

Coating: BluePET sleeving

Lead Wire Diameter (d): 0.8 mm +/- 0.05 mm

Lead Length: 35 mm +/- MIN mm

Lead Finish: Matte Tin



2400 East Devon Avenue Suite 292 Des Plaines, IL 60018 (847) 675-1760 FAX (847) 673-2850

Illinois Capacitor (HK) Ltd., Tel: 85227930931, Fax: 85227930731, www.ilcap.com.hk

© Copyright 2020 Illinois Capacitor. An affiliate of Cornell Dubilier. All Rights Reserved