


37011000410 - 370 Series



Series: 370

[Fuse 370 Datasheet](#)

Disclaimer Notice

The 370 Series are TR5®, sub-miniature, fast-acting type, 250V rated fuses, designed in accordance to IEC 60127- 3.

Features:

- Reduced PCB space requirements
- Direct solderable or plug-in versions
- Internationally approved
- Low internal resistance
- Shocksafe casing
- Vibration resistant
- Halogen free

Questions? [Contact Littelfuse Support](#)

[Check Stock](#)

[Order Samples](#)



Electrical Characteristics | **Technical Resources** | Environmental Info

Property (Mouseover for details)	Value
Ampere Rating (A)	1
Nominal Melting I ² T (A ² sec)	0.2
Interrupting Rating	35A@250VAC
Min Operating Temp °C	-40
Max Operating Temp (°C)	85
Moisture Sensitivity Level	MIL-STD-202 Method 106
Nominal Power Dissipation (W)	310
Nominal Voltage Drop (mV)	110
Nominal Cold Resistance (Ohms)	0.0676
Opening	Fast-Acting (F)
Package Size	TR5 (8.5x8mm)
VAC (V)	250

Connect with Littelfuse



[Mobile Site](#)

About Littelfuse

- [About Littelfuse](#)
- [Conflict Free Statement](#)
- [History](#)
- [Investor Relations](#)
- [Legal](#)
- [Press Room](#)
- [Privacy Statement](#)
- [Supply Chain Transparency](#)
- [Website Feedback](#)

Explore Littelfuse

- [Capabilities Brochures](#)
- [Careers](#)
- [Check Distributor Stock](#)
- [Competitor Cross Reference](#)
- [Industries](#)
- [Order Samples](#)
- [Products](#)
- [Services](#)

Technical Resources

- [Application Designs](#)
- [Education](#)
- [FAQs](#)
- [iDesign™](#)
- [Littelfuse University](#)
- [Product Catalogs](#)
- [Quality Documents](#)
- [Technical Documents](#)

