

MHLL5040-200

PHYSICAL DIMENSIONS:



A	50.0[1.969]	\pm	1.00[.039]
B	40.0[1.575]	\pm	0.50[.0197]
C	0.10[.004]	\pm	0.02[.0008]
D	0.20[.008]		MAX



ELECTRICAL CHARACTERISTICS:

Initial Permeability(μ') (13.56MHz)	130 \pm 20%
Initial Permeability(μ'') (13.56MHz)	5 Max

PRODUCTS SHAPE AND DIMENSIONS



MEASURED BY ANGLENT E4991A , 1Ts .

NOTES: UNLESS OTHERWISE SPECIFIED

1. OPERATING TEMPERATURE RANGE -40°C TO 85°C .
2. FLEXIBLE FERRITE SHEET.
3. D IS MEASURED AFTER REMOVING PAPER LINER OF ADHESIVE

DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
				Laird			
				PROJECT/PART NUMBER:	REV	PART TYPE:	DRAWN BY:
				MHLL5040-200	B	CO-FIRE	QU
C	CHANGE CURVE AND CHARACTERISTICS	03/27/14	QU	DATE:	SCALE:	SHEET:	
B	CHANGE μ' FROM 112~208	03/27/14	QU	11/20/13	NTS	1 of 1	
A	ORIGINAL DRAFT	11/20/13	QU	CAD #	TOOL #		
REV	DESCRIPTION	DATE	INT	MHLL5040-200-B			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[MHLL5040-200](#)