

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2016061630](#)
Status: **Active**
Overview: High-Current, Universal-Clamp Terminal Blocks
Description: High Current Universal Clamp Terminal Block, 35.00mm DIN-rail or Screw Mount, 285.0A / 1000V, Grey Housing and Cover, 1 Circuit

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

UL E48521

General

Product Family Terminal Blocks
 Series [201606](#)
 Application Wire-to-Wire
 Component Type One Piece
 Overview [High-Current, Universal-Clamp Terminal Blocks](#)
 Product Literature Order No 987651-7108
 Product Name Universal Clamp
 Type Universal Clamp
 UPC 78172551180

Physical

Circuits (Loaded) 1
 Circuits (maximum) 1
 Color - Resin Grey
 Entry Angle Horizontal
 Lock to Mating Part None
 Material - Metal Aluminum
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin Polyamide
 Number of Rows 1
 Orientation Vertical
 Panel Mount Screws
 Pitch - Mating Interface N/A
 Polarized to Mating Part N/A
 Stackable No
 Temperature Range - Operating -40° to +125°C
 Termination Interface: Style Screw
 Wire Size AWG 1/0+1/0, 2+2, 2+2+2, 300 MCM-2
 Wire Size mm² 33.60+33.60, 33.60+33.60+33.60, 33.60-152.01, 53.00+53.00

Electrical


Current - Maximum per Contact 285.0A
 Voltage - Maximum 1000V

Material Info

Engineering Number MX-KE163

Reference - Drawing Numbers

Sales Drawing 2016061630-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[201606 Series](#)

This document was generated on 09/20/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[201606-1630](#) [201606-1637](#) [201606-1633](#) [201606-1635](#)