

CONTACT ARRANGEMENT

code for x	function	actuator position/connected terminals			
D	On-On (alternating)	Pos.1:	1-2	Pos. 2:	2-3
F	Mom-On	Rest position:	1-2	Pressed down:	2-3

RATING


y	contacts	all other conductive parts	rating DC	rating AC
empty	Ag (solid)	Brass, 10 µm Ag over 1.5 µm Ni	6V / 6 A 12V / 5 A 30V / 4 A	125 V / 6 A 250 V / 3 A
B	Brass, 2 µm Au over 3 µm Ni	Brass, 2 µm Au over 3 µm Ni	max. 0.4 VA, max. 20 V AC/DC	
G	Ag (solid), 2 µm Au over 3 µm Ni	Brass, 2 µm Au over 3 µm Ni	6V / 6 A 12V / 5 A 30V / 4 A 150 V / 10 mA	125 V / 6 A 250 V / 3 A

Min. rating for silver contacts: 10mA, 5V AC/DC
 Min. rating for gold plated contacts: 1µA, 20mV AC/DC

Specifications:

Contact resistance: 20mOhm max.
 Insulation resistance: 1 000MOhm min. at 500V DC
 Dielectric strength: 1 500V, 50Hz for the duration of 1 minute
 Operating temperature: -45°C to +140°C
 Mechanical life: min. 30 000 cycles
 Soldering conditions: hand-soldering: max.: 420°C, 3sec., 60W
 auto-soldering: max.: 270°C, 5sec.
 Mounting instruction: max. torque: 137Ncm
 Material: Case: DAP
 Housing: stainless steel, CNS9265
 Bushing: copper alloy, C3604BD nickel plated
 Actuator: copper alloy, C3604BD chrome plated
 Included accessories: 2 pcs. nut 15/32-32, nickel plated, 14mm wrench size
 1 pc. tooth washer
 1 pc. locking washer

PANEL MOUNTING



Tolerances: 0.00: ±0.25mm 0.0: ±0.40mm		Date	Name	MPG 106 x y
		07/09	dr	
Revised	11/11	dr		30 18 88
Dimension	01/11	dr		
Travel	02/10	dr		
Actuator dim	07/09	ok		
Modifications	Date	Name		knitter-switch
				Page 1/1