



## 650 V Power SiC Merged PIN Schottky Diode, 16 A



**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**

### FEATURES

- Majority carrier diode using Schottky technology on SiC wide band gap material
- Positive  $V_F$  temperature coefficient for easy paralleling
- Virtually no recovery tail and no switching losses
- Temperature invariant switching behavior
- 175 °C maximum operating junction temperature
- MPS structure for high ruggedness to forward current surge events
- Meets JESD 201 class 1A whisker test
- Solder Bath temperature 275 °C maximum, 10 s per JESD 22-B106
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)

### DESCRIPTION / APPLICATIONS

Wide band gap SiC based 650 V Schottky diode, designed for high performance and ruggedness.

Optimum choice for high speed hard switching and efficient operation over a wide temperature range, it is also recommended for all applications suffering from Silicon ultrafast recovery behavior.

Typical applications include AC/DC PFC and DC/DC ultra high frequency output rectification in FBPS and LLC converters.

### MECHANICAL DATA

**Case:** 2L TO-220AC

Molding compound meets UL 94 V-0 flammability rating  
Base P/N-M3 - halogen-free, RoHS-compliant

**Terminals:** matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

**Mounting torque:** 10 in-lbs maximum

| PRIMARY CHARACTERISTICS  |             |
|--------------------------|-------------|
| $I_{F(AV)}$              | 16 A        |
| $V_R$                    | 650 V       |
| $V_F$ at $I_F$ at 150 °C | 1.65 V      |
| $T_J$ max.               | 175 °C      |
| $I_R$ at $V_R$ at 175 °C | 10 $\mu$ A  |
| $Q_C$ ( $V_R = 400$ V)   | 45 nC       |
| Package                  | 2L TO-220AC |
| Circuit configuration    | Single      |

| ABSOLUTE MAXIMUM RATINGS ( $T_A = 25$ °C unless otherwise specified) |                      |  |             |                  |
|--|----------------------|--|-------------|------------------|
| PARAMETER  | SYMBOL               | TEST CONDITIONS                                    | VALUES      | UNITS            |
| Peak repetitive reverse voltage                                      | $V_{RRM}$            |  | 650         | V                |
| Average rectified forward current                                    | $I_{F(AV)}$          | $T_C = 121$ °C (DC)                                | 16          | A                |
| DC blocking voltage  | $V_{DC}$             |  | 650         | V                |
| Repetitive peak surge current  | $I_{FRM}$            | $T_C = 25$ °C, $f = 50$ Hz, square wave, DC = 25 % | 55.5        | A                |
| Non-repetitive peak forward surge current                            | $I_{FSM}$            | $T_C = 25$ °C, $t_p = 10$ ms, half sine wave       | 120         |                  |
|  |                      | $T_C = 110$ °C, $t_p = 10$ ms, half sine wave      | 110         |                  |
| Power dissipation  | $P_{tot}^{(1)}$      | $T_C = 25$ °C                                      | 89          | W                |
|  |                      | $T_C = 110$ °C                                     | 38          |                  |
| $I^2t$ value   | $\int i^2 dt$        | $T_C = 25$ °C                                      | 72          | A <sup>2</sup> s |
|  |                      | $T_C = 110$ °C                                     | 61          |                  |
| Operating junction and storage temperatures                          | $T_J^{(2)}, T_{Stg}$ |  | -55 to +175 | °C               |

### Notes

(1) Based on maximum  $R_{th}$

(2) The heat generated must be less than the thermal conductivity from junction-to-ambient:  $dP_D/dT_J < 1/R_{\theta JA}$



| <b>ELECTRICAL SPECIFICATIONS</b> ( $T_J = 25\text{ }^\circ\text{C}$ unless otherwise specified) |        |   |      |      |      |               |
|---|--------|---|------|------|------|---------------|
| PARAMETER   | SYMBOL | TEST CONDITIONS   | MIN. | TYP. | MAX. | UNITS         |
| Forward voltage   | $V_F$  | $I_F = 16\text{ A}$                                       | -    | 1.45 | 1.70 | V             |
|   |        | $I_F = 16\text{ A}, T_J = 150\text{ }^\circ\text{C}$      | -    | 1.65 | 1.95 |               |
|   |        | $I_F = 16\text{ A}, T_J = 175\text{ }^\circ\text{C}$      | -    | 1.75 | -    |               |
| Reverse leakage current   | $I_R$  | $V_R = V_R\text{ rated}$                                  | -    | -    | 85   | $\mu\text{A}$ |
|   |        | $V_R = V_R\text{ rated}, T_J = 150\text{ }^\circ\text{C}$ | -    | -    | 200  |               |
|   |        | $V_R = V_R\text{ rated}, T_J = 175\text{ }^\circ\text{C}$ | -    | 10   | -    |               |
| Total capacitance   | C      | $V_R = 1\text{ V}, f = 1\text{ MHz}$                      | -    | 700  | -    | pF            |
|   |        | $V_R = 400\text{ V}, f = 1\text{ MHz}$                    | -    | 71   | -    |               |
| Total capacitive charge   | $Q_C$  | $V_R = 400\text{ V}, f = 1\text{ MHz}$                    | -    | 45   | -    | nC            |

| <b>THERMAL - MECHANICAL SPECIFICATIONS</b> ( $T_A = 25\text{ }^\circ\text{C}$ unless otherwise specified) |            |                 |          |      |      |                    |
|---|------------|-----------------|----------|------|------|--------------------|
| PARAMETER   | SYMBOL     | TEST CONDITIONS | MIN.     | TYP. | MAX. | UNITS              |
| Thermal resistance, junction-to-case  | $R_{thJC}$ |                 | -        | 1.3  | 1.7  | $^\circ\text{C/W}$ |
| Marking device  |            |                 | C16ET07T |      |      |                    |




Fig. 1 - Typical Forward Voltage Drop Characteristics




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage




Fig. 4 - Non-Repetitive Peak Forward Surge Current vs. Pulse Duration (Square Wave)




Fig. 5 - Typical Thermal Impedance  $Z_{thJC}$  Characteristics




Fig. 6 - Maximum Allowable Case Temperature vs. Average Forward Current




Fig. 8 - Typical Capacitive Energy vs. Reverse Voltage




Fig. 7 - Forward Power Loss Characteristics





Fig. 9 - Typical Capacitive Charge vs. Reverse Voltage



**ORDERING INFORMATION TABLE**



- 1** - Vishay Semiconductors product
- 2** - C = SiC diode
- 3** - Current rating (16 = 16 A)
- 4** - E = single diode
- 5** - Package TO-220
- 6** - Voltage rating: (07 = 650 V)
- 7** - T = true 2 pin
- 8** - Environmental digit:  
-M3 = halogen-free, RoHS-compliant, and termination lead (Pb)-free

| <b>ORDERING INFORMATION</b> |                      |                               |                              |
|-----------------------------|----------------------|-------------------------------|------------------------------|
| <b>PREFERRED P/N</b>        | <b>BASE QUANTITY</b> | <b>MINIMUM ORDER QUANTITY</b> | <b>PACKAGING DESCRIPTION</b> |
| VS-C16ET07T-M3              | 50/tube              | 1000                          | Antistatic plastic tubes     |

| <b>LINKS TO RELATED DOCUMENTS</b> |  |
|-----------------------------------|--|
| Dimensions                        | <a href="http://www.vishay.com/doc?96069">www.vishay.com/doc?96069</a> |
| Part marking information          | <a href="http://www.vishay.com/doc?95391">www.vishay.com/doc?95391</a> |



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.