

ANT-5GBLADE170



- 5G: 824-960 / 1710-2680 / 3400-3600/4800-4900MHZ
- Gain: 5dBi
- Copper with Rugged ABS Finish.
- Hinged: 0 - 90 degrees
- Vertical Polarisation
- VSWR <2.0
- Omni-Directional Design
- 50ohm Impedance
- Operating Temp: -30 to +60°C
- Dimensions: 171x 19mm
- Max Power: 10W

Applications

- General Low Power Radio
- M2M Applications
- Telemetry

Description

A compact Blade antenna with a hinged SMA male fixing and rugged plastic finish. This ready to operate antenna requires no tuning and provides optimum range and reliability to your application.


Ordering Information

Part No	Description
ANT-5GBLADE170-SMA	5G LTE +5dBi GSM Blade Antenna Hinged 170mm SMAM

ANT-5GBLADE170




Mechanical Dimensions



ANT-5GBLADE170



Performance / VSWR Plot



RF Solutions Ltd. Recycling Notice

Meets the following EC Directives:

DO NOT Discard with normal waste, please recycle.

ROHS Directive 2011/65/EU and amendment 2015/863/EU

Specifies certain limits for hazardous substances.

WEEE Directive 2012/19/EU Waste electrical & electronic equipment. This product must be disposed of through a licensed WEEE collection point. RF Solutions Ltd., fulfils its WEEE obligations by membership of an approved compliance scheme.

Environment agency registration number **WEE/JB0104WV**.



Disclaimer:

Whilst the information in this document is believed to be correct at the time of issue, RF Solutions Ltd does not accept any liability whatsoever for its accuracy, adequacy or completeness. No express or implied warranty or representation is given relating to the information contained in this document. RF Solutions Ltd reserves the right to make changes and improvements to the product(s) described herein without notice. Buyers and other users should determine for themselves the suitability of any such information or products for their own particular requirements or specification(s). RF Solutions Ltd shall not be liable for any loss or damage caused as a result of user's own determination of how to deploy or use RF Solutions Ltd's products. Use of RF Solutions Ltd products or components in life support and/or safety applications is not authorised except with express written approval. No licences are created, implicitly or otherwise, under any of RF Solutions Ltd's intellectual property rights. Liability for loss or damage resulting or caused by reliance on the information contained herein or from the use of the product (including liability resulting from negligence or where RF Solutions Ltd was aware of the possibility of such loss or damage arising) is excluded. This will not operate to Limit or restrict RF Solutions Ltd's liability for death or personal injury resulting from its negligence.

www.rfsolutions.co.uk

RF Solutions Ltd

William Alexander House, William Way, Burgess Hill, West Sussex, RH15 9AG

Sales: +44 (0)1444 227900

Tech Support: +44 (0)1444 227909

