

Product Search Data Sheet

Note: This datasheet may be out of date

Please download the latest datasheet of BLM18EG601SH1# from the official website of Murata Manufacturing Co., Ltd.

https://www.murata.com/en-global/products/productdetail?partno=BLM18EG601SH1%23


BLM18EG601SH1#

"#" indicates a package specification code.

In Production RoHS REACH Q200

< List of part numbers with package codes > BLM18EG601SH1J BLM18EG601SH1D BLM18EG601SH1B

Appearance & Shape





BLM18E series has a modified internal electrode structure, that minimizes stray capacitance and increases the effective frequency range.

Features

- 1. Low DC Resistance and a large Rated Current are suitable for noise suppression of the driver circuit.
- 2. Excellent direct current characteristics.
- 3. Thin type (t=0.5mm) is suitable for small and low profile equipment such as ETC, RKE.

Applications

Automotive Usage	Powertrain/Safety
---------------------	-------------------

Packaging Information

Packaging	Specifications	Minimum Order Quantity
J	330mm Paper Tape	10000
D	180mm Paper Tape	4000
В	Bulk(Bag)	1000

1 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



Note: This datasheet may be out of date

Please download the latest datasheet of BLM18EG601SH1# from the official website of Murata Manufacturing Co. Ltd.

Co., Ltd. https://www.murata.com/en-global/products/productdetail?partno=BLM18EG601SH1%23

BLM18EG601SH1#

"#" indicates a package specification code.

Specifications

Shape	SMD	Mass(typ.)
Size Code (in mm)	1608	Number of Circuit
Size Code (in inch)	0603	
Length	1.6mm	
Length Tolerance	±0.15mm	
Width	0.8mm	
Width Tolerance	±0.15mm	
Thickness	0.8mm	
Thickness Tolerance	±0.15mm	
Impedance (at 100MHz)	600Ω	
Impedance (at 100MHz) Tolerance	±25%	
Impedance (at 1GHz)	700Ω	
Impedance (at 1GHz) Tolerance	(Тур.)	
Rated Current (at 85°C)	500mA	
Rated Current (at 125°C)	500mA	
DC Resistance(max.)	0.35Ω	
Operating Temperature Range	-55℃ to 125℃	

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering

2 of 3



Product Search Data Sheet

Note: This datasheet may be out of date.


Please download the latest datasheet of BLM18EG601SH1# from the official website of Murata Manufacturing Co. Ltd.

Co., Ltd. https://www.murata.com/en-global/products/productdetail?partno=BLM18EG601SH1%23

BLM18EG601SH1#

"#" indicates a package specification code.





(Resistance element becomes dominant at high frequencies.)

Impedance-Frequency Characteristics

Equivalent Circuit

 This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

3 of 3