

5145300-3 Product Details

[Share](#) | [Print](#) | [Email](#)


5145300-3

TE Internal Number: 5145300-3

Active

[View 3D PDF](#)

Smart Card Connectors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector
- 8 Positions
- Without Card Guide Slots
- Not Stacked
- Height Above PC Board = 3.65 mm

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [SURFACE MOUNT SMART CARD W/ CARD DETECTION SWITCH \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version B)
- [3D Model](#) (IGES, Version B)
- [3D Model](#) (STEP, Version B)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Card Guide Slots = Without
- Stacked = No
- Profile = Standard
- Card Type = Smart Card

Termination Features:

- Solder Tail Contact Plating = Tin over Nickel

Dimensions:

- Height Above PC Board (mm [in]) = 3.65 [0.144]

Body Features:

- Number of Positions = 8
- Mount Style = Surface Mount
- [Card Scoop](#) = Without
- Switch Style = Unsealed
- Number of Signal Contacts = 8
- Number of Switch Contacts = 2
- Durability Rating = 50,000 Cycles
- Cover = With

Contact Features:

- Contact Base Material = Phosphor Bronze
- Contact Plating, Mating Area, Material = Gold (5)

Housing Features:

- Housing Color = Black
- Housing Material = High Temperature Thermoplastic

Configuration Features:

- Cable = Without
- Card Detection Switch = With
- Card Detection Switch Position = Normally Open

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Accepts Card Thickness (mm [in]) = 0.76 [0.030]
- PCB Thickness, Recommended (mm [in]) = 1.57 [0.062]

Packaging Features:

- Packaging Quantity = 336/Carton

Other:

- Brand = AMP

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

