

## SHUNTS

### ATO® Shunt



Operating Temp.: -40°C to +125°C  
 Maximum Continuous Load Rating: 35A\*  
 Housing Material: Thermoplastic (UL 94V0 Rated)  
 Terminal Material: Brass Tin Plated

### MINI® Shunt



Operating Temp.: -40°C to +125°C  
 Maximum Continuous Load Rating: 20A\*  
 Housing Material: Thermoplastic (UL 94V0 Rated)  
 Terminal Material: Zinc Silver Plated

### MICRO2® Shunt



Operating Temp.: -40°C to +125°C  
 Maximum Continuous Load Rating: 20A\*  
 Housing Material: PA66  
 Terminal Material: Ag plated zinc alloy

### MICRO3® Shunt



Operating Temp.: -40°C to +125°C  
 Maximum Continuous Load Rating: 15A\*  
 Housing Material: PA66  
 Terminal Material: Ag plated zinc alloy

### JCASE® Shunt



Operating Temp.: -40°C to +125°C  
 Maximum Continuous Load Rating: 50A\*  
 Housing Material: PA66  
 Terminal Material: Copper

### MCASE+® Shunt



Operating Temp.: -40°C to +125°C  
 Maximum Continuous Load Rating Unslotted: 30A\*  
 Maximum Continuous Load Rating Slotted: 50A\*  
 Housing Material: PPA (33% / 35% GF)  
 Terminal Material: Copper

| Part Number  | Type             | Max Continuous Load Rating* (A) | Housing Material        | Terminal Material  | Part Quantity     |
|--------------|------------------|---------------------------------|-------------------------|--------------------|-------------------|
| 02400094P    | ATO              | 35                              | Thermoplastic (UL 94V0) | Brass Tin Plated   | 2000              |
| 0297900.WXNV | MINI             | 20                              | Thermoplastic (UL 94V0) | Zinc Silver Plated | 3000              |
| 0327900.YX2S | MICRO2           | 20                              | PA66                    | Zinc Silver Plated | 4000              |
| 0337900.PX2S | MICRO3           | 15                              | PA66                    | Zinc Silver Plated | 2000              |
| 0495900_     | JCASE            | 50                              | PA66                    | Copper             | Z=2200 pcs/X=1 pc |
| 0695900.PXP  | MCASE+ Unslotted | 30                              | PPA (33%/35% GF)        | Copper             | 2000              |
| 0695900.PXPS | MCASE+ Slotted   | 50                              | PPA (33%/35% GF)        | Copper             | 2000              |

\*Rating varies based on mating terminal performance

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[0495900.Z](#) [02400094P](#) [0297900.WXNV](#) [0327900.YX2S](#)