
Item no.: 285-197
Product description: 2-conductor ground terminal block



Produkt kann von Bild abweichen / product may differ

Packing unit 5 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	25 - 95 mm ²
Cross section [AWG]	2 - 000 AWG
Connection method	POWER CAGE CLAMP
Weight	311 g
Color	green-yellow
Wiring type	Side-entry
No. of connection Points	2
No. of potentials	1
Height	101 mm
Height	3.98 in
Width	25 mm
Width	0.98 in
Depth	107 mm
Depth	4.21 in
Strip length from	35 mm
Strip length to	35 mm
Strip length	1.38 in
Mounting	TS 35



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
285-197	ABS	05-HG476175/3-PDA			25
285-197	CCA	NL6390			95
285-197	CSA	154112-1327714			4-3/0
285-197	GL	17295-00HH			35,0
285-197	KEMA	2116735.01			95
285-197	PRS	TE/1718/880590/08			95
285-197	RMR	11130002			25
285-197	UR	E45172			4-4/0

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected