



## Safety Data Sheet

according to Regulation (EC) No 1907/2006

### Kabelglide

Revision date: 27.11.2019

Product code: 151

Page 2 of 8

#### Hazard statements

H222	Extremely flammable aerosol.
H229	Pressurised container: May burst if heated.
H315	Causes skin irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.

#### Precautionary statements

P332+P313	If skin irritation occurs: Get medical advice/attention.
P211	Do not spray on an open flame or other ignition source.
P410+P412	Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
P273	Avoid release to the environment.
P271	Use only outdoors or in a well-ventilated area.
P251	Do not pierce or burn, even after use.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

### SECTION 3: Composition/information on ingredients

#### 3.2. Mixtures

##### Hazardous components

CAS No	Chemical name	Quantity
	EC No	Index No
	REACH No	
	GHS Classification	
74-98-6	propane	30-50%
	200-827-9	601-003-00-5
	Flam. Gas 1; H220	
	Hydrocarbons, C6, isoalkanes, <5% n-hexane	25-50%
	931-254-9	01-2119484651-34
	Flam. Liq. 2, Skin Irrit. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2; H225 H315 H336 H304 H411	
106-97-8	butane	20-30%
	203-448-7	601-004-00-0
	Flam. Gas 1; H220	

Full text of H and EUH statements: see section 16.

### SECTION 4: First aid measures

#### 4.1. Description of first aid measures

##### After inhalation

Provide fresh air. In case of accident or unwellness, seek medical advice immediately (show directions for use or safety data sheet if possible).

##### After contact with skin

After contact with skin, wash immediately with: Water. Change contaminated clothing.

##### After contact with eyes

Rinse immediately carefully and thoroughly with eye-bath or water.

##### After ingestion

If swallowed, immediately drink: Water.

#### 4.2. Most important symptoms and effects, both acute and delayed

No data available

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Kabelglide**

Revision date: 27.11.2019

Product code: 151

Page 3 of 8

**4.3. Indication of any immediate medical attention and special treatment needed**

No data available

**SECTION 5: Firefighting measures****5.1. Extinguishing media****Suitable extinguishing media**Carbon dioxide (CO<sub>2</sub>). Foam. Extinguishing powder.**Unsuitable extinguishing media**

Water with tenside additive. Water.

**5.2. Special hazards arising from the substance or mixture**

Combustible. Vapours may form explosive mixtures with air. Heating causes rise in pressure with risk of bursting.

**5.3. Advice for firefighters**

Wear a self-contained breathing apparatus and chemical protective clothing.

**Additional information**

Use water spray jet to protect personnel and to cool endangered containers. Suppress gases/vapours/mists with water spray jet. Contaminated fire-fighting water must be collected separately. Do not allow to enter into surface water or drains.

**SECTION 6: Accidental release measures****6.1. Personal precautions, protective equipment and emergency procedures**

Remove all sources of ignition. Provide adequate ventilation. Wear a self-contained breathing apparatus and chemical protective clothing.

**6.2. Environmental precautions**

Do not allow to enter into surface water or drains. Explosion hazard.

**6.3. Methods and material for containment and cleaning up**

Ventilate affected area.

**SECTION 7: Handling and storage****7.1. Precautions for safe handling****Advice on safe handling**

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

**Advice on protection against fire and explosion**

Keep away from sources of ignition - No smoking.

**7.2. Conditions for safe storage, including any incompatibilities****Requirements for storage rooms and vessels**

Keep container tightly closed. Keep in a cool, well-ventilated place. Keep away from sources of ignition - No smoking.

**Hints on joint storage**

Do not store together with: Material, rich in oxygen, oxidizing.

**SECTION 8: Exposure controls/personal protection****8.1. Control parameters**

## Safety Data Sheet

according to Regulation (EC) No 1907/2006

### Kabelglide

Revision date: 27.11.2019

Product code: 151

Page 4 of 8

#### Exposure limits (EH40)

CAS No	Substance	ppm	mg/m <sup>3</sup>	fibres/ml	Category	Origin
106-97-8	Butane	600	1450		TWA (8 h)	WEL
		750	1810		STEL (15 min)	WEL

#### 8.2. Exposure controls



##### Appropriate engineering controls

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

##### Protective and hygiene measures

Remove contaminated, saturated clothing immediately. Protect skin by using skin protective cream. After work, wash hands and face. When using do not eat or drink.

##### Eye/face protection

Tightly sealed safety glasses.

##### Hand protection

DIN EN 374 Tested protective gloves are to be worn: NBR (Nitrile rubber) For special purposes, it is recommended to check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves. NBR (Nitrile rubber)

##### Skin protection

Protective clothing:

##### Respiratory protection

In case of inadequate ventilation wear respiratory protection.

### SECTION 9: Physical and chemical properties

#### 9.1. Information on basic physical and chemical properties

Physical state:	Aerosol
Colour:	
Odour:	characteristic

##### Changes in the physical state

Initial boiling point and boiling range:	-0,5 °C
Flash point:	< 0 °C
Lower explosion limits:	1,2 vol. %
Upper explosion limits:	9,4 vol. %
Ignition temperature:	298 °C
Vapour pressure:	2100 hPa
(at 20 °C)	
Vapour pressure:	4900 hPa
(at 50 °C)	
Density (at 20 °C):	0,72 g/cm <sup>3</sup>

### SECTION 10: Stability and reactivity

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Kabelglide**

Revision date: 27.11.2019

Product code: 151

Page 5 of 8

**10.1. Reactivity**

No data available

**10.2. Chemical stability**

No data available

**10.3. Possibility of hazardous reactions**

No data available

**10.4. Conditions to avoid**

Keep away from heat. Ignition hazard.

**10.5. Incompatible materials**

No data available

**10.6. Hazardous decomposition products**

No data available

**SECTION 11: Toxicological information**
**11.1. Information on toxicological effects**
**Acute toxicity**

CAS No	Chemical name					
	Exposure route	Dose	Species	Source	Method	
	Hydrocarbons, C6, isoalkanes, <5% n-hexane					
	oral	LD50 >1000 mg/kg	Fisch 1			
106-97-8	butane					
	inhalation (4 h) gas	LC50 273000 ppm	Rat	GESTIS		

**Irritation and corrosivity**

Vapours may cause drowsiness and dizziness. After skin contact: irritant.

**SECTION 12: Ecological information**
**12.1. Toxicity**

Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

CAS No	Chemical name					
	Aquatic toxicity	Dose	[h]   [d]	Species	Source	Method
	Hydrocarbons, C6, isoalkanes, <5% n-hexane					
	Acute algae toxicity	ErC50 >1000 mg/l	72 h	Alge		
	Acute crustacea toxicity	EC50 >1000 mg/l	48 h	Daphnia pulex (water flea)		

**12.3. Bioaccumulative potential**
**Partition coefficient n-octanol/water**

CAS No	Chemical name	Log Pow
74-98-6	propane	2,36
106-97-8	butane	2,89

**Further information**

Do not allow to enter into surface water or drains.

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Kabelglide**

Revision date: 27.11.2019

Product code: 151

Page 6 of 8

**SECTION 13: Disposal considerations****13.1. Waste treatment methods****Advice on disposal**

Do not allow to enter into surface water or drains. Dispose of waste according to applicable legislation.

**Waste disposal number of waste from residues/unused products**

160504 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; gases in pressure containers and discarded chemicals; gases in pressure containers (including halons) containing hazardous substances; hazardous waste

**Waste disposal number of contaminated packaging**

150104 WASTE PACKAGING; ABSORBENTS, WIPING CLOTHS, FILTER MATERIALS AND PROTECTIVE CLOTHING NOT OTHERWISE SPECIFIED; packaging (including separately collected municipal packaging waste); metallic packaging

**Contaminated packaging**

Non-contaminated packages may be recycled. Handle contaminated packages in the same way as the substance itself.

**SECTION 14: Transport information****Land transport (ADR/RID)**

**14.1. UN number:** UN1950  
**14.2. UN proper shipping name:** AEROSOLS  
**14.3. Transport hazard class(es):** 2  
Hazard label: 2.1



Classification code: 5F  
Special Provisions: 190 327 625  
Limited quantity: 1 L  
Transport category: 2  
Tunnel restriction code: D

**Other applicable information (land transport)**

E0

**Inland waterways transport (ADN)**

**14.1. UN number:** UN1950  
**14.2. UN proper shipping name:** AEROSOLS  
**14.3. Transport hazard class(es):** 2  
Hazard label: 2.1



Classification code: 5F  
Special Provisions: 190 327 344 625  
Limited quantity: 1 L

**Other applicable information (inland waterways transport)**

E0

**Marine transport (IMDG)**

**14.1. UN number:** UN1950

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Kabelglide**

Revision date: 27.11.2019

Product code: 151

Page 7 of 8

**14.2. UN proper shipping name:** AEROSOLS  
**14.3. Transport hazard class(es):** 2  
**14.4. Packing group:** -  
Hazard label: 2, see SP63

Special Provisions: 63, 190, 277, 327, 344, 959  
Limited quantity: See SP277  
EmS: F-D, S-U

**Other applicable information (marine transport)**  
E0

**Air transport (ICAO-TI/IATA-DGR)**

**14.1. UN number:** UN1950  
**14.2. UN proper shipping name:** AEROSOLS, flammable  
**14.3. Transport hazard class(es):** 2.1  
Hazard label: 2.1



Special Provisions: A145 A167  
Limited quantity Passenger: 30 kg G  
IATA-packing instructions - Passenger: 203  
IATA-max. quantity - Passenger: 75 kg  
IATA-packing instructions - Cargo: 203  
IATA-max. quantity - Cargo: 150 kg

**Other applicable information (air transport)**  
E0  
: Y203

**14.5. Environmental hazards**

ENVIRONMENTALLY HAZARDOUS: yes

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU regulatory information**

Restrictions on use (REACH, annex XVII):  
Entry 28: Hydrocarbons, C6, isoalkanes, <5% n-hexane; butane  
2004/42/EC (VOC): 230g/400ml Dose

**National regulatory information**

Water contaminating class (D): 2 - clearly water contaminating

**SECTION 16: Other information**

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

**Kabelglide**

Revision date: 27.11.2019

Product code: 151

Page 8 of 8

**Relevant H and EUH statements (number and full text)**

H220	Extremely flammable gas.
H222	Extremely flammable aerosol.
H225	Highly flammable liquid and vapour.
H229	Pressurised container: May burst if heated.
H304	May be fatal if swallowed and enters airways.
H315	Causes skin irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.

*(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)*