


# HER201G - HER208G

## 2.0 AMPS. Glass Passivated High Efficient Rectifiers

### DO-15



### Features

- ✦ Glass passivated chip junction.
- ✦ High efficiency, Low VF
- ✦ High current capability
- ✦ High reliability
- ✦ High surge current capability
- ✦ For use in low voltage, high frequency inverter, free wheeling, and polarity protection application.
- ✦ Green compound with suffix "G" on packing code & prefix "G" on datecode.

### Mechanical Data

- ✦ Case: Molded plastic DO-15
- ✦ Epoxy: UL 94V0 rate flame retardant
- ✦ Lead: Pure tin plated, lead free, solderable per MIL-STD-202, Method 208 guaranteed
- ✦ Polarity: Color band denotes cathode
- ✦ High temperature soldering guaranteed: 260°C/10 seconds/.375", (9.5mm) lead lengths at 5 lbs., (2.3kg) tension
- ✦ Mounting position: Any
- ✦ Weight: 0.40 gram

Dimensions in inches and (millimeters)

#### Marking Diagram



- HER20XG = Specific Device Code
- G = Green Compound
- Y = Year
- WW = Work Week

### Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	Symbol	HER 201G	HER 202G	HER 203G	HER 204G	HER 205G	HER 206G	HER 207G	HER 208G	Units	
Maximum Recurrent Peak Reverse Voltage	$V_{RRM}$	50	100	200	300	400	600	800	1000	V	
Maximum RMS Voltage	$V_{RMS}$	35	70	140	210	280	420	560	700	V	
Maximum DC Blocking Voltage	$V_{DC}$	50	100	200	300	400	600	800	1000	V	
Maximum Average Forward Rectified Current .375 (9.5mm) Lead Length @ $T_A = 55^\circ C$	$I_{(AV)}$	2.0								A	
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	$I_{FSM}$	60								A	
Maximum Instantaneous Forward Voltage @ 2.0A	$V_F$	1.0			1.3		1.7			V	
Maximum DC Reverse Current Rated DC Blocking Voltage @ $T_A=25^\circ C$ @ $T_A=125^\circ C$	$I_R$	5.0					150				$\mu A$
Maximum Reverse Recovery Time ( Note 1 )	$T_{rr}$	50					75				nS
Typical Junction Capacitance ( Note 2 )	$C_j$	35					20				pF
Typical Thermal Resistance (Note 3)	$R_{\theta JA}$	60								$^\circ C/W$	
Operating Temperature Range	$T_J$	-65 to +150									$^\circ C$
Storage Temperature Range	$T_{STG}$	-65 to +150									$^\circ C$

- Notes:
1. Reverse Recovery Test Conditions:  $I_F=0.5A$ ,  $I_R=1.0A$ ,  $I_{RR}=0.25A$
  2. Measured at 1 MHz and Applied Reverse Voltage of 4.0 V D.C.
  3. Mount on Cu-Pad Size 10mm x 10mm on P.C.B.