


Search

Home > Products > Fuses > Axial Radial Thru Hole Fuses > TR5 Fuses > 370 > 37001000410

Print

37001000410 - 370 Series



Series: 370

[Fuse 370 Datasheet](#)

The 370 Series are TR5®, sub-miniature, fast-acting type, 250V rated fuses, designed in accordance to IEC 60127- 3.

Features:

- Reduced PCB space requirements
- Direct solderable or plug-in versions
- Internationally approved
- Low internal resistance
- Shocksafe casing
- Vibration resistant
- Halogen free

Questions? [Contact Littelfuse Support](#)

Check Stock

Order Samples

NEW!
Product Selection Guide eCatalog
[Read Now](#)

Electronics
News and Information
SIGN UP NOW

Feedback

Electrical Characteristics | **Technical Resources** | **Environmental Info**

Property (Mouseover for details)	Value
Ampere Rating (A)	0.1
Nominal Melting I ² T (A ² sec)	0.0038
Interrupting Rating	35A@250VAC
Min Operating Temp °C	-40
Max Operating Temp (°C)	85
Moisture Sensitivity Level	MIL-STD-202 Method 106
Nominal Power Dissipation (W)	130
Nominal Voltage Drop (mV)	600
Nominal Cold Resistance (Ohms)	4.61
Opening	Fast-Acting (F)
Package Size	TR5 (8.5x8mm)
VAC (V)	250

Connect with Littelfuse
Sign up to receive special offers and news

For more details about how we use your information, check our [Privacy Statement](#).



[Mobile Site](#)

- About Littelfuse**
- About Littelfuse
 - Conflict Free Statement
 - History
 - Investor Relations
 - Legal
 - Press Room
 - Privacy Statement
 - Supply Chain Transparency
 - Website Feedback

- Explore Littelfuse**
- Capabilities Brochures
 - Careers
 - Check Distributor Stock
 - Competitor Cross Reference
 - Industries
 - Order Samples
 - Products
 - Services

- Technical Resources**
- Application Designs
 - Education
 - FAQs
 - iDesign™
 - Littelfuse University
 - Product Catalogs
 - Quality Documents
 - Technical Documents