



| part number | pole number | length per reel | A | n x 1,27 = B | c |
|----------------|-------------|------------------|-------------|-------------------------|-------------|
| 09 18 009 7008 | 9 | 30,48 m (100 ft) | 11,43 ±0,2 | 8 x 1,27 = 10,16 ±0,2 | ∅6,10 ±0,2 |
| 09 18 010 7008 | 10 | | 12,70 ±0,2 | 9 x 1,27 = 11,43 ±0,2 | ∅6,20 ±0,2 |
| 09 18 014 7008 | 14 | | 17,78 ±0,2 | 13 x 1,27 = 16,51 ±0,2 | ∅7,20 ±0,2 |
| 09 18 015 7008 | 15 | | 19,05 ±0,2 | 14 x 1,27 = 17,78 ±0,2 | ∅7,20 ±0,2 |
| 09 18 016 7008 | 16 | | 20,32 ±0,2 | 15 x 1,27 = 19,05 ±0,2 | ∅7,20 ±0,2 |
| 09 18 020 7008 | 20 | | 25,40 ±0,2 | 19 x 1,27 = 24,13 ±0,2 | ∅7,70 ±0,2 |
| 09 18 025 7008 | 25 | | 31,75 ±0,25 | 24 x 1,27 = 30,48 ±0,25 | ∅8,80 ±0,3 |
| 09 18 026 7008 | 26 | | 33,02 ±0,25 | 25 x 1,27 = 31,75 ±0,25 | ∅8,80 ±0,3 |
| 09 18 034 7008 | 34 | | 43,18 ±0,3 | 33 x 1,27 = 41,91 ±0,3 | ∅10,00 ±0,4 |
| 09 18 037 7008 | 37 | | 46,99 ±0,3 | 36 x 1,27 = 45,72 ±0,3 | ∅10,30 ±0,4 |
| 09 18 040 7008 | 40 | | 50,80 ±0,3 | 39 x 1,27 = 49,53 ±0,3 | ∅10,70 ±0,4 |
| 09 18 050 7008 | 50 | | 63,50 ±0,4 | 49 x 1,27 = 62,23 ±0,4 | ∅11,10 ±0,4 |
| 09 18 060 7008 | 60 | | 76,20 ±0,5 | 59 x 1,27 = 74,93 ±0,5 | ∅12,50 ±0,4 |
| 09 18 064 7008 | 64 | | 81,28 ±0,5 | 63 x 1,27 = 80,01 ±0,5 | ∅13,00 ±0,4 |



| | | |
|-----------|----------|---------------|
| conductor | material | tinned copper |
| | gauge | AWG 28/7 |

| | | |
|------------|-----------------|-----------------|
| insulation | material | PVC |
| | colour | grey (RAL 7032) |
| | polarity marker | blue |


| | | | |
|----------------|-----------------------|------------------------------------|----------------|
| technical data | test voltage | > 2 kV at 50 Hz eff. over 1 minute | |
| | insulation resistance | min. 20 MΩ/km at 20°C | |
| | conductor resistance | max. 216 Ω/km at 20°C | |
| | capacitance | max. 60 pF/m at 1 kHz | |
| | impedance (GSG) | app. 100Ω at 1 MHz | |
| | current | 2,1 A at 25°C | |
| | operating voltage | max. 300 V | |
| | temperature rating | static | -30°C to +75°C |
| | | operating | -20°C to +75°C |
| | flame resistant | acc. to UL 1581 Sec. 1061 | |
| | approvals | acc. to UL PLCC, CL2 | |



(the illustration of the cable is not true to scale)

- 01 flat cable, AWG 28/7
- 02 clear polyester
- 03 outer jacket grey PVC

cross section at flat



| | | | | | | |
|---|---------------------|--|-----------------------|-----------------------------|--------------------|--|
| | All rights reserved | Created by STORCK | Inspected by TADJE | Standardisation HOFFMANN | Date 2020-06-19 | State Final Release |
| | Department EL PD | Title SEK round flat cable w/o shielding AWG28/7 (grey) | | | | Doc-Key / ECM-Nr. 100790562/UGD/004/A 500000135932 |
| HARTING Electronics GmbH D-32339 Espelkamp | | Type TB | Number 09180XX7008 | | Rev. A | Page 1/1 |