

JUMO GmbH & Co. KG

Delivery address: Mackenrodtstraße 14,
36039 Fulda, Germany
Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
E-mail: mail@jumo.net
Internet: www.jumo.net

JUMO Instrument Co. Ltd.

JUMO House
Temple Bank, Riverway
Harlow - Essex CM20 2DY, UK
Phone: +44 1279 63 55 33
Fax: +44 1279 63 52 62
E-mail: sales@jumo.co.uk
Internet: www.jumo.co.uk

JUMO Process Control, Inc.

8 Technology Boulevard
Canastota, NY 13032, USA
Phone: 315-697-JUMO
1-800-554-JUMO
Fax: 315-697-5867
E-mail: info@jumo.us
Internet: www.jumo.us




Push-in thermocouples with bayonet lock

- for temperatures from 0 to 400°C
- as single or twin thermocouple
- good heat transfer through adjustable spring pressure
- insulated assembly, or joined to protection tube
- insertion and removal without tools

Push-in thermocouples with bayonet lock are preferred for measuring temperatures in solids, bearings and molding tools, for example in the plastics industry. The special form of the measuring tips makes these temperature probes suitable for use in flat-bottom or cone-shaped bores.

The rugged pressure spring, which also functions as a cable protector, is made from rust and acid resistant stainless steel 1.4310 and ensures a steady pressure between the measuring tip and the bottom of the hole. The fitting length can be altered by rotating the bayonet lock. Bayonet locks and suitable sockets are available in the diameters 12, 14.5, 15 and 16mm.

The measuring insert is normally fitted with thermocouples to EN 60 584 or DIN 43 710. Versions with two thermocouples are also available.



Technical data

Connection

available with cable ends as: bare wires, with ferrules, receptacles or multipole connector (e.g. connectors that are free from thermal emf)

Compensating cable

silicone, ambient temperature -50 to +180°C
PTFE, ambient temperature -190 to +260°C
metal braiding, ambient temperature -20 to +350°C

Process connection

bayonet lock, nickel-plated brass, 12mm, 14.5mm, 15mm or 16mm dia.

Protection tube

stainless steel 1.4571, 6mm and 8mm dia.

Measuring insert

insulated assembly:
1x Fe-Con J, EN 60 584, Cl. 2, operating temperature 0 to 400°C
1x Fe-Con L, DIN 43 710, Cl. 2, operating temperature 0 to 400°C
1x NiCr-Ni K, EN 60 584, Cl. 2, operating temperature 0 to 400°C
2x Fe-Con L, DIN 43 710, Cl. 2, operating temperature 0 to 400°C
2x NiCr-Ni K, EN 60 584, Cl. 2, operating temperature 0 to 400°C

Accessories

bayonet sockets, Data Sheet 90.9725


JUMO GmbH & Co. KG
 Delivery address: Mackenrodtstraße 14,
 36039 Fulda, Germany
 Postal address: 36035 Fulda, Germany
 Phone: +49 661 6003-0
 Fax: +49 661 6003-607
 E-mail: mail@jumo.net
 Internet: www.jumo.net

JUMO Instrument Co. Ltd.
 JUMO House
 Temple Bank, Riverway
 Harlow - Essex CM20 2DY, UK
 Phone: +44 1279 63 55 33
 Fax: +44 1279 63 52 62
 E-mail: sales@jumo.co.uk
 Internet: www.jumo.co.uk


JUMO Process Control, Inc.
 8 Technology Boulevard
 Canastota, NY 13032, USA
 Phone: 315-697-JUMO
 1-800-554-JUMO
 Fax: 315-697-5867
 E-mail: info@jumo.us
 Internet: www.jumo.us




Dimensions




Type 901190/10



Type 901190/20



Type 901190/30



Type 901190/40

JUMO GmbH & Co. KG
 Delivery address: Mackenrodtstraße 14,
 36039 Fulda, Germany
 Postal address: 36035 Fulda, Germany
 Phone: +49 661 6003-0
 Fax: +49 661 6003-607
 E-mail: mail@jumo.net
 Internet: www.jumo.net

JUMO Instrument Co. Ltd.
 JUMO House
 Temple Bank, Riverway
 Harlow - Essex CM20 2DY, UK
 Phone: +44 1279 63 55 33
 Fax: +44 1279 63 52 62
 E-mail: sales@jumo.co.uk
 Internet: www.jumo.co.uk

JUMO Process Control, Inc.
 8 Technology Boulevard
 Canastota, NY 13032, USA
 Phone: 315-697-JUMO
 1-800-554-JUMO
 Fax: 315-697-5867
 E-mail: info@jumo.us
 Internet: www.jumo.us




Order details: Push-in thermocouples with bayonet lock

(1) Basic version

901190/10 Push-in thermocouple, protection tube/
 measuring tip (flat-bottom) stainless steel,
 Mat. Ref. 1.4571, bayonet lock 12mm dia.

901190/20 Push-in thermocouple, protection tube/
 measuring tip (120°) stainless steel,
 Mat. Ref. 1.4571, bayonet lock 12mm dia.



(2) Operating temperature in °C/compensating cable

x	x	832	0 to 200°C/silicone
x	x	835	0 to 260°C/metal braiding
x	x	836	0 to 260°C/PTFE
x	x	848	0 to 400°C/metal braiding

(3) Measuring insert

x	x	1040	1 x Fe-Con J
x	x	1042	1 x Fe-Con L
x	x	1043	1 x NiCr-Ni K
x	x	2042	2 x Fe-Con L
x	x	2043	2 x NiCr-Ni K

(4) Protection tube diameter D in mm

x		6	6mm
x	x	8	8mm

(5) Fitting length EL in mm

x		175	20 - 175mm
	x	240	6 - 240mm

(6) Compensating cable end

x	x	03	bare cable ends
x	x	11	ferrules to DIN 46 228 Part 4 (standard)
x	x	13	receptacle 6.3 to DIN 46 247
x	x	80	multipole connector (please specify type in plain text)

(7) Compensating cable length AL in mm (500 ≤ AL ≤ 500000)

x	x	2500	2500mm (standard)
x	x	...	please specify in plain text (500mm steps)

(8) Extra codes

x	x	000	no extra code
x	x	300	bayonet lock 14.5mm dia.
x	x	302	bayonet lock 15mm dia.
x	x	303	bayonet lock 16mm dia.
x	x	309	uninsulated assembly (thermocouple welded to tip)

Order code (1) (2) (3) (4) (5) (6) (7) (8) ,...¹
 - - - - - - /

Order example 901190/10 - 848 - 1042 - 6 - 175 - 11 - 2500 / 000

1. List extra codes in sequence, separated by commas.

JUMO GmbH & Co. KG
 Delivery address: Mackenrodtstraße 14,
 36039 Fulda, Germany
 Postal address: 36035 Fulda, Germany
 Phone: +49 661 6003-0
 Fax: +49 661 6003-607
 E-mail: mail@jumo.net
 Internet: www.jumo.net

JUMO Instrument Co. Ltd.
 JUMO House
 Temple Bank, Riverway
 Harlow - Essex CM20 2DY, UK
 Phone: +44 1279 63 55 33
 Fax: +44 1279 63 52 62
 E-mail: sales@jumo.co.uk
 Internet: www.jumo.co.uk

JUMO Process Control, Inc.
 8 Technology Boulevard
 Canastota, NY 13032, USA
 Phone: 315-697-JUMO
 1-800-554-JUMO
 Fax: 315-697-5867
 E-mail: info@jumo.us
 Internet: www.jumo.us




Order details: Push-in thermocouples with bayonet lock

(1) Basic version

901190/30 Push-in thermocouple, protection tube /
 measuring tip (120°) stainless steel,
 Mat. Ref. 1.4571, bayonet lock 12mm dia.

901190/40 Push-in thermocouple, protection tube
 stainless steel, Mat. Ref. 1.4571,
 measuring tip (120°) ceramic, KER 221,
 bayonet lock 12mm dia.



		(2) Operating temperature in °C / compensating cable
x	x	832 0 to 200°C / silicone
x		835 0 to 260°C / metal braiding
x		836 0 to 260°C / PTFE
	x	848 0 to 400°C / metal braiding
		(3) Measuring insert
x	x	1040 1 x Fe-Con J
x	x	1042 1 x Fe-Con L
x	x	1043 1 x NiCr-Ni K
x	x	2042 2 x Fe-Con L
x	x	2043 2 x NiCr-Ni K
		(4) Protection tube diameter D in mm
x	x	6 6mm
		(5) Fitting length EL in mm
x		175 33 - 175mm
	x	175 29 - 175mm
		(6) Compensating cable end
x	x	03 bare cable ends
x	x	11 ferrules to DIN 46 228 Part 4 (standard)
x	x	13 receptacle 6.3 to DIN 46 247
x	x	80 multipole connector (please specify type in plain text)
		(7) Compensating cable length AL in mm (500 ≤ AL ≤ 500000)
x	x	2500 2500mm (standard)
x	x	... please specify in plain text (500mm steps)
		(8) Extra codes
x	x	000 no extra code
x	x	300 bayonet lock 14.5mm dia.
x	x	302 bayonet lock 15mm dia.
x	x	303 bayonet lock 16mm dia.
x	x	309 uninsulated assembly (thermocouple welded to tip)

Order code (1) - (2) - (3) - (4) - (5) - (6) - (7) / (8) ,...¹

Order example 901190/30 - 836 - 1042 - 6 - 175 - 11 - 2500 / 000

1. List extra codes in sequence, separated by commas.

Note: Bayonet sockets, Data Sheet 90.9725

Stock versions

(1)	(2)	(3)	(4)	(5)	(6)	(7)	(8)	Sales No.
901190/10	848	1040	6	175	11	2500	000	90/00352190
901190/10	- 848	- 1040	- 6	- 175	- 11	- 2500	/ 000	90/00371309
901190/10	- 848	- 1042	- 6	- 175	- 11	- 2500	/ 000	90/00055784
901190/10	- 848	- 1042	- 8	- 175	- 11	- 2500	/ 000	90/00055785
901190/20	- 848	- 1042	- 8	- 240	- 11	- 2500	/ 309	90/00055792
901190/30	- 835	- 1042	- 6	- 175	- 13	- 2500	/ 309	90/00055806
901190/40	- 848	- 1042	- 6	- 175	- 13	- 2500	/ 000	90/00055804