

Enter full or partial part number, keyword, certification #, etc.

Search

Home > Products > Fuses > Axial Radial Thru Hole Fuses > TE5 Fuses > 400 > 40012500440

Print

40012500440 - 400 Series



Series: 400

[Fuse 400 Datasheet](#)

The Littelfuse 400 Series is a TE5® Time Lag Fuse with High Breaking Capacity.

Features:

- Operating temperature: -40°C to 125°C
- Higher nominal melting I²T
- Higher interrupt rating
- Broad current rating 500mA to 6.3A
- Lead-Free, Halogen-Free, Compliance with RoHS
- Shock safe casing

Applications:

- SMPS for NB, printers, adaptors, consumer electronics, industrial controllers, battery chargers

Questions? [Contact Littelfuse Support](#)

Check Stock

Order Samples

NEW!
Product Selection Guide eCatalog
[Read Now](#)

Electronics
News and Information
SIGN UP NOW

Feedback

Electrical Characteristics Technical Resources Environmental Info

Property (Mouseover for details)	Value
Ampere Rating (A)	2.5
Nominal Melting I ² T (A ² sec)	61.94
Interrupting Rating	130A@250VAC
Min Operating Temp °C	-40
Max Operating Temp (°C)	85
Nominal Power Dissipation (W)	683
Nominal Voltage Drop (mV)	61
Opening	Slo-Blo/Time Lag (T)/Time Delay
Package Size	TE5 (8.5x8mm)
VAC (V)	250

Connect with Littelfuse

Sign up to receive special offers and news

Submit

For more details about how we use your information, check our [Privacy Statement](#).



Mobile Site

About Littelfuse

- About Littelfuse
- Conflict Free Statement
- History
- Investor Relations
- Legal
- Press Room
- Privacy Statement
- Supply Chain Transparency
- Website Feedback

Explore Littelfuse

- Capabilities Brochures
- Careers
- Check Distributor Stock
- Competitor Cross Reference
- Industries
- Order Samples
- Products
- Services

Technical Resources

- Application Designs
- Education
- FAQs
- iDesign™
- Littelfuse University
- Product Catalogs
- Quality Documents
- Technical Documents