

# 3M™ Scotchlok™ IDC Connector 560 & 560B, 560B, BULK, Double Run or Tap

3M ID 7000005896

- Overview
- Product Details
- Specifications
- Documents
- Contact a Representative




[View Images](#)

- Blue, polypropylene-insulated connector is suitable for tap or parallel splicing
- Unique 'U' contact provides a dependable electrical connection
- Quick and easy to use - simply snap shut without stripping or twisting the wire
- Connects a (tap) wire 0.75 mm<sup>2</sup> to 1.5 mm<sup>2</sup> solid/stranded, 1.5mm<sup>2</sup> stranded end to a through (run) wire and insulates the connection

[View all details](#)

Buy Online



**RS Components**

1 Day

Buy local

Location

## Product Details

- Blue, polypropylene-insulated connector is suitable for tap or parallel splicing
- Unique 'U' contact provides a dependable electrical connection
- Quick and easy to use - simply snap shut without stripping or twisting the wire
- Connects a (tap) wire 0.75 mm<sup>2</sup> to 1.5 mm<sup>2</sup> solid/stranded, 1.5mm<sup>2</sup> stranded end to a through (run) wire and insulates the connection

3M™ Scotchlok™ Insulation Displacement Connector 560/560B is a double run or tap connector for tap or parallel splicing.

3M™ Scotchlok™ Insulation Displacement Connector 560/560B is 600V rated for building wire and 1000V rated for signs, fixtures and luminaires. It withstands temperatures of 105 degrees C. It is suitable for general purpose electrical connections on an auto, boat, van or trailer. Polypropylene insulated, self stripping and flame retardant.

## Specifications

|   |   |
|---|---|
| Conductor Size                          | 18–16 AWG / 14 AWG Str                      |
| Connection Type                         | Double Run or Tap                           |
| Connector Style                         | Insulation Displacement                     |
| Flame Retardant                         | Yes   |
| Insulation Material                     | Polypropylene                               |
| Maximum Operating Temperature (Celsius) | 105 Degree Celsius                          |
| Maximum Recommended Voltage Rating      | 600 V                                       |
| Maximum Wire Gauge                      | 14 AWG Stranded                             |
| Minimum Wire Gauge                      | 18 AWG                                      |
| Product Colour                          | Blue  |
| RoHS 2011/65/EU Compliant               | Yes   |
| RoHS EU Comments                        | RoHS 2011/65/EU compliant without exemption |
| Water Resistant                         | No  |

## Documents

### Brochures

[unknown \(PDF, 2.0MB\)](#)

### Data Sheets

[3M™ Scotchlok™ ID Electrical Tap Connector 560B \(PDF, 72.8KB\)](#)

[3M™ Scotchlok™ ID Electrical Tap Connector 560 \(PDF, 487.9KB\)](#)

## Contact a Representative

### Send Us a Message

Thank you for your interest in 3M. In order to help us manage and respond to your query effectively, we politely ask you to provide some key information, including your contact details. The information you provide will be used to respond to your request through email or telephone by a 3M representative or one of our authorised business partners with whom we might share your personal information consistent with the [3M privacy policy](#)

#### Type of Enquiry

Select One

#### Business email address

#### Message

Please type your message here

#### First Name

#### Last Name

#### Business phone number

+44

#### Company

#### Postal Code

#### City

#### Country

United Kingdom

By checking the box, I give my consent to receive newsletters, advertisements, surveys and information about promotions and offers of 3M United Kingdom PLC and its group companies via email ([as described here](#)). I acknowledge that my personal data will be processed by 3M United Kingdom PLC and its group companies in accordance with 3M's [privacy policy](#), and that my personal data will be transferred to, stored and/or processed by 3M and third party partners on our behalf, in countries outside of the UK and European Union but always under strict obligations of confidentiality and security.

**SEND MESSAGE**

#### OUR COMPANY

- About 3M
- 3M Careers
- Investor Relations
- Partners and Suppliers
- Sustainability
- Technologies

#### NEWS

- News Center
- 3M Subscription

#### REGULATORY

- MSDS Search
- SVHC Search
- UK Modern Slavery Act Statement
- WEEE and Battery Compliance
- UK Importer's Address (GPSR 2005 Guideline)

#### HELP

- Help Centre
- Site Map

#### FOLLOW US

