



MYRRA - SERIE 44000 EI 42-14,8 5 VA

EI 42-14,8 SERIE 44000 5 VA
Primary Voltage 117 V

Secondary Protection mA	Reference	Secondary Voltage V	Secondary Current mA	No-load Voltage V	Ambient, Temperature C	Rating VA
800	44241	6	833	8,4	T 50 B	5
630	44242	9	556	12,6	T 50 B	5
400	44243	12	417	16,9	T 50 B	5
315	44244	15	333	21	T 50 B	5
315	44245	18	278	25,3	T 50 B	5
200	44246	24	33,7	32,1	T 50 B	5
400	44247	2 x 6	2 x 417	2 x 8,4	T 50 B	5
315	44248	2 x 9	2 x 278	2 x 12,6	T 50 B	5
200	44249	2 x 12	2 x 208	2 x 16,9	T 50 B	5
160	44250	2 x 15	2 x 167	2 x 21	T 50 B	5
160	44251	2 x 18	2 x 139	2 x 25,3	T 50 B	5
80	44252	2 x 24	2 x 104	2 x 33,7	T 50 B	5

EI 42-14,8 SERIE 44000 5 VA
Primary Voltage 230 V

Secondary Protection mA	Reference	Secondary Voltage V	Secondary Current mA	No-load Voltage V	Ambient, Temperature C	Rating VA
800	44229	6	833	8,4	T 50 B	5
630	44230	9	556	12,6	T 50 B	5
400	44231	12	417	16,9	T 50 B	5
315	44232	15	333	21	T 50 B	5
315	44233	18	278	25,3	T 50 B	5
200	44234	24	33,7	32,1	T 50 B	5
400	44235	2 x 6	2 x 417	2 x 8,4	T 50 B	5
315	44236	2 x 9	2 x 278	2 x 12,6	T 50 B	5

200	44237	2 x 12	2 x 208	2 x 16,9	T 50 B	5
160	44238	2 x 15	2 x 167	2 x 21	T 50 B	5
160	44239	2 x 18	2 x 139	2 x 25,3	T 50 B	5
80	44240*	2 x 24	2 x 104	2 x 33,7	T 50 B	5

- * Vacuum filling
- * Two compartments bobbins
- * Self-extinguishing plastics UL 94 VO
- * Degree of protection IP 00
- * 200 grams weight
- * Resin class B CEI 85
- (20 000h testing to CEI 126)
- * Fuse protection on secondary side (see diagram) to be assumed by customer
- * 30 V and 36 V model are VDE EN 60742 certified (production on request)
- * Insulation voltage 4 KV
- (6 KV MYRRA test)
- * 100% tested production
- * Certification : CCA procedure on request

* To be noted : 2 * 24 V model is non approved. Protection transformers according to EN 60742 circuit isolation transformer.

